

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582368

Luminaire Tested: **HCC6W35D010BZ-HM63040930-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010BZ-HM63040930-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3655.1 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582368
CATALOG NUMBER: HCC6W35D010BZ-HM63040930-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582368

CATALOG NUMBER: HCC6W35D010BZ-HM63040930-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			88	
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77	
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			68	
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			60	
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			53	
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			47	
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			42	
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			38	
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			35	
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	99252	99252	99252
5°	99763	100302	100302
10°	102553	100783	100371
15°	105812	101363	101363
20°	107051	99035	101322
25°	104909	94082	98528
30°	99230	87425	92552
35°	89804	79960	83895
40°	78125	72328	75134
45°	66759	64472	66759
50°	58582	56493	58787
55°	51114	47597	49480
60°	45194	39536	38999
65°	40095	31184	26734
70°	35391	22023	16125
75°	30140	12476	7795
80°	22478	3883	2336
85°	12328	1572	1572



TEST NUMBER: P582368

CATALOG NUMBER: HCC6W35D010BZ-HM63040930-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.7	4.8
10°-20°	508.1	13.9
20°-30°	742.1	20.3
30°-40°	778.3	21.3
40°-50°	655.7	17.9
50°-60°	459.4	12.6
60°-70°	246.3	6.7
70°-80°	82.6	2.3
80°-90°	9.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.9	39.0
0°-40°	2202.2	60.2
0°-60°	3317.2	90.8
0°-90°	3655.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3655.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1810	1810	1810	1810	1810	
5°	1813	1820	1823	1823	1823	174
15°	1864	1840	1786	1776	1786	526
25°	1734	1661	1555	1582	1629	795
35°	1342	1273	1195	1229	1254	833
45°	861	846	832	854	861	671
55°	535	518	498	508	518	481
65°	309	282	240	199	206	309
75°	142	110	59	37	37	151
85°	20	10	2	2	2	27
90°	0	0	0	0	0	



TEST NUMBER: P582368

CATALOG NUMBER: HCC6W35D010BZ-HM63040930-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1810.5	1810.5	1810.5	1810.5	1810.5	1810.5	1810.5	1810.5	1810.5
2.5°	1798.2	1798.2	1803.1	1808.0	1812.9	1812.9	1815.4	1817.8	1815.4
5°	1812.9	1812.9	1820.3	1822.7	1822.7	1820.3	1822.7	1822.7	1822.7
7.5°	1835.0	1830.1	1832.5	1827.6	1822.7	1820.3	1817.8	1817.8	1817.8
10°	1842.3	1837.4	1832.5	1822.7	1810.5	1803.1	1800.7	1803.1	1803.1
12.5°	1852.1	1847.2	1835.0	1815.4	1800.7	1788.4	1786.0	1790.9	1790.9
15°	1864.4	1859.5	1839.9	1808.0	1786.0	1773.7	1776.2	1781.1	1786.0
17.5°	1864.4	1854.6	1822.7	1781.1	1754.0	1741.7	1751.6	1763.9	1771.3
20°	1835.0	1825.2	1781.1	1729.5	1697.6	1690.3	1707.4	1729.5	1736.8
22.5°	1795.8	1776.2	1724.6	1663.3	1628.9	1628.9	1653.5	1680.5	1690.3
25°	1734.4	1719.7	1660.9	1589.7	1555.4	1552.9	1582.3	1619.1	1628.9
27.5°	1665.8	1646.2	1582.3	1508.7	1471.9	1474.4	1506.2	1543.1	1552.9
30°	1567.6	1543.1	1486.6	1415.5	1381.1	1390.9	1422.9	1449.9	1462.1
32.5°	1457.2	1435.2	1383.6	1317.4	1287.9	1297.7	1324.8	1349.3	1359.1
35°	1341.9	1317.4	1273.2	1214.4	1194.8	1204.6	1229.1	1248.7	1253.6
37.5°	1211.9	1194.8	1162.8	1116.2	1101.5	1113.8	1133.4	1145.6	1150.5
40°	1091.7	1077.0	1049.9	1015.6	1010.7	1020.5	1040.1	1047.5	1049.9
42.5°	974.0	961.6	944.5	919.9	919.9	929.7	946.9	951.8	954.3
45°	861.1	853.8	846.3	826.7	831.6	843.9	853.8	861.1	861.1
47.5°	763.0	765.4	755.6	740.9	745.8	758.1	765.4	772.8	772.8
50°	686.9	679.5	669.7	655.0	662.4	672.2	682.0	686.9	689.3
52.5°	598.6	596.1	588.8	571.6	576.5	581.4	591.2	598.6	601.0
55°	534.8	527.5	517.7	498.0	498.0	502.9	507.8	512.8	517.7
57.5°	473.5	466.1	451.4	429.3	426.9	426.9	424.4	429.3	436.7
60°	412.2	409.7	387.6	368.0	360.6	353.3	343.4	345.9	355.7
62.5°	358.2	353.3	333.6	309.1	294.4	282.1	269.8	267.4	277.2
65°	309.1	304.2	282.1	257.6	240.4	218.3	198.7	198.7	206.1
67.5°	264.9	255.1	235.5	208.5	186.5	159.4	139.8	144.7	147.2
70°	220.8	213.4	191.4	164.3	137.4	110.4	98.1	100.6	100.6
72.5°	181.6	171.8	149.6	122.7	95.7	71.2	66.3	63.8	63.8
75°	142.3	132.5	110.4	83.4	58.9	41.7	36.8	36.8	36.8
77.5°	103.0	95.7	76.1	51.5	31.9	19.6	17.2	14.7	14.7
80°	71.2	63.8	46.6	27.0	12.3	7.4	7.4	7.4	7.4
82.5°	41.7	34.3	22.1	12.3	4.9	2.5	2.5	2.5	2.5
85°	19.6	14.7	9.8	4.9	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)