

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582394

Luminaire Tested: **HCC6S35D010MW-HM63040935-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MW-HM63040935-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3347.6 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582394
CATALOG NUMBER: HCC6S35D010MW-HM63040935-61WWW

Luminous Intensity Polar Plot





TEST NUMBER: P582394

CATALOG NUMBER: HCC6S35D010MW-HM63040935-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	98517	98517	98517
5°	102889	98228	93704
10°	105693	96536	88058
15°	108309	94439	82498
20°	108795	90168	75776
25°	106506	84416	69494
30°	101047	77626	63693
35°	91785	69767	57139
40°	79964	62145	51411
45°	69193	54378	45191
50°	60442	46830	39598
55°	53408	41145	33987
60°	47990	36072	29438
65°	42975	31378	28550
70°	38388	26751	26751
75°	33296	22536	25121
80°	26708	19100	22920
85°	18304	16731	19750



TEST NUMBER: P582394
 CATALOG NUMBER: HCC6S35D010MW-HM63040935-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.9	5.0
10°-20°	469.5	14.0
20°-30°	654.3	19.5
30°-40°	674.2	20.1
40°-50°	558.7	16.7
50°-60°	401.5	12.0
60°-70°	255.7	7.6
70°-80°	131.3	3.9
80°-90°	33.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1292.7	38.6
0°-40°	1966.9	58.8
0°-60°	2927.2	87.4
0°-90°	3347.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3347.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1797	1797	1797	1797	1797	
5°	1870	1841	1785	1727	1703	179
15°	1908	1836	1664	1512	1454	538
25°	1761	1640	1396	1217	1149	807
35°	1372	1260	1042	904	854	852
45°	892	830	701	612	583	691
55°	559	513	430	382	356	503
65°	331	295	242	210	220	332
75°	157	136	106	111	119	168
85°	29	27	27	29	31	37
90°	0	0	0	0	0	



TEST NUMBER: P582394

CATALOG NUMBER: HCC6S35D010MW-HM63040935-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1797.1	1797.1	1797.1	1797.1	1797.1	1797.1	1797.1	1797.1	1797.1
2.5°	1830.9	1823.7	1814.0	1804.3	1789.8	1772.9	1758.4	1753.5	1746.3
5°	1869.7	1860.0	1840.6	1816.4	1785.0	1753.5	1726.9	1710.0	1702.8
7.5°	1893.8	1881.8	1855.2	1814.0	1768.1	1722.1	1683.4	1659.2	1649.6
10°	1898.7	1886.6	1850.3	1794.7	1734.2	1671.4	1622.9	1593.9	1581.9
12.5°	1905.9	1889.0	1843.0	1777.7	1700.3	1627.7	1567.3	1531.0	1519.0
15°	1908.4	1889.0	1835.8	1756.0	1664.0	1577.0	1511.7	1468.2	1453.6
17.5°	1898.7	1876.9	1814.0	1717.2	1613.3	1521.4	1443.9	1398.1	1378.7
20°	1864.9	1840.6	1768.1	1659.2	1545.6	1448.8	1369.0	1320.6	1298.9
22.5°	1821.3	1789.8	1707.6	1591.6	1473.0	1371.5	1291.6	1243.2	1221.5
25°	1760.8	1731.8	1639.9	1516.5	1395.6	1289.2	1216.6	1165.8	1148.9
27.5°	1690.6	1656.8	1562.5	1439.1	1315.8	1209.4	1139.2	1093.2	1071.5
30°	1596.3	1564.9	1470.5	1347.2	1226.3	1127.1	1054.5	1015.9	1006.2
32.5°	1485.1	1458.5	1366.6	1250.4	1134.3	1042.5	982.0	940.8	931.1
35°	1371.5	1339.9	1260.1	1151.2	1042.5	960.2	904.5	868.4	853.8
37.5°	1248.1	1219.0	1151.2	1054.5	957.8	880.4	832.1	800.6	786.1
40°	1117.4	1095.7	1032.8	955.4	868.4	800.6	759.5	732.9	718.4
42.5°	996.5	974.7	931.1	858.7	786.1	725.6	689.3	665.2	653.1
45°	892.5	873.1	829.6	766.7	701.4	650.6	612.0	595.1	582.9
47.5°	788.5	778.9	740.1	682.1	621.7	578.0	551.4	532.2	522.5
50°	708.7	696.6	660.3	599.8	549.1	515.2	491.0	474.0	464.3
52.5°	626.4	614.3	580.5	529.7	488.6	457.1	433.0	418.5	408.8
55°	558.8	549.1	512.8	466.8	430.5	403.9	382.2	365.3	355.6
57.5°	495.9	486.2	452.3	408.8	377.3	353.1	333.8	319.3	307.2
60°	437.7	430.5	396.7	355.6	329.0	304.7	287.8	275.8	268.5
62.5°	387.0	372.5	343.4	307.2	283.0	263.6	246.7	239.5	244.3
65°	331.3	324.1	295.1	263.6	241.9	222.5	210.4	215.3	220.1
67.5°	285.4	275.8	251.5	222.5	203.2	188.7	181.4	191.0	193.5
70°	239.5	229.8	208.0	183.8	166.9	157.2	157.2	164.4	166.9
72.5°	195.9	188.7	169.3	150.0	137.8	130.6	135.5	140.3	142.7
75°	157.2	150.0	135.5	118.6	106.4	106.4	111.2	116.1	118.6
77.5°	120.9	116.1	101.5	89.5	84.6	84.6	89.5	92.0	94.3
80°	84.6	79.8	72.6	65.4	60.5	65.4	70.1	70.1	72.6
82.5°	55.7	53.2	48.4	43.5	43.5	46.0	48.4	50.8	50.8
85°	29.1	29.1	26.6	24.2	26.6	29.1	29.1	31.4	31.4
87.5°	9.7	9.7	9.7	9.7	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)