

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582387

Luminaire Tested: **HCC6W35D010MB-HM63040935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MB-HM63040935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3616.1 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582387
CATALOG NUMBER: HCC6W35D010MB-HM63040935-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P582387

CATALOG NUMBER: HCC6W35D010MB-HM63040935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	101165	101165	101165
5°	102217	101287	100622
10°	103667	100978	99898
15°	106113	100341	99382
20°	107092	97355	97641
25°	104746	92455	94215
30°	99211	85893	88805
35°	89838	78507	81419
40°	78232	70962	73559
45°	66379	62813	65069
50°	58787	54872	56314
55°	51774	46928	46698
60°	46411	39514	36324
65°	41418	31690	26034
70°	36432	22872	16269
75°	30755	13852	9214
80°	23646	6125	3820
85°	13712	1572	1572



TEST NUMBER: P582387
 CATALOG NUMBER: HCC6W35D010MB-HM63040935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.2	4.8
10°-20°	503.5	13.9
20°-30°	727.8	20.1
30°-40°	765.8	21.2
40°-50°	643.7	17.8
50°-60°	451.8	12.5
60°-70°	248.5	6.9
70°-80°	88.2	2.4
80°-90°	11.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1406.4	38.9
0°-40°	2172.2	60.1
0°-60°	3267.7	90.4
0°-90°	3616.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3616.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1845	1845	1845	1845	1845	
5°	1858	1853	1841	1833	1828	177
15°	1870	1838	1768	1746	1751	528
25°	1732	1645	1528	1531	1558	792
35°	1342	1265	1173	1197	1217	832
45°	856	832	810	830	839	672
55°	542	513	491	491	489	488
65°	319	285	244	201	201	318
75°	145	116	65	44	44	156
85°	22	12	2	2	2	30
90°	0	0	0	0	0	



TEST NUMBER: P582387

CATALOG NUMBER: HCC6W35D010MB-HM63040935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1845.4	1845.4	1845.4	1845.4	1845.4	1845.4	1845.4	1845.4	1845.4
2.5°	1845.4	1845.4	1843.0	1843.0	1838.1	1838.1	1835.7	1835.7	1835.7
5°	1857.5	1857.5	1852.7	1845.4	1840.6	1833.4	1833.4	1830.9	1828.5
7.5°	1864.7	1862.3	1855.1	1845.4	1833.4	1821.2	1816.4	1818.8	1816.4
10°	1862.3	1857.5	1847.8	1828.5	1814.0	1797.1	1794.6	1792.2	1794.6
12.5°	1867.2	1860.0	1840.6	1816.4	1792.2	1772.9	1770.5	1770.5	1772.9
15°	1869.7	1862.3	1838.1	1801.8	1768.0	1748.6	1746.3	1748.6	1751.1
17.5°	1862.3	1852.7	1816.4	1768.0	1729.4	1710.0	1710.0	1714.8	1719.7
20°	1835.7	1821.2	1770.5	1712.3	1668.8	1654.3	1659.2	1668.8	1673.7
22.5°	1787.4	1770.5	1712.3	1647.1	1601.1	1589.1	1601.1	1613.3	1618.0
25°	1731.7	1712.3	1644.7	1577.0	1528.5	1514.1	1531.0	1550.4	1557.6
27.5°	1656.8	1635.0	1572.1	1494.7	1446.4	1439.1	1458.4	1480.2	1485.0
30°	1567.3	1543.1	1473.0	1400.4	1356.9	1354.4	1376.2	1395.5	1402.9
32.5°	1458.4	1436.7	1376.2	1303.7	1264.9	1264.9	1286.7	1303.7	1310.9
35°	1342.4	1318.1	1264.9	1204.5	1173.1	1175.4	1197.2	1209.4	1216.6
37.5°	1204.5	1197.2	1156.1	1105.3	1083.6	1088.3	1105.3	1115.0	1122.3
40°	1093.2	1073.9	1047.3	1006.2	991.6	996.5	1013.4	1023.1	1027.9
42.5°	972.3	960.2	938.4	909.4	899.8	907.0	921.5	928.8	926.4
45°	856.2	853.8	832.0	815.0	810.2	819.9	829.6	836.9	839.3
47.5°	771.5	761.8	742.6	730.4	725.6	735.2	744.9	749.8	749.8
50°	689.3	679.7	660.3	648.2	643.4	653.1	660.3	665.1	660.3
52.5°	607.1	597.4	580.5	566.0	563.5	568.3	570.8	573.2	578.0
55°	541.7	532.2	512.8	495.9	491.0	493.4	491.0	491.0	488.6
57.5°	478.9	469.3	449.9	430.5	423.3	420.8	413.6	411.1	408.8
60°	423.3	411.1	391.8	370.1	360.4	350.7	338.7	331.3	331.3
62.5°	370.1	357.9	336.2	316.8	302.4	285.4	266.1	256.4	256.4
65°	319.3	309.6	285.4	263.6	244.3	222.5	200.7	195.9	200.7
67.5°	270.9	261.2	237.0	215.3	191.0	164.4	145.2	145.2	150.0
70°	227.3	217.6	195.9	169.3	142.7	116.1	101.5	101.5	101.5
72.5°	186.3	176.6	152.4	128.1	101.5	74.9	67.7	70.1	67.7
75°	145.2	137.8	116.1	89.5	65.4	46.0	43.5	41.1	43.5
77.5°	108.9	101.5	82.3	58.0	36.3	26.6	24.2	24.2	24.2
80°	74.9	67.7	53.2	33.8	19.4	12.1	12.1	12.1	12.1
82.5°	46.0	38.7	29.1	16.9	7.2	7.2	7.2	7.2	7.2
85°	21.8	16.9	12.1	4.8	2.5	2.5	2.5	2.5	2.5
87.5°	4.8	4.8	2.5	2.5	0.0	2.5	2.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)