

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582512

Luminaire Tested: **HCC6W40D010BZ-HM63040930-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010BZ-HM63040930-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4244.4 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582512
CATALOG NUMBER: HCC6W40D010BZ-HM63040930-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582512

CATALOG NUMBER: HCC6W40D010BZ-HM63040930-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			53
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	115254	115254	115254
5°	115854	116476	116476
10°	119092	117032	116553
15°	122872	117702	117702
20°	124307	115008	117663
25°	121828	109246	114418
30°	115233	101522	107472
35°	104286	92842	97413
40°	90720	83986	87256
45°	77520	74876	77520
50°	68023	65593	68271
55°	59353	55262	57451
60°	52463	45917	45292
65°	46555	36217	31041
70°	41097	25565	18737
75°	35012	14467	9044
80°	26077	4483	2715
85°	14341	1824	1824



TEST NUMBER: P582512
 CATALOG NUMBER: HCC6W40D010BZ-HM63040930-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.7	4.8
10°-20°	590.0	13.9
20°-30°	861.8	20.3
30°-40°	903.8	21.3
40°-50°	761.4	17.9
50°-60°	533.5	12.6
60°-70°	286.0	6.7
70°-80°	95.9	2.3
80°-90°	10.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1653.4	39.0
0°-40°	2557.2	60.2
0°-60°	3852.0	90.8
0°-90°	4244.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4244.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2102	2102	2102	2102	2102	
5°	2105	2114	2117	2117	2117	202
15°	2165	2136	2074	2062	2074	611
25°	2014	1929	1806	1837	1892	923
35°	1558	1478	1387	1427	1456	967
45°	1000	983	966	991	1000	779
55°	621	601	578	590	601	559
65°	359	328	279	231	239	358
75°	165	128	68	43	43	175
85°	23	11	3	3	3	31
90°	0	0	0	0	0	



TEST NUMBER: P582512

CATALOG NUMBER: HCC6W40D010BZ-HM63040930-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2102.4	2102.4	2102.4	2102.4	2102.4	2102.4	2102.4	2102.4	2102.4
2.5°	2088.1	2088.1	2093.8	2099.5	2105.3	2105.3	2108.0	2110.9	2108.0
5°	2105.3	2105.3	2113.7	2116.6	2116.6	2113.7	2116.6	2116.6	2116.6
7.5°	2130.8	2125.2	2127.9	2122.3	2116.6	2113.7	2110.9	2110.9	2110.9
10°	2139.4	2133.7	2127.9	2116.6	2102.4	2093.8	2091.0	2093.8	2093.8
12.5°	2150.8	2145.1	2130.8	2108.0	2091.0	2076.8	2073.9	2079.5	2079.5
15°	2165.0	2159.3	2136.5	2099.5	2073.9	2059.6	2062.5	2068.2	2073.9
17.5°	2165.0	2153.7	2116.6	2068.2	2036.8	2022.6	2034.0	2048.3	2056.7
20°	2130.8	2119.5	2068.2	2008.3	1971.4	1962.8	1982.7	2008.3	2016.9
22.5°	2085.2	2062.5	2002.6	1931.4	1891.6	1891.6	1920.1	1951.3	1962.8
25°	2014.1	1997.0	1928.6	1845.9	1806.1	1803.2	1837.4	1880.1	1891.6
27.5°	1934.3	1911.5	1837.4	1752.0	1709.3	1712.1	1749.1	1791.9	1803.2
30°	1820.4	1791.9	1726.3	1643.7	1603.8	1615.2	1652.3	1683.6	1697.8
32.5°	1692.1	1666.6	1606.7	1529.8	1495.6	1507.0	1538.3	1566.8	1578.2
35°	1558.3	1529.8	1478.5	1410.1	1387.3	1398.7	1427.2	1450.0	1455.6
37.5°	1407.2	1387.3	1350.3	1296.2	1279.0	1293.3	1316.1	1330.3	1336.0
40°	1267.7	1250.5	1219.3	1179.3	1173.6	1185.1	1207.8	1216.4	1219.3
42.5°	1130.9	1116.7	1096.7	1068.3	1068.3	1079.7	1099.7	1105.3	1108.1
45°	999.9	991.4	982.8	960.0	965.8	980.0	991.4	999.9	999.9
47.5°	886.0	888.7	877.4	860.3	866.1	880.3	888.7	897.3	897.3
50°	797.6	789.2	777.7	760.7	769.1	780.6	791.9	797.6	800.5
52.5°	695.1	692.2	683.6	663.7	669.4	675.2	686.5	695.1	697.9
55°	621.0	612.4	601.1	578.2	578.2	584.1	589.7	595.4	601.1
57.5°	549.8	541.3	524.2	498.6	495.7	495.7	492.8	498.6	507.0
60°	478.5	475.8	450.0	427.4	418.8	410.2	398.9	401.6	413.1
62.5°	415.9	410.2	387.4	358.9	341.9	327.6	313.4	310.5	322.0
65°	358.9	353.2	327.6	299.1	279.2	253.5	230.7	230.7	239.3
67.5°	307.7	296.2	273.4	242.2	216.4	185.2	162.4	168.0	170.9
70°	256.4	247.8	222.3	190.9	159.5	128.2	114.0	116.9	116.9
72.5°	210.8	199.4	173.7	142.5	111.1	82.6	76.9	74.1	74.1
75°	165.3	153.8	128.2	96.8	68.3	48.4	42.7	42.7	42.7
77.5°	119.6	111.1	88.4	59.9	37.1	22.8	19.9	17.1	17.1
80°	82.6	74.1	54.1	31.4	14.2	8.6	8.6	8.6	8.6
82.5°	48.4	39.8	25.6	14.2	5.7	2.9	2.9	2.9	2.9
85°	22.8	17.1	11.3	5.7	2.9	2.9	2.9	2.9	2.9
87.5°	2.9	2.9	2.9	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)