

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593260

Luminaire Tested: **HCC6S35D010SL-HM63040950-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593260  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S35D010SL-HM63040950-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3376.8 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593260  
CATALOG NUMBER: HCC6S35D010SL-HM63040950-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P593260

CATALOG NUMBER: HCC6S35D010SL-HM63040950-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89	89	89	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79	79	79	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70	70	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	63	63	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57	57	57	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52	52	52	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48	48	48	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44	44	44	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41	41	41	41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38	38	38	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	127901
5°	127294
10°	124486
15°	121561
20°	116998
25°	110650
30°	100553
35°	81385
40°	54889
45°	37717
50°	30907
55°	27048
60°	25579
65°	24140
70°	22664
75°	21562
80°	19605
85°	17171



TEST NUMBER: P593260  
 CATALOG NUMBER: HCC6S35D010SL-HM63040950-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.4	6.5
10°-20°	601.5	17.8
20°-30°	835.7	24.7
30°-40°	744.0	22.0
40°-50°	395.0	11.7
50°-60°	258.3	7.7
60°-70°	185.1	5.5
70°-80°	107.3	3.2
80°-90°	31.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1655.6	49.0
0°-40°	2399.6	71.1
0°-60°	3053.0	90.4
0°-90°	3376.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3376.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2333	
5°	2313	218
15°	2142	602
25°	1829	836
35°	1216	744
45°	486	395
55°	283	258
65°	186	185
75°	102	107
85°	27	31
90°	0	



TEST NUMBER: P593260  
CATALOG NUMBER: HCC6S35D010SL-HM63040950-61NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2333.1
2.5°	2320.7
5°	2313.2
7.5°	2285.9
10°	2236.3
12.5°	2191.6
15°	2141.9
17.5°	2079.9
20°	2005.5
22.5°	1921.1
25°	1829.3
27.5°	1722.5
30°	1588.5
32.5°	1427.1
35°	1216.1
37.5°	982.8
40°	767.0
42.5°	595.6
45°	486.5
47.5°	414.5
50°	362.4
52.5°	320.2
55°	283.0
57.5°	255.7
60°	233.3
62.5°	211.0
65°	186.1
67.5°	163.8
70°	141.4
72.5°	121.6
75°	101.8
77.5°	81.9
80°	62.1
82.5°	44.7
85°	27.3
87.5°	12.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)