

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582429

Luminaire Tested: **HCC6S40D010SL-HM63040827-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010SL-HM63040827-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3578.6 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582429
CATALOG NUMBER: HCC6S40D010SL-HM63040827-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582429

CATALOG NUMBER: HCC6S40D010SL-HM63040827-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44																			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37																			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	110090	110090	110090
5°	112216	109883	107401
10°	116030	108482	103923
15°	119581	106601	100670
20°	121437	102156	95401
25°	119245	95159	88838
30°	113353	86710	81525
35°	101884	77497	73528
40°	87922	67913	65687
45°	74457	58463	56928
50°	63836	49380	48902
55°	55339	41576	39951
60°	48297	33758	28485
65°	42495	26008	15760
70°	36657	17214	7694
75°	31094	8388	2987
80°	24056	3567	1799
85°	14215	1761	1761



TEST NUMBER: P582429
 CATALOG NUMBER: HCC6S40D010SL-HM63040827-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	5.3
10°-20°	535.9	15.0
20°-30°	754.7	21.1
30°-40°	771.0	21.5
40°-50°	621.7	17.4
50°-60°	417.0	11.7
60°-70°	211.0	5.9
70°-80°	67.5	1.9
80°-90°	10.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1480.1	41.4
0°-40°	2251.1	62.9
0°-60°	3289.7	91.9
0°-90°	3578.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3578.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2008	2008	2008	2008	2008	
5°	2039	2025	1997	1966	1952	196
15°	2107	2022	1878	1793	1774	595
25°	1971	1816	1573	1477	1469	903
35°	1522	1384	1158	1093	1099	947
45°	960	884	754	729	734	747
55°	579	514	435	415	418	521
65°	328	271	200	133	122	327
75°	147	104	40	14	14	158
85°	23	11	3	3	3	30
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582429

CATALOG NUMBER: HCC6S40D010SL-HM63040827-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2
2.5°	2016.6	2013.8	2010.9	2005.3	1996.8	1988.4	1982.7	1977.0	1974.3
5°	2039.2	2033.6	2025.1	2013.8	1996.8	1977.0	1965.8	1954.5	1951.7
7.5°	2070.3	2059.0	2036.4	2010.9	1982.7	1954.5	1934.7	1923.4	1914.9
10°	2084.4	2064.6	2033.6	1991.2	1948.8	1914.9	1889.5	1872.6	1866.9
12.5°	2095.8	2073.1	2028.0	1971.4	1914.9	1869.8	1841.5	1827.3	1821.8
15°	2107.0	2084.4	2022.3	1948.8	1878.3	1824.6	1793.4	1779.3	1773.8
17.5°	2107.0	2076.0	2002.5	1909.3	1824.6	1759.5	1728.5	1714.4	1711.5
20°	2081.6	2047.7	1957.3	1847.1	1751.1	1677.6	1649.4	1641.0	1635.3
22.5°	2033.6	1994.1	1892.4	1768.1	1663.5	1593.0	1562.0	1556.3	1550.6
25°	1971.4	1931.9	1816.1	1683.3	1573.2	1502.6	1477.1	1471.5	1468.7
27.5°	1892.4	1850.0	1728.5	1593.0	1474.4	1406.6	1383.9	1383.9	1381.1
30°	1790.7	1742.7	1624.1	1488.5	1369.8	1307.7	1290.8	1290.8	1287.9
32.5°	1666.4	1618.4	1511.0	1381.1	1268.2	1203.2	1189.1	1194.8	1191.8
35°	1522.4	1482.8	1383.9	1256.9	1158.0	1098.7	1093.1	1098.7	1098.7
37.5°	1378.4	1341.6	1256.9	1146.7	1053.5	999.8	999.8	1008.4	1005.5
40°	1228.6	1200.4	1121.3	1025.3	949.0	912.2	906.7	915.1	917.9
42.5°	1087.4	1064.8	997.0	917.9	850.1	813.4	821.9	827.5	830.3
45°	960.4	937.7	884.0	802.1	754.1	728.7	728.7	737.2	734.3
47.5°	847.3	830.3	776.8	697.6	655.3	643.9	649.6	655.3	655.3
50°	748.5	723.1	672.2	610.0	579.0	564.9	570.5	573.4	573.4
52.5°	655.3	638.3	587.5	531.0	502.8	494.2	494.2	497.1	497.1
55°	579.0	559.3	514.0	457.6	435.0	423.7	415.2	412.3	418.0
57.5°	505.6	488.6	446.2	392.5	367.2	355.9	339.0	333.3	339.0
60°	440.5	426.4	384.1	333.3	307.9	285.3	265.5	254.2	259.8
62.5°	384.1	367.2	324.9	282.4	254.2	228.7	197.7	180.7	189.3
65°	327.6	313.5	271.2	228.7	200.5	169.5	132.7	121.5	121.5
67.5°	276.7	262.6	223.2	186.4	152.5	115.8	81.9	79.1	81.9
70°	228.7	214.6	180.7	144.0	107.4	70.6	48.0	48.0	48.0
72.5°	189.3	172.3	141.3	104.5	67.8	36.7	25.5	28.2	28.2
75°	146.8	132.7	104.5	70.6	39.6	16.9	14.1	14.1	14.1
77.5°	110.1	98.8	73.5	45.2	19.8	5.7	5.7	5.7	5.7
80°	76.2	65.0	48.0	28.2	11.3	5.7	5.7	5.7	5.7
82.5°	45.2	39.6	28.2	14.1	5.7	2.8	2.8	2.8	2.8
85°	22.6	19.8	11.3	5.7	2.8	2.8	2.8	2.8	2.8
87.5°	5.7	5.7	2.8	2.8	0.0	2.8	2.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)