

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582423

Luminaire Tested: **HCC6W40D010MW-HM63040827-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010MW-HM63040827-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4222.6 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582423
CATALOG NUMBER: HCC6W40D010MW-HM63040827-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P582423

CATALOG NUMBER: HCC6W40D010MW-HM63040827-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	118137	118137	118137
5°	119365	118275	117499
10°	121062	117911	116653
15°	123905	117174	116051
20°	125054	113690	114017
25°	122318	107970	110020
30°	115847	100294	103693
35°	104902	91671	95071
40°	91350	82870	85897
45°	77512	73349	75977
50°	68654	64075	65763
55°	60461	54803	54526
60°	54184	46137	42431
65°	48345	37008	30405
70°	42555	26703	19010
75°	35902	16140	10760
80°	27655	7135	4451
85°	16039	1761	1761



TEST NUMBER: P582423
 CATALOG NUMBER: HCC6W40D010MW-HM63040827-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.6	4.8
10°-20°	587.9	13.9
20°-30°	849.8	20.1
30°-40°	894.2	21.2
40°-50°	751.7	17.8
50°-60°	527.6	12.5
60°-70°	290.2	6.9
70°-80°	103.0	2.4
80°-90°	13.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1642.3	38.9
0°-40°	2536.5	60.1
0°-60°	3815.8	90.4
0°-90°	4222.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4222.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2155	2155	2155	2155	2155	
5°	2169	2163	2149	2141	2135	207
15°	2183	2146	2065	2039	2045	616
25°	2022	1920	1785	1788	1819	925
35°	1568	1477	1370	1398	1421	971
45°	1000	972	946	969	980	784
55°	633	599	573	573	570	569
65°	373	333	285	234	234	371
75°	170	136	76	51	51	182
85°	26	14	3	3	3	35
90°	0	0	0	0	0	



TEST NUMBER: P582423

CATALOG NUMBER: HCC6W40D010MW-HM63040827-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0
2.5°	2155.0	2155.0	2152.1	2152.1	2146.4	2146.4	2143.6	2143.6	2143.6
5°	2169.1	2169.1	2163.4	2155.0	2149.3	2140.9	2140.9	2138.0	2135.2
7.5°	2177.5	2174.8	2166.2	2155.0	2140.9	2126.8	2121.1	2123.9	2121.1
10°	2174.8	2169.1	2157.8	2135.2	2118.2	2098.4	2095.6	2092.9	2095.6
12.5°	2180.3	2171.9	2149.3	2121.1	2092.9	2070.2	2067.4	2067.4	2070.2
15°	2183.2	2174.8	2146.4	2104.1	2064.6	2041.9	2039.2	2041.9	2044.8
17.5°	2174.8	2163.4	2121.1	2064.6	2019.4	1996.8	1996.8	2002.4	2008.0
20°	2143.6	2126.8	2067.4	1999.6	1948.8	1931.8	1937.5	1948.8	1954.4
22.5°	2087.2	2067.4	1999.6	1923.4	1869.7	1855.6	1869.7	1883.8	1889.5
25°	2022.2	1999.6	1920.5	1841.5	1785.0	1768.0	1787.8	1810.3	1818.9
27.5°	1934.7	1909.3	1835.8	1745.4	1689.0	1680.4	1703.1	1728.4	1734.1
30°	1830.1	1801.9	1720.0	1635.3	1584.4	1581.6	1607.1	1629.6	1638.1
32.5°	1703.1	1677.6	1607.1	1522.3	1477.1	1477.1	1502.5	1522.3	1530.8
35°	1567.5	1539.3	1477.1	1406.4	1369.8	1372.6	1398.0	1412.1	1420.6
37.5°	1406.4	1398.0	1350.0	1290.6	1265.3	1271.0	1290.6	1302.0	1310.4
40°	1276.5	1254.0	1223.0	1175.0	1158.0	1163.6	1183.4	1194.6	1200.3
42.5°	1135.4	1121.3	1095.8	1061.9	1050.6	1059.2	1076.0	1084.5	1081.7
45°	999.8	997.0	971.6	951.8	946.1	957.5	968.7	977.2	980.0
47.5°	901.0	889.7	867.1	853.0	847.3	858.5	869.9	875.6	875.6
50°	805.0	793.6	771.1	757.0	751.3	762.5	771.1	776.6	771.1
52.5°	709.0	697.6	677.8	661.0	658.0	663.7	666.5	669.4	675.1
55°	632.6	621.4	598.7	579.0	573.4	576.1	573.4	573.4	570.5
57.5°	559.3	547.9	525.4	502.7	494.2	491.5	483.0	480.1	477.3
60°	494.2	480.1	457.6	432.1	420.8	409.5	395.4	387.0	387.0
62.5°	432.1	418.0	392.5	370.0	353.1	333.3	310.6	299.4	299.4
65°	372.7	361.5	333.3	307.9	285.3	259.8	234.4	228.7	234.4
67.5°	316.3	305.1	276.7	251.4	223.2	192.0	169.5	169.5	175.2
70°	265.5	254.2	228.7	197.7	166.6	135.6	118.6	118.6	118.6
72.5°	217.5	206.2	177.9	149.7	118.6	87.6	79.1	81.9	79.1
75°	169.5	161.0	135.6	104.5	76.2	53.7	50.8	48.0	50.8
77.5°	127.2	118.6	96.0	67.8	42.3	31.1	28.2	28.2	28.2
80°	87.6	79.1	62.1	39.6	22.6	14.1	14.1	14.1	14.1
82.5°	53.7	45.2	33.9	19.8	8.4	8.4	8.4	8.4	8.4
85°	25.5	19.8	14.1	5.7	2.8	2.8	2.8	2.8	2.8
87.5°	5.7	5.7	2.8	2.8	0.0	2.8	2.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)