

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582565

Luminaire Tested: **HCC6W45D010BZ-HM64560827-61PSMDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582565  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W45D010BZ-HM64560827-61PSMDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4320.4 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582565  
CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582565

CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	154417
5°	154000
10°	151706
15°	149303
20°	144388
25°	137524
30°	125570
35°	101101
40°	68135
45°	49687
50°	42950
55°	38794
60°	36806
65°	34842
70°	32778
75°	31030
80°	28918
85°	26858



TEST NUMBER: P582565  
 CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	264.9	6.1
10°-20°	738.8	17.1
20°-30°	1037.9	24.0
30°-40°	923.9	21.4
40°-50°	516.3	12.0
50°-60°	367.9	8.5
60°-70°	267.6	6.2
70°-80°	155.0	3.6
80°-90°	48.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2041.5	47.3
0°-40°	2965.5	68.6
0°-60°	3849.6	89.1
0°-90°	4320.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4320.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2817	
5°	2798	265
15°	2631	739
25°	2274	1038
35°	1511	924
45°	641	516
55°	406	368
65°	269	268
75°	146	155
85°	43	48
90°	0	



TEST NUMBER: P582565  
CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2816.8
2.5°	2804.6
5°	2798.5
7.5°	2774.1
10°	2725.3
12.5°	2679.5
15°	2630.7
17.5°	2563.6
20°	2475.0
22.5°	2377.4
25°	2273.6
27.5°	2145.4
30°	1983.7
32.5°	1776.2
35°	1510.7
37.5°	1211.6
40°	952.1
42.5°	759.9
45°	640.9
47.5°	561.5
50°	503.6
52.5°	451.7
55°	405.9
57.5°	369.3
60°	335.7
62.5°	305.2
65°	268.6
67.5°	238.0
70°	204.5
72.5°	174.0
75°	146.5
77.5°	119.1
80°	91.6
82.5°	67.1
85°	42.7
87.5°	21.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)