

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582571

Luminaire Tested: **HCC6W45D010SL-HM64560827-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010SL-HM64560827-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4454.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582571
CATALOG NUMBER: HCC6W45D010SL-HM64560827-61WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582571

CATALOG NUMBER: HCC6W45D010SL-HM64560827-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51								
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39								
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152016
5°	151926
10°	150454
15°	148894
20°	144685
25°	138577
30°	128602
35°	110657
40°	80773
45°	55347
50°	44485
55°	38775
60°	35787
65°	34037
70°	31768
75°	29717
80°	26961
85°	23021



TEST NUMBER: P582571
 CATALOG NUMBER: HCC6W45D010SL-HM64560827-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.7	5.9
10°-20°	736.8	16.5
20°-30°	1047.9	23.5
30°-40°	1008.9	22.6
40°-50°	580.5	13.0
50°-60°	367.8	8.3
60°-70°	260.4	5.8
70°-80°	148.4	3.3
80°-90°	42.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2046.4	45.9
0°-40°	3055.3	68.6
0°-60°	4003.5	89.9
0°-90°	4454.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4454.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2773	
5°	2761	262
15°	2624	737
25°	2291	1048
35°	1654	1009
45°	714	580
55°	406	368
65°	262	260
75°	140	148
85°	37	42
90°	0	



TEST NUMBER: P582571
CATALOG NUMBER: HCC6W45D010SL-HM64560827-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2773.0
2.5°	2760.8
5°	2760.8
7.5°	2742.5
10°	2702.8
12.5°	2663.2
15°	2623.5
17.5°	2562.5
20°	2480.1
22.5°	2388.6
25°	2291.0
27.5°	2172.0
30°	2031.6
32.5°	1860.8
35°	1653.5
37.5°	1400.2
40°	1128.7
42.5°	890.8
45°	713.9
47.5°	600.9
50°	521.6
52.5°	457.6
55°	405.7
57.5°	360.0
60°	326.4
62.5°	295.9
65°	262.4
67.5°	231.9
70°	198.2
72.5°	167.7
75°	140.3
77.5°	112.8
80°	85.4
82.5°	61.0
85°	36.6
87.5°	15.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)