

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593283

Luminaire Tested: **HCC6W40D010MB-HM63040850-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010MB-HM63040850-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4186.1 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593283
CATALOG NUMBER: HCC6W40D010MB-HM63040850-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593283

CATALOG NUMBER: HCC6W40D010MB-HM63040850-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44																			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37																			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	128773	128773	128773
5°	131268	128538	125627
10°	135730	126896	121569
15°	139882	124694	117753
20°	142054	119500	111596
25°	139490	111315	103917
30°	132596	101427	95369
35°	119177	90654	86010
40°	102850	79442	76844
45°	87087	68387	66604
50°	74676	57764	57201
55°	64734	48620	46737
60°	56520	39481	33320
65°	49720	30418	18433
70°	42892	20132	9008
75°	36410	9807	3495
80°	28160	4167	2084
85°	16605	2076	2076



TEST NUMBER: P593283
 CATALOG NUMBER: HCC6W40D010MB-HM63040850-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	5.3
10°-20°	626.9	15.0
20°-30°	882.8	21.1
30°-40°	901.9	21.5
40°-50°	727.2	17.4
50°-60°	487.8	11.7
60°-70°	246.8	5.9
70°-80°	78.9	1.9
80°-90°	12.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1731.3	41.4
0°-40°	2633.3	62.9
0°-60°	3848.2	91.9
0°-90°	4186.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4186.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2349	2349	2349	2349	2349	
5°	2385	2369	2336	2300	2283	230
15°	2465	2366	2197	2098	2075	696
25°	2306	2124	1840	1728	1718	1056
35°	1781	1619	1355	1279	1285	1108
45°	1123	1034	882	852	859	874
55°	677	601	509	486	489	609
65°	383	317	234	155	142	383
75°	172	122	46	16	16	185
85°	26	13	3	3	3	35
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593283

CATALOG NUMBER: HCC6W40D010MB-HM63040850-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2349.0	2349.0	2349.0	2349.0	2349.0	2349.0	2349.0	2349.0	2349.0
2.5°	2359.0	2355.7	2352.3	2345.7	2335.8	2325.9	2319.3	2312.7	2309.4
5°	2385.4	2378.8	2368.9	2355.7	2335.8	2312.7	2299.5	2286.2	2282.9
7.5°	2421.7	2408.5	2382.1	2352.3	2319.3	2286.2	2263.1	2250.0	2240.1
10°	2438.3	2415.1	2378.8	2329.2	2279.6	2240.1	2210.2	2190.5	2183.9
12.5°	2451.5	2425.1	2372.2	2306.1	2240.1	2187.2	2154.2	2137.6	2131.0
15°	2464.7	2438.3	2365.6	2279.6	2197.1	2134.3	2098.0	2081.4	2074.8
17.5°	2464.7	2428.4	2342.4	2233.5	2134.3	2058.3	2022.0	2005.4	2002.1
20°	2435.0	2395.3	2289.7	2160.8	2048.4	1962.5	1929.4	1919.5	1912.9
22.5°	2378.8	2332.5	2213.5	2068.2	1946.1	1863.4	1827.1	1820.5	1813.9
25°	2306.1	2259.8	2124.4	1969.1	1840.3	1757.7	1727.9	1721.3	1718.0
27.5°	2213.5	2164.1	2022.0	1863.4	1724.6	1645.3	1618.9	1618.9	1615.6
30°	2094.7	2038.5	1899.8	1741.2	1602.3	1529.6	1509.9	1509.9	1506.6
32.5°	1949.4	1893.2	1767.6	1615.6	1483.5	1407.5	1390.9	1397.5	1394.2
35°	1780.8	1734.5	1618.9	1470.3	1354.6	1285.2	1278.6	1285.2	1285.2
37.5°	1612.3	1569.3	1470.3	1341.4	1232.3	1169.6	1169.6	1179.4	1176.2
40°	1437.2	1404.2	1311.6	1199.4	1110.1	1067.2	1060.6	1070.5	1073.8
42.5°	1272.0	1245.5	1166.3	1073.8	994.5	951.5	961.4	968.0	971.3
45°	1123.3	1096.9	1034.1	938.3	882.1	852.3	852.3	862.4	859.1
47.5°	991.2	971.3	908.5	816.1	766.5	753.3	759.9	766.5	766.5
50°	875.6	845.7	786.4	713.6	677.3	660.8	667.4	670.7	670.7
52.5°	766.5	746.7	687.2	621.1	588.1	578.1	578.1	581.5	581.5
55°	677.3	654.2	601.3	535.3	508.7	495.5	485.7	482.4	489.0
57.5°	591.4	571.5	522.1	459.3	429.5	416.3	396.5	389.9	396.5
60°	515.5	498.8	449.4	389.9	360.1	333.7	310.6	297.3	303.9
62.5°	449.4	429.5	380.0	330.4	297.3	267.6	231.2	211.4	221.3
65°	383.3	366.7	317.2	267.6	234.5	198.2	155.2	142.1	142.1
67.5°	323.8	307.3	261.0	218.0	178.5	135.5	95.8	92.5	95.8
70°	267.6	251.1	211.4	168.4	125.6	82.6	56.2	56.2	56.2
72.5°	221.3	201.5	165.1	122.3	79.3	43.0	29.7	33.0	33.0
75°	171.9	155.2	122.3	82.6	46.3	19.8	16.5	16.5	16.5
77.5°	128.9	115.7	85.9	52.9	23.1	6.6	6.6	6.6	6.6
80°	89.2	76.0	56.2	33.0	13.2	6.6	6.6	6.6	6.6
82.5°	52.9	46.3	33.0	16.5	6.6	3.3	3.3	3.3	3.3
85°	26.4	23.1	13.2	6.6	3.3	3.3	3.3	3.3	3.3
87.5°	6.6	6.6	3.3	3.3	0.0	3.3	3.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)