

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582581

Luminaire Tested: **HCC6W45D010BZ-HM64560830-61NDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W45D010BZ-HM64560830-61NDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4784.3 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582581  
CATALOG NUMBER: HCC6W45D010BZ-HM64560830-61NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582581

CATALOG NUMBER: HCC6W45D010BZ-HM64560830-61NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93	93	93	93	93	93	93	93	93	93	93	93															
	2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87	87	87	87	87	87	87															
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81	81	81	81	81	81	81	81														
	4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75	75	75	75	75	75	75	75	75	75														
	5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70	70	70	70	70	70	70	70	70	70														
	6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65	65	65	65	65	65	65	65	65	65	65													
	7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61	61	61	61	61	61	61	61	61	61	61	61	61	61													
	8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57	57	57	57	57	57	57	57	57	57	57	57	57	57													
	9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54	54	54	54	54	54	54	54	54	54	54	54	54	54													
	10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51	51	51	51	51	51	51	51	51	51	51	51	51	51													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	292871
5°	291635
10°	284731
15°	270285
20°	240908
25°	202941
30°	161683
35°	115355
40°	62023
45°	26576
50°	12085
55°	4406
60°	2171
65°	1699
70°	1587
75°	699
80°	1042
85°	0



TEST NUMBER: P582581  
 CATALOG NUMBER: HCC6W45D010BZ-HM64560830-61NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	500.3	10.5
10°-20°	1320.1	27.6
20°-30°	1528.9	32.0
30°-40°	1057.2	22.1
40°-50°	305.3	6.4
50°-60°	52.6	1.1
60°-70°	13.4	0.3
70°-80°	5.2	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3349.3	70.0
0°-40°	4406.5	92.1
0°-60°	4764.4	99.6
0°-90°	4784.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4784.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5342	
5°	5300	500
15°	4762	1320
25°	3355	1529
35°	1724	1057
45°	343	305
55°	46	53
65°	13	13
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P582581  
CATALOG NUMBER: HCC6W45D010BZ-HM64560830-61NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5342.4
2.5°	5319.3
5°	5299.6
7.5°	5240.3
10°	5115.0
12.5°	4963.4
15°	4762.4
17.5°	4479.0
20°	4129.5
22.5°	3744.0
25°	3355.1
27.5°	2956.3
30°	2554.2
32.5°	2152.1
35°	1723.7
37.5°	1278.8
40°	866.7
42.5°	547.1
45°	342.8
47.5°	220.8
50°	141.7
52.5°	85.7
55°	46.1
57.5°	26.4
60°	19.8
62.5°	16.4
65°	13.1
67.5°	9.9
70°	9.9
72.5°	6.6
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)