

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582592

Luminaire Tested: **HCC6S45D010SL-HM64560830-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560830-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4560.2 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582592
CATALOG NUMBER: HCC6S45D010SL-HM64560830-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582592

CATALOG NUMBER: HCC6S45D010SL-HM64560830-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	134211	134211	134211
5°	140155	133810	127647
10°	143980	131505	119954
15°	147543	128656	112390
20°	148203	122826	103224
25°	145091	114999	94669
30°	137654	105744	86767
35°	125026	95044	77838
40°	108933	84651	70031
45°	94258	74077	61565
50°	82334	63785	53951
55°	72752	56055	46287
60°	65389	49130	40095
65°	58554	42741	38889
70°	52284	36432	36432
75°	45369	30712	34186
80°	36400	25982	31222
85°	24845	22769	26921



TEST NUMBER: P582592
 CATALOG NUMBER: HCC6S45D010SL-HM64560830-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.1	5.0
10°-20°	639.6	14.0
20°-30°	891.3	19.5
30°-40°	918.4	20.1
40°-50°	761.1	16.7
50°-60°	547.0	12.0
60°-70°	348.3	7.6
70°-80°	178.9	3.9
80°-90°	45.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1761.0	38.6
0°-40°	2679.4	58.8
0°-60°	3987.5	87.4
0°-90°	4560.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4560.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2448	2448	2448	2448	2448	
5°	2547	2507	2432	2353	2320	244
15°	2600	2501	2267	2059	1980	733
25°	2399	2234	1901	1657	1565	1099
35°	1868	1717	1420	1232	1163	1160
45°	1216	1130	956	834	794	941
55°	761	698	586	521	484	686
65°	451	402	330	287	300	452
75°	214	184	145	152	161	228
85°	40	36	36	40	43	51
90°	0	0	0	0	0	



TEST NUMBER: P582592

CATALOG NUMBER: HCC6S45D010SL-HM64560830-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2448.2	2448.2	2448.2	2448.2	2448.2	2448.2	2448.2	2448.2	2448.2
2.5°	2494.3	2484.4	2471.2	2458.0	2438.2	2415.2	2395.4	2388.8	2379.0
5°	2546.9	2533.8	2507.4	2474.4	2431.6	2388.8	2352.6	2329.5	2319.6
7.5°	2579.9	2563.5	2527.2	2471.2	2408.5	2346.0	2293.2	2260.3	2247.1
10°	2586.5	2570.0	2520.5	2444.8	2362.4	2276.8	2210.9	2171.3	2154.9
12.5°	2596.4	2573.3	2510.7	2421.8	2316.3	2217.4	2135.1	2085.7	2069.2
15°	2599.7	2573.3	2500.8	2392.1	2266.9	2148.2	2059.3	2000.0	1980.3
17.5°	2586.5	2556.8	2471.2	2339.4	2197.7	2072.5	1967.0	1904.5	1878.1
20°	2540.4	2507.4	2408.5	2260.3	2105.4	1973.7	1865.0	1799.0	1769.4
22.5°	2481.0	2438.2	2326.2	2168.1	2006.7	1868.2	1759.5	1693.6	1663.9
25°	2398.7	2359.1	2234.0	2065.9	1901.2	1756.2	1657.3	1588.1	1565.1
27.5°	2303.2	2257.0	2128.5	1960.4	1792.5	1647.5	1551.9	1489.2	1459.7
30°	2174.6	2131.8	2003.2	1835.3	1670.5	1535.5	1436.6	1383.9	1370.7
32.5°	2023.1	1986.8	1861.7	1703.4	1545.3	1420.2	1337.7	1281.7	1268.5
35°	1868.2	1825.4	1716.7	1568.4	1420.2	1308.1	1232.2	1182.9	1163.1
37.5°	1700.1	1660.6	1568.4	1436.6	1304.7	1199.4	1133.5	1090.7	1070.8
40°	1522.2	1492.6	1406.9	1301.4	1182.9	1090.7	1034.6	998.3	978.6
42.5°	1357.5	1327.8	1268.5	1169.7	1070.8	988.5	939.1	906.1	889.6
45°	1215.8	1189.4	1130.2	1044.4	955.5	886.3	833.7	810.5	794.1
47.5°	1074.1	1061.0	1008.2	929.1	846.8	787.4	751.2	724.9	711.7
50°	965.4	949.0	899.5	817.1	747.9	701.8	668.8	645.9	632.6
52.5°	853.4	836.9	790.7	721.6	665.6	622.7	589.8	570.0	556.8
55°	761.2	747.9	698.5	635.9	586.5	550.3	520.6	497.6	484.3
57.5°	675.4	662.3	616.2	556.8	514.0	481.0	454.7	434.9	418.4
60°	596.4	586.5	540.4	484.3	448.1	415.1	392.1	375.6	365.7
62.5°	527.1	507.4	467.9	418.4	385.4	359.2	336.1	326.2	332.8
65°	451.4	441.5	402.0	359.2	329.5	303.1	286.7	293.2	299.8
67.5°	388.8	375.6	342.6	303.1	276.8	257.0	247.2	260.3	263.6
70°	326.2	313.1	283.4	250.4	227.3	214.2	214.2	224.0	227.3
72.5°	266.9	257.0	230.6	204.3	187.8	177.9	184.5	191.1	194.4
75°	214.2	204.3	184.5	161.4	145.0	145.0	151.6	158.1	161.4
77.5°	164.7	158.1	138.4	121.9	115.3	115.3	121.9	125.2	128.4
80°	115.3	108.7	98.9	88.9	82.3	88.9	95.6	95.6	98.9
82.5°	75.8	72.5	65.9	59.4	59.4	62.6	65.9	69.2	69.2
85°	39.5	39.5	36.2	33.0	36.2	39.5	39.5	42.8	42.8
87.5°	13.1	13.1	13.1	13.1	16.4	16.4	16.4	16.4	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)