

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582494

Luminaire Tested: **HCC6S40D010MW-HM63040927-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010MW-HM63040927-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3553.4 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582494
CATALOG NUMBER: HCC6S40D010MW-HM63040927-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582494

CATALOG NUMBER: HCC6S40D010MW-HM63040927-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	96489	96489	96489
5°	96984	97518	97518
10°	99703	97977	97582
15°	102872	98536	98536
20°	104070	96276	98510
25°	101994	91463	95788
30°	96471	84994	89982
35°	87308	77731	81566
40°	75949	70325	73051
45°	64906	62681	64906
50°	56953	54915	57158
55°	49690	46278	48094
60°	43933	38440	37914
65°	38980	30315	25995
70°	34397	21414	15660
75°	29314	12115	7562
80°	21815	3757	2241
85°	12014	1510	1510



TEST NUMBER: P582494

CATALOG NUMBER: HCC6S40D010MW-HM63040927-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.8	4.8
10°-20°	494.0	13.9
20°-30°	721.5	20.3
30°-40°	756.6	21.3
40°-50°	637.4	17.9
50°-60°	446.6	12.6
60°-70°	239.4	6.7
70°-80°	80.3	2.3
80°-90°	8.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1384.3	39.0
0°-40°	2140.9	60.2
0°-60°	3224.9	90.8
0°-90°	3553.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3553.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1760	1760	1760	1760	1760	
5°	1762	1770	1772	1772	1772	169
15°	1813	1789	1736	1727	1736	511
25°	1686	1615	1512	1538	1584	772
35°	1305	1238	1162	1195	1219	810
45°	837	823	808	830	837	652
55°	520	503	484	494	503	468
65°	300	274	234	193	200	300
75°	138	107	57	36	36	147
85°	19	10	2	2	2	26
90°	0	0	0	0	0	



TEST NUMBER: P582494

CATALOG NUMBER: HCC6S40D010MW-HM63040927-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1760.1	1760.1	1760.1	1760.1	1760.1	1760.1	1760.1	1760.1	1760.1
2.5°	1748.2	1748.2	1753.0	1757.7	1762.4	1762.4	1764.8	1767.2	1764.8
5°	1762.4	1762.4	1769.7	1772.1	1772.1	1769.7	1772.1	1772.1	1772.1
7.5°	1783.9	1779.2	1781.6	1776.8	1772.1	1769.7	1767.2	1767.2	1767.2
10°	1791.1	1786.3	1781.6	1772.1	1760.1	1753.0	1750.6	1753.0	1753.0
12.5°	1800.7	1795.8	1783.9	1764.8	1750.6	1738.6	1736.2	1741.1	1741.1
15°	1812.6	1807.8	1788.7	1757.7	1736.2	1724.3	1726.7	1731.5	1736.2
17.5°	1812.6	1803.1	1772.1	1731.5	1705.2	1693.3	1702.8	1714.8	1722.0
20°	1783.9	1774.5	1731.5	1681.3	1650.3	1643.2	1660.0	1681.3	1688.6
22.5°	1745.8	1726.7	1676.6	1617.0	1583.6	1583.6	1607.5	1633.7	1643.2
25°	1686.2	1671.8	1614.6	1545.5	1512.1	1509.7	1538.3	1574.1	1583.6
27.5°	1619.3	1600.3	1538.3	1466.7	1431.0	1433.4	1464.4	1500.1	1509.7
30°	1524.0	1500.1	1445.2	1376.1	1342.7	1352.2	1383.2	1409.5	1421.5
32.5°	1416.6	1395.2	1345.1	1280.7	1252.1	1261.6	1287.9	1311.7	1321.2
35°	1304.6	1280.7	1237.7	1180.5	1161.5	1171.0	1194.9	1214.0	1218.8
37.5°	1178.1	1161.5	1130.5	1085.1	1070.9	1082.8	1101.9	1113.8	1118.5
40°	1061.3	1047.0	1020.8	987.4	982.7	992.2	1011.3	1018.4	1020.8
42.5°	946.8	934.9	918.2	894.4	894.4	903.9	920.5	925.4	927.8
45°	837.2	829.9	822.8	803.7	808.5	820.4	829.9	837.2	837.2
47.5°	741.7	744.0	734.6	720.3	725.1	736.9	744.0	751.3	751.3
50°	667.8	660.7	651.1	636.8	643.9	653.4	663.1	667.8	670.2
52.5°	581.9	579.6	572.4	555.7	560.4	565.2	574.8	581.9	584.3
55°	519.9	512.8	503.2	484.2	484.2	489.0	493.7	498.5	503.2
57.5°	460.3	453.1	438.8	417.3	415.0	415.0	412.6	417.3	424.6
60°	400.7	398.3	376.8	357.7	350.6	343.5	333.8	336.2	345.8
62.5°	348.2	343.5	324.3	300.5	286.2	274.2	262.3	260.0	269.5
65°	300.5	295.7	274.2	250.5	233.7	212.2	193.2	193.2	200.4
67.5°	257.6	248.0	229.0	202.7	181.2	155.0	136.0	140.7	143.1
70°	214.6	207.5	186.0	159.7	133.6	107.4	95.4	97.7	97.7
72.5°	176.5	167.0	145.5	119.2	93.0	69.1	64.4	62.0	62.0
75°	138.4	128.7	107.4	81.1	57.2	40.5	35.7	35.7	35.7
77.5°	100.1	93.0	74.0	50.1	31.0	19.1	16.8	14.2	14.2
80°	69.1	62.0	45.4	26.2	11.9	7.1	7.1	7.1	7.1
82.5°	40.5	33.4	21.5	11.9	4.7	2.4	2.4	2.4	2.4
85°	19.1	14.2	9.5	4.7	2.4	2.4	2.4	2.4	2.4
87.5°	2.4	2.4	2.4	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)