

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582602

Luminaire Tested: **HCC6S45D010MB-HM64560835-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010MB-HM64560835-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5129.9 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582602
CATALOG NUMBER: HCC6S45D010MB-HM64560835-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582602

CATALOG NUMBER: HCC6S45D010MB-HM64560835-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	139298	139298	139298
5°	140017	140777	140777
10°	143941	141447	140868
15°	148508	142260	142260
20°	150245	138997	142212
25°	147238	132032	138286
30°	139268	122702	129893
35°	126043	112217	117744
40°	109648	101512	105455
45°	93692	90482	93692
50°	82223	79281	82513
55°	71739	66808	69426
60°	63416	55489	54732
65°	56271	43779	37527
70°	49672	30903	22616
75°	42277	17495	10929
80°	31507	5430	3252
85°	17360	2139	2139



TEST NUMBER: P582602
 CATALOG NUMBER: HCC6S45D010MB-HM64560835-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	4.8
10°-20°	713.1	13.9
20°-30°	1041.5	20.3
30°-40°	1092.3	21.3
40°-50°	920.2	17.9
50°-60°	644.8	12.6
60°-70°	345.7	6.7
70°-80°	115.9	2.3
80°-90°	12.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1998.4	39.0
0°-40°	3090.7	60.2
0°-60°	4655.7	90.8
0°-90°	5129.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5129.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2541	2541	2541	2541	2541	
5°	2544	2555	2558	2558	2558	245
15°	2617	2582	2507	2493	2507	738
25°	2434	2331	2183	2221	2286	1115
35°	1883	1787	1677	1725	1759	1169
45°	1208	1188	1167	1198	1208	941
55°	751	726	699	713	726	676
65°	434	396	338	279	289	433
75°	200	155	83	52	52	212
85°	28	14	3	3	3	38
90°	0	0	0	0	0	



TEST NUMBER: P582602

CATALOG NUMBER: HCC6S45D010MB-HM64560835-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2541.0	2541.0	2541.0	2541.0	2541.0	2541.0	2541.0	2541.0	2541.0
2.5°	2523.7	2523.7	2530.6	2537.6	2544.4	2544.4	2547.9	2551.3	2547.9
5°	2544.4	2544.4	2554.7	2558.2	2558.2	2554.7	2558.2	2558.2	2558.2
7.5°	2575.4	2568.5	2571.9	2565.1	2558.2	2554.7	2551.3	2551.3	2551.3
10°	2585.8	2578.8	2571.9	2558.2	2541.0	2530.6	2527.2	2530.6	2530.6
12.5°	2599.5	2592.6	2575.4	2547.9	2527.2	2510.0	2506.6	2513.4	2513.4
15°	2616.7	2609.8	2582.2	2537.6	2506.6	2489.3	2492.7	2499.7	2506.6
17.5°	2616.7	2602.9	2558.2	2499.7	2461.8	2444.5	2458.4	2475.5	2485.8
20°	2575.4	2561.6	2499.7	2427.3	2382.6	2372.3	2396.3	2427.3	2437.7
22.5°	2520.3	2492.7	2420.5	2334.4	2286.2	2286.2	2320.7	2358.4	2372.3
25°	2434.2	2413.6	2331.0	2231.0	2182.8	2179.4	2220.7	2272.5	2286.2
27.5°	2337.8	2310.2	2220.7	2117.5	2065.8	2069.3	2114.0	2165.7	2179.4
30°	2200.1	2165.7	2086.5	1986.6	1938.4	1952.2	1996.9	2034.8	2052.0
32.5°	2045.1	2014.2	1941.9	1848.9	1807.6	1821.3	1859.2	1893.7	1907.4
35°	1883.4	1848.9	1786.9	1704.3	1676.8	1690.5	1725.0	1752.5	1759.4
37.5°	1700.8	1676.8	1632.0	1566.5	1545.9	1563.1	1590.7	1607.9	1614.8
40°	1532.2	1511.5	1473.6	1425.4	1418.5	1432.4	1459.8	1470.1	1473.6
42.5°	1366.9	1349.7	1325.6	1291.1	1291.1	1305.0	1329.0	1335.9	1339.3
45°	1208.5	1198.2	1187.9	1160.3	1167.1	1184.4	1198.2	1208.5	1208.5
47.5°	1070.8	1074.2	1060.5	1039.7	1046.7	1063.9	1074.2	1084.6	1084.6
50°	964.1	953.8	939.9	919.3	929.6	943.4	957.2	964.1	967.5
52.5°	840.1	836.7	826.4	802.2	809.1	816.1	829.8	840.1	843.5
55°	750.6	740.3	726.4	699.0	699.0	705.8	712.7	719.6	726.4
57.5°	664.5	654.2	633.5	602.6	599.1	599.1	595.6	602.6	612.9
60°	578.4	575.0	544.0	516.5	506.1	495.8	482.0	485.5	499.2
62.5°	502.6	495.8	468.3	433.8	413.1	396.0	378.8	375.2	389.1
65°	433.8	427.0	396.0	361.5	337.5	306.4	278.9	278.9	289.3
67.5°	371.8	358.1	330.6	292.7	261.7	223.8	196.2	203.2	206.6
70°	309.9	299.6	268.5	230.7	192.8	155.0	137.7	141.1	141.1
72.5°	254.8	241.1	210.0	172.2	134.3	99.8	93.0	89.5	89.5
75°	199.6	185.9	155.0	117.1	82.6	58.5	51.6	51.6	51.6
77.5°	144.6	134.3	106.7	72.3	44.8	27.6	24.0	20.6	20.6
80°	99.8	89.5	65.5	37.9	17.2	10.3	10.3	10.3	10.3
82.5°	58.5	48.2	31.0	17.2	6.9	3.4	3.4	3.4	3.4
85°	27.6	20.6	13.7	6.9	3.4	3.4	3.4	3.4	3.4
87.5°	3.4	3.4	3.4	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)