

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582597

Luminaire Tested: **HCC6W45D010BZ-HM64560835-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010BZ-HM64560835-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4754.6 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582597
CATALOG NUMBER: HCC6W45D010BZ-HM64560835-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582597
 CATALOG NUMBER: HCC6W45D010BZ-HM64560835-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52																			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48																			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44																			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176998
5°	176342
10°	173399
15°	170347
20°	164462
25°	155942
30°	141845
35°	113334
40°	75627
45°	53897
50°	44920
55°	39148
60°	36993
65°	34829
70°	31993
75°	29886
80°	27181
85°	23839



TEST NUMBER: P582597
 CATALOG NUMBER: HCC6W45D010BZ-HM64560835-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.1	6.4
10°-20°	842.8	17.7
20°-30°	1177.7	24.8
30°-40°	1037.4	21.8
40°-50°	560.4	11.8
50°-60°	374.7	7.9
60°-70°	265.6	5.6
70°-80°	149.3	3.1
80°-90°	43.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2323.5	48.9
0°-40°	3360.9	70.7
0°-60°	4296.1	90.4
0°-90°	4754.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4754.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3229	
5°	3204	303
15°	3002	843
25°	2578	1178
35°	1694	1037
45°	695	560
55°	410	375
65°	268	266
75°	141	149
85°	38	44
90°	0	



TEST NUMBER: P582597
CATALOG NUMBER: HCC6W45D010BZ-HM64560835-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3228.7
2.5°	3211.4
5°	3204.5
7.5°	3173.6
10°	3115.0
12.5°	3060.0
15°	3001.5
17.5°	2922.3
20°	2819.1
22.5°	2705.4
25°	2578.1
27.5°	2430.1
30°	2240.8
32.5°	2006.8
35°	1693.5
37.5°	1352.7
40°	1056.8
42.5°	832.9
45°	695.2
47.5°	602.3
50°	526.7
52.5°	464.6
55°	409.6
57.5°	371.7
60°	337.4
62.5°	302.9
65°	268.5
67.5°	234.0
70°	199.6
72.5°	168.7
75°	141.1
77.5°	113.5
80°	86.1
82.5°	61.9
85°	37.9
87.5°	17.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)