

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582647

Luminaire Tested: **HCC6S45D010MW-HM64560927-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010MW-HM64560927-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3635.6 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582647
CATALOG NUMBER: HCC6S45D010MW-HM64560927-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P582647

CATALOG NUMBER: HCC6S45D010MW-HM64560927-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	101774	101774	101774
5°	103978	101744	99928
10°	107151	100800	97410
15°	110545	99461	95001
20°	112296	95727	91142
25°	110450	90054	85910
30°	105155	83481	80266
35°	95894	75362	74171
40°	83850	67698	67333
45°	72163	59572	60944
50°	62727	51913	52988
55°	54775	45571	46058
60°	48669	39481	36148
65°	43429	33233	27629
70°	38212	27248	23161
75°	32767	21499	22007
80°	26392	18405	21625
85°	17549	15913	19121



TEST NUMBER: P582647
 CATALOG NUMBER: HCC6S45D010MW-HM64560927-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.8	4.8
10°-20°	500.4	13.8
20°-30°	714.3	19.6
30°-40°	748.2	20.6
40°-50°	630.0	17.3
50°-60°	448.4	12.3
60°-70°	262.5	7.2
70°-80°	124.2	3.4
80°-90°	32.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.5	38.2
0°-40°	2138.7	58.8
0°-60°	3217.0	88.5
0°-90°	3635.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3635.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1856	1856	1856	1856	1856	
5°	1890	1874	1849	1823	1816	182
15°	1948	1877	1752	1682	1674	550
25°	1826	1697	1489	1418	1420	836
35°	1433	1314	1126	1088	1108	890
45°	931	862	768	771	786	723
55°	573	525	477	477	482	517
65°	335	297	256	216	213	334
75°	155	129	102	99	104	166
85°	28	23	25	30	30	36
90°	0	0	0	0	0	



TEST NUMBER: P582647

CATALOG NUMBER: HCC6S45D010MW-HM64560927-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1856.5	1856.5	1856.5	1856.5	1856.5	1856.5	1856.5	1856.5	1856.5
2.5°	1859.0	1859.0	1856.5	1853.9	1848.9	1841.3	1836.2	1831.1	1831.1
5°	1889.5	1884.3	1874.2	1861.6	1848.9	1833.6	1823.4	1815.9	1815.9
7.5°	1914.8	1904.6	1884.3	1861.6	1838.7	1818.4	1800.7	1790.5	1788.0
10°	1924.9	1912.2	1881.8	1846.3	1810.8	1783.0	1762.7	1749.9	1749.9
12.5°	1935.1	1919.8	1879.3	1828.6	1783.0	1744.8	1724.5	1714.5	1711.9
15°	1947.8	1927.5	1876.8	1813.3	1752.5	1709.4	1681.5	1673.9	1673.9
17.5°	1947.8	1922.4	1859.0	1780.4	1704.3	1656.0	1630.7	1623.1	1625.7
20°	1924.9	1897.0	1821.0	1724.5	1640.9	1590.1	1564.8	1559.7	1562.3
22.5°	1881.8	1848.9	1762.7	1658.6	1567.4	1514.1	1491.2	1491.2	1488.8
25°	1826.0	1790.5	1696.6	1587.7	1488.8	1435.4	1417.7	1420.3	1420.3
27.5°	1752.5	1716.9	1623.1	1506.5	1407.6	1354.3	1341.6	1346.7	1349.2
30°	1661.2	1623.1	1524.2	1410.1	1318.8	1265.5	1257.9	1265.5	1268.0
32.5°	1549.5	1521.7	1425.3	1308.6	1222.4	1176.8	1174.3	1181.8	1192.0
35°	1432.9	1402.4	1313.8	1207.3	1126.1	1088.0	1088.0	1100.6	1108.3
37.5°	1306.1	1275.6	1194.5	1105.8	1037.3	1001.7	1006.9	1019.6	1022.0
40°	1171.7	1148.8	1080.5	1004.3	946.0	918.1	925.7	938.4	940.9
42.5°	1044.9	1024.6	968.8	900.3	857.2	836.9	847.0	862.3	867.3
45°	930.8	907.9	862.3	804.0	768.4	758.3	771.0	781.1	786.1
47.5°	826.7	806.4	768.4	715.2	689.8	684.8	697.5	702.5	707.6
50°	735.5	715.2	677.2	629.0	608.7	608.7	618.9	623.9	621.3
52.5°	646.7	629.0	593.4	552.8	540.2	540.2	547.8	550.4	555.4
55°	573.1	555.4	525.0	486.9	476.8	471.7	476.8	476.8	481.9
57.5°	504.7	489.5	461.6	426.0	413.4	408.3	405.7	403.3	408.3
60°	443.9	431.2	400.7	370.3	360.1	347.4	337.4	327.1	329.7
62.5°	388.0	375.4	347.4	317.1	306.9	289.1	276.5	263.8	268.9
65°	334.8	322.1	296.8	271.3	256.2	235.9	215.6	208.0	213.0
67.5°	286.6	276.5	251.0	225.7	213.0	190.3	170.0	170.0	172.4
70°	238.4	228.3	208.0	185.1	170.0	149.7	142.1	144.5	144.5
72.5°	195.3	187.7	167.4	147.1	131.8	119.2	119.2	121.8	124.2
75°	154.7	149.7	129.4	111.6	101.5	93.8	98.9	101.5	103.9
77.5°	119.2	111.6	96.4	83.6	76.1	78.6	83.6	86.2	88.8
80°	83.6	81.2	68.5	60.9	58.3	60.9	65.9	68.5	68.5
82.5°	53.3	50.7	43.2	40.6	40.6	43.2	48.2	48.2	48.2
85°	27.9	25.3	22.9	22.9	25.3	27.9	30.4	30.4	30.4
87.5°	10.1	7.6	10.1	10.1	12.7	12.7	12.7	12.7	12.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)