

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582633

Luminaire Tested: **HCC6S45D010SL-HM64560927-61MDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582633  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S45D010SL-HM64560927-61MDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3503.7 lumens  
Efficiency: N/A  
Efficacy: 79.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582633  
CATALOG NUMBER: HCC6S45D010SL-HM64560927-61MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582633

CATALOG NUMBER: HCC6S45D010SL-HM64560927-61MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79				79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70				70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63				63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57				57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48				48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44				44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40				40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37				37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	130428
5°	129952
10°	127775
15°	125529
20°	121192
25°	114914
30°	104522
35°	83520
40°	55719
45°	39725
50°	33091
55°	28845
60°	27257
65°	25671
70°	23578
75°	22028
80°	20047
85°	17549



TEST NUMBER: P582633

CATALOG NUMBER: HCC6S45D010SL-HM64560927-61MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.3	6.4
10°-20°	621.0	17.7
20°-30°	867.8	24.8
30°-40°	764.5	21.8
40°-50°	413.0	11.8
50°-60°	276.1	7.9
60°-70°	195.7	5.6
70°-80°	110.1	3.1
80°-90°	32.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1712.2	48.9
0°-40°	2476.6	70.7
0°-60°	3165.8	90.4
0°-90°	3503.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3503.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2379	
5°	2362	223
15°	2212	621
25°	1900	868
35°	1248	764
45°	512	413
55°	302	276
65°	198	196
75°	104	110
85°	28	32
90°	0	



TEST NUMBER: P582633  
CATALOG NUMBER: HCC6S45D010SL-HM64560927-61MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2379.2
2.5°	2366.5
5°	2361.5
7.5°	2338.6
10°	2295.4
12.5°	2254.9
15°	2211.8
17.5°	2153.4
20°	2077.4
22.5°	1993.6
25°	1899.8
27.5°	1790.7
30°	1651.2
32.5°	1478.8
35°	1248.0
37.5°	996.8
40°	778.6
42.5°	613.8
45°	512.4
47.5°	443.9
50°	388.0
52.5°	342.4
55°	301.8
57.5°	273.9
60°	248.6
62.5°	223.2
65°	197.9
67.5°	172.4
70°	147.1
72.5°	124.3
75°	104.0
77.5°	83.8
80°	63.5
82.5°	45.6
85°	27.9
87.5°	12.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)