

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582531

Luminaire Tested: **HCC6S40D010MB-HM63040935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010MB-HM63040935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4199.1 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582531
CATALOG NUMBER: HCC6S40D010MB-HM63040935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582531

CATALOG NUMBER: HCC6S40D010MB-HM63040935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	117480	117480	117480
5°	118699	117615	116844
10°	120383	117255	116008
15°	123219	116516	115404
20°	124366	113054	113381
25°	121634	107365	109403
30°	115208	99731	103117
35°	104320	91156	94536
40°	90849	82404	85424
45°	77086	72938	75558
50°	68271	63716	65388
55°	60136	54497	54220
60°	53888	45884	42190
65°	48099	36800	30237
70°	42331	26559	18897
75°	35711	16055	10696
80°	27497	7072	4420
85°	15913	1761	1761



TEST NUMBER: P582531
 CATALOG NUMBER: HCC6S40D010MB-HM63040935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.4	4.8
10°-20°	584.6	13.9
20°-30°	845.1	20.1
30°-40°	889.2	21.2
40°-50°	747.5	17.8
50°-60°	524.7	12.5
60°-70°	288.6	6.9
70°-80°	102.5	2.4
80°-90°	13.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1633.1	38.9
0°-40°	2522.4	60.1
0°-60°	3794.6	90.4
0°-90°	4199.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4199.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2143	2143	2143	2143	2143	
5°	2157	2151	2137	2129	2123	206
15°	2171	2134	2053	2028	2033	613
25°	2011	1910	1775	1778	1809	920
35°	1559	1469	1362	1390	1413	966
45°	994	966	941	963	975	780
55°	629	595	570	570	567	566
65°	371	332	284	233	233	369
75°	169	135	76	50	50	181
85°	25	14	3	3	3	35
90°	0	0	0	0	0	



TEST NUMBER: P582531

CATALOG NUMBER: HCC6S40D010MB-HM63040935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2143.0	2143.0	2143.0	2143.0	2143.0	2143.0	2143.0	2143.0	2143.0
2.5°	2143.0	2143.0	2140.1	2140.1	2134.5	2134.5	2131.8	2131.8	2131.8
5°	2157.0	2157.0	2151.4	2143.0	2137.3	2128.9	2128.9	2126.1	2123.3
7.5°	2165.4	2162.6	2154.2	2143.0	2128.9	2114.9	2109.2	2112.0	2109.2
10°	2162.6	2157.0	2145.7	2123.3	2106.4	2086.8	2084.0	2081.1	2084.0
12.5°	2168.2	2159.7	2137.3	2109.2	2081.1	2058.7	2055.9	2055.9	2058.7
15°	2171.1	2162.6	2134.5	2092.3	2053.0	2030.6	2027.8	2030.6	2033.4
17.5°	2162.6	2151.4	2109.2	2053.0	2008.2	1985.6	1985.6	1991.3	1996.8
20°	2131.8	2114.9	2055.9	1988.5	1937.9	1921.1	1926.7	1937.9	1943.5
22.5°	2075.6	2055.9	1988.5	1912.7	1859.3	1845.3	1859.3	1873.4	1878.9
25°	2010.9	1988.5	1909.8	1831.2	1775.0	1758.2	1777.9	1800.3	1808.7
27.5°	1923.9	1898.6	1825.6	1735.7	1679.5	1671.0	1693.6	1718.8	1724.5
30°	1820.0	1791.9	1710.5	1626.2	1575.5	1572.8	1598.1	1620.5	1629.0
32.5°	1693.6	1668.3	1598.1	1513.8	1468.8	1468.8	1494.2	1513.8	1522.3
35°	1558.8	1530.7	1468.8	1398.7	1362.1	1364.9	1390.2	1404.3	1412.6
37.5°	1398.7	1390.2	1342.5	1283.5	1258.2	1263.9	1283.5	1294.7	1303.2
40°	1269.5	1247.0	1216.1	1168.4	1151.5	1157.2	1176.8	1188.0	1193.7
42.5°	1129.1	1115.0	1089.8	1056.0	1044.8	1053.2	1070.1	1078.5	1075.6
45°	994.3	991.4	966.2	946.5	940.8	952.1	963.4	971.7	974.6
47.5°	896.0	884.7	862.2	848.2	842.6	853.8	865.0	870.7	870.7
50°	800.5	789.2	766.7	752.8	747.1	758.3	766.7	772.4	766.7
52.5°	705.0	693.7	674.0	657.3	654.4	660.0	662.8	665.6	671.2
55°	629.2	617.8	595.4	575.7	570.2	573.0	570.2	570.2	567.3
57.5°	556.1	544.9	522.5	499.9	491.5	488.7	480.2	477.5	474.7
60°	491.5	477.5	454.9	429.7	418.5	407.3	393.2	384.8	384.8
62.5°	429.7	415.6	390.4	367.9	351.1	331.5	308.9	297.7	297.7
65°	370.8	359.6	331.5	306.1	283.7	258.4	233.1	227.5	233.1
67.5°	314.6	303.4	275.3	250.0	221.9	191.0	168.6	168.6	174.1
70°	264.1	252.7	227.5	196.7	165.7	134.8	117.9	117.9	117.9
72.5°	216.3	205.0	176.9	148.9	117.9	87.1	78.6	81.5	78.6
75°	168.6	160.1	134.8	103.9	75.8	53.4	50.5	47.7	50.5
77.5°	126.4	117.9	95.5	67.4	42.1	30.9	28.1	28.1	28.1
80°	87.1	78.6	61.7	39.3	22.4	14.0	14.0	14.0	14.0
82.5°	53.4	45.0	33.8	19.7	8.4	8.4	8.4	8.4	8.4
85°	25.3	19.7	14.0	5.7	2.8	2.8	2.8	2.8	2.8
87.5°	5.7	5.7	2.8	2.8	0.0	2.8	2.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)