

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582643

Luminaire Tested: **HCC6S45D010SL-HM64560927-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560927-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3704.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582643
CATALOG NUMBER: HCC6S45D010SL-HM64560927-61WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582643

CATALOG NUMBER: HCC6S45D010SL-HM64560927-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51																			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126404
5°	126331
10°	125109
15°	123803
20°	120311
25°	115228
30°	106941
35°	92013
40°	67162
45°	46013
50°	36997
55°	32247
60°	29756
65°	28304
70°	26431
75°	24718
80°	22414
85°	19121



TEST NUMBER: P582643
 CATALOG NUMBER: HCC6S45D010SL-HM64560927-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.6	5.9
10°-20°	612.7	16.5
20°-30°	871.3	23.5
30°-40°	838.9	22.6
40°-50°	482.6	13.0
50°-60°	305.8	8.3
60°-70°	216.5	5.8
70°-80°	123.4	3.3
80°-90°	35.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1701.6	45.9
0°-40°	2540.5	68.6
0°-60°	3329.0	89.9
0°-90°	3704.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3704.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2306	
5°	2296	218
15°	2181	613
25°	1905	871
35°	1375	839
45°	594	483
55°	337	306
65°	218	216
75°	117	123
85°	30	35
90°	0	



TEST NUMBER: P582643
CATALOG NUMBER: HCC6S45D010SL-HM64560927-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2305.8
2.5°	2295.7
5°	2295.7
7.5°	2280.4
10°	2247.5
12.5°	2214.5
15°	2181.4
17.5°	2130.8
20°	2062.3
22.5°	1986.1
25°	1905.0
27.5°	1806.1
30°	1689.4
32.5°	1547.3
35°	1374.9
37.5°	1164.3
40°	938.5
42.5°	740.6
45°	593.5
47.5°	499.7
50°	433.8
52.5°	380.5
55°	337.4
57.5°	299.3
60°	271.4
62.5°	246.1
65°	218.2
67.5°	192.7
70°	164.9
72.5°	139.5
75°	116.7
77.5°	93.8
80°	71.0
82.5°	50.7
85°	30.4
87.5°	12.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)