

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582657

Luminaire Tested: **HCC6W45D010MB-HM64560930-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MB-HM64560930-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4531.3 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582657
CATALOG NUMBER: HCC6W45D010MB-HM64560930-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P582657

CATALOG NUMBER: HCC6W45D010MB-HM64560930-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	126777	126777	126777
5°	128092	126926	126089
10°	129907	126540	125187
15°	132963	125744	124535
20°	134202	121997	122353
25°	131258	115864	118065
30°	124323	107630	111277
35°	112571	98377	102024
40°	98034	88931	92180
45°	83179	78714	81536
50°	73669	68757	70565
55°	64887	58798	58512
60°	58153	49514	45523
65°	51899	39719	32636
70°	45665	28659	20404
75°	38507	17347	11544
80°	29675	7671	4767
85°	17171	1887	1887



TEST NUMBER: P582657
 CATALOG NUMBER: HCC6W45D010MB-HM64560930-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.5	4.8
10°-20°	630.9	13.9
20°-30°	912.0	20.1
30°-40°	959.6	21.2
40°-50°	806.7	17.8
50°-60°	566.2	12.5
60°-70°	311.5	6.9
70°-80°	110.6	2.4
80°-90°	14.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1762.4	38.9
0°-40°	2722.0	60.1
0°-60°	4094.8	90.4
0°-90°	4531.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4531.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2313	2313	2313	2313	2313	
5°	2328	2322	2306	2297	2291	222
15°	2343	2303	2216	2188	2194	661
25°	2170	2061	1916	1919	1952	993
35°	1682	1585	1470	1500	1524	1043
45°	1073	1043	1015	1040	1052	842
55°	679	643	615	615	612	611
65°	400	358	306	252	252	398
75°	182	146	82	54	54	195
85°	27	15	3	3	3	38
90°	0	0	0	0	0	



TEST NUMBER: P582657

CATALOG NUMBER: HCC6W45D010MB-HM64560930-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2312.6	2312.6	2312.6	2312.6	2312.6	2312.6	2312.6	2312.6	2312.6
2.5°	2312.6	2312.6	2309.5	2309.5	2303.4	2303.4	2300.4	2300.4	2300.4
5°	2327.7	2327.7	2321.6	2312.6	2306.5	2297.3	2297.3	2294.4	2291.3
7.5°	2336.7	2333.7	2324.7	2312.6	2297.3	2282.2	2276.2	2279.1	2276.2
10°	2333.7	2327.7	2315.5	2291.3	2273.2	2251.9	2248.9	2245.8	2248.9
12.5°	2339.8	2330.8	2306.5	2276.2	2245.8	2221.5	2218.6	2218.6	2221.5
15°	2342.8	2333.7	2303.4	2258.0	2215.6	2191.3	2188.2	2191.3	2194.3
17.5°	2333.7	2321.6	2276.2	2215.6	2167.0	2142.8	2142.8	2148.8	2154.9
20°	2300.4	2282.2	2218.6	2145.9	2091.2	2073.0	2079.1	2091.2	2097.3
22.5°	2239.7	2218.6	2145.9	2064.0	2006.4	1991.3	2006.4	2021.5	2027.6
25°	2170.0	2145.9	2061.0	1976.2	1915.5	1897.3	1918.6	1942.7	1951.9
27.5°	2076.1	2048.9	1970.1	1873.0	1812.4	1803.4	1827.5	1854.9	1861.0
30°	1964.0	1933.7	1845.8	1754.8	1700.3	1697.2	1724.5	1748.8	1757.9
32.5°	1827.5	1800.3	1724.5	1633.6	1585.1	1585.1	1612.4	1633.6	1642.7
35°	1682.1	1651.8	1585.1	1509.3	1470.0	1472.9	1500.3	1515.4	1524.5
37.5°	1509.3	1500.3	1448.8	1385.1	1357.9	1363.8	1385.1	1397.2	1406.3
40°	1369.9	1345.7	1312.4	1260.9	1242.7	1248.7	1269.9	1282.1	1288.1
42.5°	1218.4	1203.3	1175.9	1139.6	1127.5	1136.5	1154.7	1163.9	1160.8
45°	1072.9	1069.9	1042.6	1021.4	1015.3	1027.4	1039.6	1048.7	1051.7
47.5°	966.8	954.7	930.4	915.3	909.2	921.4	933.5	939.6	939.6
50°	863.8	851.7	827.4	812.3	806.2	818.3	827.4	833.5	827.4
52.5°	760.7	748.6	727.4	709.2	706.1	712.2	715.3	718.3	724.3
55°	678.9	666.7	642.6	621.3	615.2	618.3	615.2	615.2	612.2
57.5°	600.1	588.0	563.7	539.5	530.4	527.4	518.2	515.3	512.2
60°	530.4	515.3	491.0	463.7	451.6	439.5	424.3	415.2	415.2
62.5°	463.7	448.6	421.3	397.1	378.9	357.6	333.4	321.3	321.3
65°	400.1	387.9	357.6	330.3	306.2	278.8	251.6	245.5	251.6
67.5°	339.5	327.4	297.0	269.8	239.4	206.1	181.8	181.8	187.9
70°	284.9	272.7	245.5	212.2	178.8	145.5	127.3	127.3	127.3
72.5°	233.4	221.2	191.0	160.6	127.3	94.0	84.8	87.9	84.8
75°	181.8	172.8	145.5	112.1	81.9	57.6	54.5	51.5	54.5
77.5°	136.4	127.3	103.1	72.7	45.5	33.3	30.3	30.3	30.3
80°	94.0	84.8	66.6	42.5	24.3	15.1	15.1	15.1	15.1
82.5°	57.6	48.4	36.4	21.2	9.1	9.1	9.1	9.1	9.1
85°	27.3	21.2	15.1	6.1	3.0	3.0	3.0	3.0	3.0
87.5°	6.1	6.1	3.0	3.0	0.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)