

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582663

Luminaire Tested: **HCC6W45D010MB-HM64560930-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MB-HM64560930-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3840.2 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582663
CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P582663
 CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78		
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69		
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37		
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	118137	118137	118137
5°	120421	117917	115254
10°	124513	116414	111527
15°	128327	114393	108026
20°	130322	109624	102378
25°	127967	102115	95328
30°	121639	93052	87488
35°	109326	83165	78902
40°	94355	72879	70496
45°	79892	62743	61092
50°	68501	52988	52467
55°	59381	44605	42875
60°	51838	36214	30568
65°	45595	27915	16902
70°	39350	18465	8255
75°	33402	9002	3198
80°	25856	3820	1926
85°	15284	1887	1887



TEST NUMBER: P582663
 CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.4	5.3
10°-20°	575.1	15.0
20°-30°	809.8	21.1
30°-40°	827.4	21.5
40°-50°	667.1	17.4
50°-60°	447.5	11.7
60°-70°	226.4	5.9
70°-80°	72.4	1.9
80°-90°	11.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1588.3	41.4
0°-40°	2415.7	62.9
0°-60°	3530.3	91.9
0°-90°	3840.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3840.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2155	2155	2155	2155	2155	
5°	2188	2173	2143	2110	2094	211
15°	2261	2170	2016	1925	1903	638
25°	2116	1949	1688	1585	1576	969
35°	1634	1485	1243	1173	1179	1017
45°	1030	949	809	782	788	801
55°	621	552	467	446	449	559
65°	352	291	215	142	130	351
75°	158	112	42	15	15	169
85°	24	12	3	3	3	33
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582663

CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0	2155.0
2.5°	2164.1	2161.0	2158.1	2152.0	2142.8	2133.8	2127.7	2121.6	2118.7
5°	2188.3	2182.2	2173.2	2161.0	2142.8	2121.6	2109.5	2097.4	2094.4
7.5°	2221.7	2209.6	2185.3	2158.1	2127.7	2097.4	2076.2	2064.1	2055.0
10°	2236.8	2215.6	2182.2	2136.9	2091.3	2055.0	2027.6	2009.5	2003.5
12.5°	2249.0	2224.7	2176.3	2115.6	2055.0	2006.5	1976.2	1961.0	1954.9
15°	2261.1	2236.8	2170.2	2091.3	2015.6	1958.0	1924.7	1909.5	1903.4
17.5°	2261.1	2227.8	2148.9	2048.9	1958.0	1888.3	1855.0	1839.7	1836.8
20°	2233.9	2197.4	2100.5	1982.3	1879.1	1800.4	1770.1	1761.0	1754.9
22.5°	2182.2	2139.8	2030.7	1897.3	1785.2	1709.4	1676.1	1670.0	1664.0
25°	2115.6	2073.2	1948.9	1806.4	1688.2	1612.4	1585.2	1579.1	1576.0
27.5°	2030.7	1985.3	1855.0	1709.4	1582.1	1509.4	1485.1	1485.1	1482.1
30°	1921.6	1870.1	1742.8	1597.3	1470.0	1403.4	1385.2	1385.2	1382.1
32.5°	1788.2	1736.7	1621.6	1482.1	1360.9	1291.2	1276.0	1282.1	1279.0
35°	1633.6	1591.3	1485.1	1348.7	1242.7	1179.0	1173.0	1179.0	1179.0
37.5°	1479.2	1439.7	1348.7	1230.6	1130.5	1072.9	1072.9	1082.1	1079.0
40°	1318.5	1288.2	1203.3	1100.3	1018.4	979.0	972.9	982.0	985.1
42.5°	1166.9	1142.6	1069.9	985.1	912.4	872.9	882.0	888.1	891.1
45°	1030.5	1006.3	948.7	860.7	809.3	782.0	782.0	791.1	788.0
47.5°	909.3	891.1	833.5	748.6	703.2	691.0	697.1	703.2	703.2
50°	803.2	775.9	721.4	654.7	621.3	606.2	612.3	615.2	615.2
52.5°	703.2	685.0	630.5	569.8	539.5	530.4	530.4	533.5	533.5
55°	621.3	600.1	551.7	491.0	466.7	454.7	445.5	442.6	448.6
57.5°	542.5	524.3	478.9	421.3	394.0	381.9	363.7	357.6	363.7
60°	472.8	457.7	412.2	357.6	330.3	306.2	284.9	272.8	278.8
62.5°	412.2	394.0	348.6	303.1	272.8	245.5	212.2	194.0	203.0
65°	351.5	336.4	291.0	245.5	215.2	181.8	142.4	130.3	130.3
67.5°	297.0	281.9	239.4	200.0	163.6	124.2	87.9	84.8	87.9
70°	245.5	230.4	194.0	154.6	115.2	75.8	51.5	51.5	51.5
72.5°	203.0	184.9	151.6	112.1	72.7	39.4	27.3	30.3	30.3
75°	157.7	142.4	112.1	75.8	42.5	18.2	15.1	15.1	15.1
77.5°	118.2	106.0	78.8	48.4	21.2	6.1	6.1	6.1	6.1
80°	81.9	69.7	51.5	30.3	12.1	6.1	6.1	6.1	6.1
82.5°	48.4	42.5	30.3	15.1	6.1	3.0	3.0	3.0	3.0
85°	24.3	21.2	12.1	6.1	3.0	3.0	3.0	3.0	3.0
87.5°	6.1	6.1	3.0	3.0	0.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)