

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582662

Luminaire Tested: **HCC6W45D010MB-HM64560930-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582662  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W45D010MB-HM64560930-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4767.8 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582662  
CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WDWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582662

CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	177820
5°	179336
10°	185802
15°	201812
20°	209925
25°	200794
30°	173280
35°	124771
40°	70296
45°	36430
50°	21722
55°	15655
60°	13299
65°	15332
70°	19442
75°	20545
80°	20110
85°	19058



TEST NUMBER: P582662  
 CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	313.6	6.6
10°-20°	1002.9	21.0
20°-30°	1499.1	31.4
30°-40°	1145.9	24.0
40°-50°	400.3	8.4
50°-60°	152.6	3.2
60°-70°	119.6	2.5
70°-80°	101.2	2.1
80°-90°	32.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2815.6	59.1
0°-40°	3961.6	83.1
0°-60°	4514.4	94.7
0°-90°	4767.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4767.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3244	
5°	3259	314
15°	3556	1003
25°	3320	1499
35°	1864	1146
45°	470	400
55°	164	153
65°	118	120
75°	97	101
85°	30	33
90°	0	



TEST NUMBER: P582662  
CATALOG NUMBER: HCC6W45D010MB-HM64560930-61WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3243.7
2.5°	3234.7
5°	3258.9
7.5°	3292.3
10°	3337.8
12.5°	3440.8
15°	3555.9
17.5°	3625.7
20°	3598.4
22.5°	3489.3
25°	3319.6
27.5°	3077.0
30°	2737.4
32.5°	2331.2
35°	1864.4
37.5°	1382.4
40°	982.3
42.5°	688.2
45°	469.9
47.5°	330.4
50°	254.7
52.5°	200.1
55°	163.8
57.5°	133.4
60°	121.3
62.5°	118.2
65°	118.2
67.5°	124.3
70°	121.3
72.5°	112.1
75°	97.0
77.5°	81.9
80°	63.7
82.5°	45.5
85°	30.3
87.5°	12.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)