

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582682

Luminaire Tested: **HCC6S45D010SL-HM64560935-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582682
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560935-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4244.2 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582682
CATALOG NUMBER: HCC6S45D010SL-HM64560935-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582682

CATALOG NUMBER: HCC6S45D010SL-HM64560935-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	124902	124902	124902
5°	130442	124537	118798
10°	133999	122393	111638
15°	137311	119740	104598
20°	137929	114314	96072
25°	135038	107026	88106
30°	128115	98414	80747
35°	116359	88446	72438
40°	101383	78783	65172
45°	87730	68945	57293
50°	76629	59367	50207
55°	67706	52165	43086
60°	60861	45720	37322
65°	54506	39771	36204
70°	48662	33916	33916
75°	42214	28573	31835
80°	33874	24214	29044
85°	23147	21260	25097



TEST NUMBER: P582682
 CATALOG NUMBER: HCC6S45D010SL-HM64560935-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.1	5.0
10°-20°	595.2	14.0
20°-30°	829.6	19.5
30°-40°	854.7	20.1
40°-50°	708.4	16.7
50°-60°	509.1	12.0
60°-70°	324.2	7.6
70°-80°	166.5	3.9
80°-90°	42.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1638.9	38.6
0°-40°	2493.7	58.8
0°-60°	3711.1	87.4
0°-90°	4244.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4244.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2278	2278	2278	2278	2278	
5°	2370	2334	2263	2190	2159	227
15°	2419	2328	2110	1917	1843	682
25°	2232	2079	1769	1542	1457	1023
35°	1739	1598	1322	1147	1082	1080
45°	1132	1052	889	776	739	876
55°	708	650	546	485	451	638
65°	420	374	307	267	279	421
75°	199	172	135	141	150	213
85°	37	34	34	37	40	47
90°	0	0	0	0	0	



TEST NUMBER: P582682

CATALOG NUMBER: HCC6S45D010SL-HM64560935-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2278.4	2278.4	2278.4	2278.4	2278.4	2278.4	2278.4	2278.4	2278.4
2.5°	2321.4	2312.1	2299.9	2287.6	2269.2	2247.7	2229.4	2223.2	2214.0
5°	2370.4	2358.2	2333.6	2303.0	2263.1	2223.2	2189.5	2168.1	2158.8
7.5°	2401.1	2385.8	2352.0	2299.9	2241.6	2183.3	2134.3	2103.7	2091.3
10°	2407.2	2391.9	2345.9	2275.4	2198.7	2118.9	2057.7	2020.8	2005.5
12.5°	2416.4	2394.9	2336.7	2253.9	2155.7	2063.8	1987.1	1941.1	1925.8
15°	2419.4	2394.9	2327.5	2226.2	2109.8	1999.4	1916.6	1861.4	1843.0
17.5°	2407.2	2379.7	2299.9	2177.2	2045.4	1928.9	1830.7	1772.4	1747.9
20°	2364.3	2333.6	2241.6	2103.7	1959.5	1836.8	1735.7	1674.3	1646.8
22.5°	2309.1	2269.2	2165.0	2017.8	1867.5	1738.7	1637.5	1576.2	1548.6
25°	2232.5	2195.6	2079.1	1922.7	1769.4	1634.5	1542.5	1478.1	1456.6
27.5°	2143.5	2100.6	1981.0	1824.6	1668.2	1533.2	1444.3	1386.0	1358.5
30°	2023.9	1984.0	1864.5	1708.0	1554.7	1428.9	1337.0	1288.0	1275.6
32.5°	1882.9	1849.1	1732.6	1585.4	1438.2	1321.6	1245.0	1192.8	1180.6
35°	1738.7	1698.9	1597.6	1459.7	1321.6	1217.5	1146.8	1100.9	1082.4
37.5°	1582.4	1545.5	1459.7	1337.0	1214.3	1116.2	1054.9	1015.0	996.6
40°	1416.7	1389.2	1309.4	1211.2	1100.9	1015.0	962.9	929.1	910.7
42.5°	1263.4	1235.8	1180.6	1088.7	996.6	920.0	874.0	843.3	827.9
45°	1131.6	1107.0	1051.8	972.1	889.3	824.9	775.8	754.4	739.0
47.5°	999.6	987.4	938.4	864.7	788.1	732.9	699.1	674.6	662.4
50°	898.5	883.2	837.2	760.5	696.1	653.1	622.5	601.0	588.7
52.5°	794.2	778.9	735.9	671.5	619.5	579.6	549.0	530.5	518.2
55°	708.4	696.1	650.1	591.9	545.8	512.1	484.6	463.1	450.8
57.5°	628.6	616.4	573.5	518.2	478.3	447.7	423.2	404.8	389.4
60°	555.1	545.8	502.9	450.8	417.0	386.4	364.9	349.6	340.4
62.5°	490.7	472.2	435.4	389.4	358.8	334.3	312.8	303.6	309.7
65°	420.2	410.9	374.1	334.3	306.6	282.1	266.7	273.0	279.1
67.5°	361.9	349.6	318.9	282.1	257.6	239.2	230.0	242.2	245.3
70°	303.6	291.4	263.7	233.1	211.6	199.3	199.3	208.6	211.6
72.5°	248.4	239.2	214.7	190.1	174.8	165.6	171.7	177.8	180.9
75°	199.3	190.1	171.7	150.3	134.9	134.9	141.1	147.2	150.3
77.5°	153.3	147.2	128.8	113.4	107.3	107.3	113.4	116.5	119.6
80°	107.3	101.2	92.0	82.8	76.7	82.8	88.9	88.9	92.0
82.5°	70.5	67.4	61.3	55.2	55.2	58.3	61.3	64.4	64.4
85°	36.8	36.8	33.8	30.6	33.8	36.8	36.8	39.9	39.9
87.5°	12.3	12.3	12.3	12.3	15.4	15.4	15.4	15.4	15.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)