

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582574

Luminaire Tested: **HCC6W45D010BZ-HM64560827-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010BZ-HM64560827-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4222.7 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582574
CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582574

CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	124272	124272	124272
5°	129782	123910	118198
10°	133320	121775	111076
15°	136618	119132	104064
20°	137229	113737	95582
25°	134355	106482	87658
30°	127469	97914	80341
35°	115770	88011	72076
40°	100875	78383	64843
45°	87280	68596	57014
50°	76236	59060	49960
55°	67352	51907	42875
60°	60543	45490	37124
65°	54208	39576	36009
70°	48406	33756	33756
75°	42023	28425	31687
80°	33685	24056	28886
85°	23021	21071	24908



TEST NUMBER: P582574
 CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.1	5.0
10°-20°	592.2	14.0
20°-30°	825.4	19.5
30°-40°	850.4	20.1
40°-50°	704.8	16.7
50°-60°	506.5	12.0
60°-70°	322.6	7.6
70°-80°	165.6	3.9
80°-90°	42.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1630.7	38.6
0°-40°	2481.1	58.8
0°-60°	3692.4	87.4
0°-90°	4222.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4222.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2267	2267	2267	2267	2267	
5°	2358	2322	2252	2178	2148	226
15°	2407	2316	2099	1907	1834	678
25°	2221	2069	1760	1535	1449	1018
35°	1730	1590	1315	1141	1077	1075
45°	1126	1047	885	772	735	871
55°	705	647	543	482	449	635
65°	418	372	305	265	278	419
75°	198	171	134	140	150	212
85°	37	34	34	37	40	47
90°	0	0	0	0	0	



TEST NUMBER: P582574

CATALOG NUMBER: HCC6W45D010BZ-HM64560827-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2266.9	2266.9	2266.9	2266.9	2266.9	2266.9	2266.9	2266.9	2266.9
2.5°	2309.6	2300.5	2288.3	2276.1	2257.8	2236.4	2218.1	2212.0	2202.9
5°	2358.4	2346.2	2321.8	2291.3	2251.7	2212.0	2178.5	2157.0	2147.9
7.5°	2388.9	2373.7	2340.1	2288.3	2230.3	2172.4	2123.5	2093.0	2080.8
10°	2395.0	2379.8	2334.0	2263.9	2187.6	2108.2	2047.2	2010.6	1995.4
12.5°	2404.2	2382.8	2324.9	2242.5	2144.8	2053.3	1977.1	1931.3	1916.1
15°	2407.2	2382.8	2315.7	2215.1	2099.1	1989.3	1906.9	1851.9	1833.6
17.5°	2395.0	2367.6	2288.3	2166.2	2035.0	1919.1	1821.4	1763.5	1739.1
20°	2352.3	2321.8	2230.3	2093.0	1949.6	1827.5	1726.9	1665.9	1638.4
22.5°	2297.4	2257.8	2154.0	2007.6	1858.0	1729.9	1629.3	1568.2	1540.7
25°	2221.2	2184.6	2068.6	1913.0	1760.4	1626.2	1534.6	1470.6	1449.2
27.5°	2132.6	2089.9	1971.0	1815.3	1659.8	1525.5	1437.0	1379.1	1351.6
30°	2013.7	1974.0	1855.0	1699.4	1546.8	1421.8	1330.3	1281.4	1269.2
32.5°	1873.3	1839.7	1723.8	1577.3	1430.9	1315.1	1238.7	1186.8	1174.6
35°	1729.9	1690.3	1589.5	1452.3	1315.1	1211.2	1141.1	1095.3	1077.0
37.5°	1574.3	1537.7	1452.3	1330.3	1208.2	1110.6	1049.6	1009.8	991.5
40°	1409.6	1382.1	1302.9	1205.1	1095.3	1009.8	958.0	924.4	906.1
42.5°	1257.0	1229.5	1174.6	1083.1	991.5	915.3	869.5	839.0	823.8
45°	1125.8	1101.4	1046.6	967.1	884.8	820.7	772.0	750.6	735.4
47.5°	994.6	982.4	933.6	860.4	784.2	729.3	695.6	671.2	659.0
50°	893.9	878.7	832.9	756.7	692.5	649.8	619.3	598.0	585.8
52.5°	790.3	775.0	732.3	668.1	616.3	576.6	546.1	527.8	515.7
55°	704.7	692.5	646.8	588.8	543.1	509.6	482.1	460.8	448.6
57.5°	625.4	613.2	570.5	515.7	476.0	445.5	421.0	402.7	387.4
60°	552.2	543.1	500.4	448.6	414.9	384.4	363.0	347.8	338.6
62.5°	488.2	469.9	433.2	387.4	356.9	332.5	311.2	302.0	308.1
65°	417.9	408.8	372.2	332.5	305.1	280.7	265.4	271.5	277.6
67.5°	360.0	347.8	317.3	280.7	256.3	238.0	228.9	241.1	244.1
70°	302.0	289.8	262.4	231.9	210.6	198.4	198.4	207.5	210.6
72.5°	247.2	238.0	213.6	189.2	174.0	164.8	170.9	177.0	180.1
75°	198.4	189.2	170.9	149.6	134.2	134.2	140.3	146.5	149.6
77.5°	152.6	146.5	128.1	112.8	106.7	106.7	112.8	115.9	118.9
80°	106.7	100.6	91.5	82.3	76.2	82.3	88.4	88.4	91.5
82.5°	70.1	67.1	61.0	54.9	54.9	57.9	61.0	64.0	64.0
85°	36.6	36.6	33.5	30.5	33.5	36.6	36.6	39.6	39.6
87.5°	12.2	12.2	12.2	12.2	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)