

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582567

Luminaire Tested: **HCC6W45D010MB-HM64560827-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MB-HM64560827-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4561.3 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582567
CATALOG NUMBER: HCC6W45D010MB-HM64560827-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P582567

CATALOG NUMBER: HCC6W45D010MB-HM64560827-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	127616	127616	127616
5°	128945	127768	126926
10°	130776	127375	126016
15°	133849	126573	125364
20°	135094	122814	123170
25°	132135	116632	118846
30°	125146	108346	112017
35°	113314	99026	102700
40°	98685	89518	92788
45°	83730	79233	82071
50°	74155	69217	71034
55°	65317	59190	58904
60°	58537	49832	45819
65°	52236	39965	32857
70°	45969	28867	20532
75°	38782	17432	11628
80°	29833	7703	4799
85°	17234	1887	1887



TEST NUMBER: P582567

CATALOG NUMBER: HCC6W45D010MB-HM64560827-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	4.8
10°-20°	635.1	13.9
20°-30°	918.0	20.1
30°-40°	966.0	21.2
40°-50°	812.0	17.8
50°-60°	569.9	12.5
60°-70°	313.5	6.9
70°-80°	111.3	2.4
80°-90°	14.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1774.1	38.9
0°-40°	2740.0	60.1
0°-60°	4122.0	90.4
0°-90°	4561.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4561.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2328	2328	2328	2328	2328	
5°	2343	2337	2322	2313	2306	224
15°	2358	2319	2230	2203	2209	665
25°	2184	2075	1928	1931	1965	999
35°	1693	1596	1480	1510	1535	1049
45°	1080	1050	1022	1046	1059	847
55°	683	647	619	619	616	615
65°	403	360	308	253	253	401
75°	183	146	82	55	55	197
85°	27	15	3	3	3	38
90°	0	0	0	0	0	



TEST NUMBER: P582567

CATALOG NUMBER: HCC6W45D010MB-HM64560827-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2327.9	2327.9	2327.9	2327.9	2327.9	2327.9	2327.9	2327.9	2327.9
2.5°	2327.9	2327.9	2324.9	2324.9	2318.8	2318.8	2315.7	2315.7	2315.7
5°	2343.2	2343.2	2337.1	2327.9	2321.8	2312.6	2312.6	2309.5	2306.5
7.5°	2352.3	2349.3	2340.1	2327.9	2312.6	2297.3	2291.2	2294.3	2291.2
10°	2349.3	2343.2	2331.0	2306.5	2288.2	2266.8	2263.8	2260.7	2263.8
12.5°	2355.4	2346.2	2321.8	2291.2	2260.7	2236.3	2233.3	2233.3	2236.3
15°	2358.4	2349.3	2318.8	2272.9	2230.2	2205.8	2202.8	2205.8	2208.9
17.5°	2349.3	2337.1	2291.2	2230.2	2181.4	2157.0	2157.0	2163.1	2169.2
20°	2315.7	2297.3	2233.3	2160.1	2105.2	2086.9	2093.0	2105.2	2111.3
22.5°	2254.6	2233.3	2160.1	2077.7	2019.8	2004.4	2019.8	2035.0	2041.1
25°	2184.5	2160.1	2074.7	1989.2	1928.2	1909.9	1931.2	1955.6	1964.8
27.5°	2089.9	2062.5	1983.1	1885.5	1824.5	1815.3	1839.7	1867.2	1873.3
30°	1977.0	1946.5	1858.0	1766.5	1711.6	1708.6	1736.0	1760.4	1769.6
32.5°	1839.7	1812.3	1736.0	1644.4	1595.6	1595.6	1623.1	1644.4	1653.6
35°	1693.2	1662.7	1595.6	1519.4	1479.7	1482.8	1510.2	1525.5	1534.6
37.5°	1519.4	1510.2	1458.4	1394.3	1366.8	1372.9	1394.3	1406.5	1415.7
40°	1379.0	1354.6	1321.0	1269.2	1250.9	1257.0	1278.3	1290.5	1296.6
42.5°	1226.5	1211.2	1183.8	1147.2	1135.0	1144.1	1162.4	1171.6	1168.5
45°	1080.0	1076.9	1049.5	1028.1	1022.0	1034.2	1046.4	1055.6	1058.6
47.5°	973.2	961.0	936.6	921.4	915.3	927.5	939.7	945.8	945.8
50°	869.5	857.3	832.9	817.7	811.6	823.8	832.9	839.0	832.9
52.5°	765.7	753.5	732.2	713.9	710.8	716.9	720.0	723.0	729.1
55°	683.4	671.2	646.8	625.4	619.3	622.4	619.3	619.3	616.3
57.5°	604.1	591.9	567.5	543.1	533.9	530.9	521.8	518.7	515.7
60°	533.9	518.7	494.3	466.9	454.5	442.3	427.1	417.9	417.9
62.5°	466.9	451.5	424.0	399.6	381.3	360.0	335.6	323.4	323.4
65°	402.7	390.5	360.0	332.5	308.1	280.7	253.3	247.2	253.3
67.5°	341.7	329.5	299.0	271.5	241.1	207.5	183.1	183.1	189.2
70°	286.8	274.6	247.2	213.6	180.1	146.4	128.1	128.1	128.1
72.5°	235.0	222.8	192.3	161.8	128.1	94.5	85.4	88.4	85.4
75°	183.1	174.0	146.4	112.8	82.3	57.9	54.9	51.8	54.9
77.5°	137.2	128.1	103.7	73.2	45.7	33.5	30.5	30.5	30.5
80°	94.5	85.4	67.1	42.7	24.4	15.2	15.2	15.2	15.2
82.5°	57.9	48.8	36.6	21.3	9.1	9.1	9.1	9.1	9.1
85°	27.4	21.3	15.2	6.1	3.0	3.0	3.0	3.0	3.0
87.5°	6.1	6.1	3.0	3.0	0.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)