

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582593

Luminaire Tested: **HCC6W45D010MB-HM64560830-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MB-HM64560830-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4721.7 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582593
CATALOG NUMBER: HCC6W45D010MB-HM64560830-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582593

CATALOG NUMBER: HCC6W45D010MB-HM64560830-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			87																
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76			76																
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66																
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			58																
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52			52																
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46			46																
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42			42																
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38			38																
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34			34																
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31			31																

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	132177	132177	132177
5°	135037	132132	129776
10°	139165	130909	126512
15°	143571	129172	123378
20°	145846	124325	118363
25°	143452	116952	111569
30°	136572	108422	104250
35°	124544	97875	96329
40°	108897	87922	87450
45°	93715	77372	79163
50°	81464	67418	68825
55°	71147	59181	59811
60°	63197	51279	46937
65°	56400	43156	35892
70°	49640	35359	30101
75°	42552	27895	28594
80°	34316	23930	28065
85°	22769	20757	24845



TEST NUMBER: P582593
 CATALOG NUMBER: HCC6W45D010MB-HM64560830-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.3	4.8
10°-20°	649.9	13.8
20°-30°	927.7	19.6
30°-40°	971.8	20.6
40°-50°	818.2	17.3
50°-60°	582.3	12.3
60°-70°	340.8	7.2
70°-80°	161.3	3.4
80°-90°	41.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1805.9	38.2
0°-40°	2777.6	58.8
0°-60°	4178.1	88.5
0°-90°	4721.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4721.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2411	2411	2411	2411	2411	
5°	2454	2434	2401	2368	2358	236
15°	2530	2437	2276	2184	2174	714
25°	2372	2204	1934	1841	1844	1085
35°	1861	1706	1462	1413	1439	1156
45°	1209	1120	998	1001	1021	938
55°	744	682	619	619	626	671
65°	435	385	333	280	277	434
75°	201	168	132	128	135	216
85°	36	30	33	40	40	47
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582593

CATALOG NUMBER: HCC6W45D010MB-HM64560830-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2411.1	2411.1	2411.1	2411.1	2411.1	2411.1	2411.1	2411.1	2411.1
2.5°	2414.4	2414.4	2411.1	2407.8	2401.1	2391.3	2384.7	2378.1	2378.1
5°	2453.9	2447.3	2434.1	2417.7	2401.1	2381.4	2368.3	2358.3	2358.3
7.5°	2486.9	2473.6	2447.3	2417.7	2388.0	2361.7	2338.6	2325.5	2322.2
10°	2500.0	2483.5	2444.1	2397.8	2351.7	2315.5	2289.2	2272.7	2272.7
12.5°	2513.2	2493.4	2440.7	2374.9	2315.5	2266.1	2239.8	2226.6	2223.3
15°	2529.7	2503.3	2437.4	2355.0	2276.0	2220.0	2183.8	2173.9	2173.9
17.5°	2529.7	2496.7	2414.4	2312.2	2213.5	2150.8	2118.0	2108.0	2111.3
20°	2500.0	2463.8	2365.0	2239.8	2131.1	2065.2	2032.2	2025.7	2028.9
22.5°	2444.1	2401.1	2289.2	2154.1	2035.6	1966.4	1936.7	1936.7	1933.5
25°	2371.6	2325.5	2203.6	2061.9	1933.5	1864.2	1841.3	1844.5	1844.5
27.5°	2276.0	2229.9	2108.0	1956.6	1828.1	1758.9	1742.4	1749.1	1752.3
30°	2157.5	2108.0	1979.6	1831.4	1712.8	1643.6	1633.8	1643.6	1646.9
32.5°	2012.5	1976.3	1851.1	1699.6	1587.7	1528.3	1525.0	1534.9	1548.1
35°	1861.0	1821.4	1706.2	1567.8	1462.5	1413.0	1413.0	1429.5	1439.4
37.5°	1696.3	1656.7	1551.4	1436.1	1347.2	1301.1	1307.7	1324.1	1327.4
40°	1521.7	1492.1	1403.1	1304.4	1228.6	1192.4	1202.2	1218.7	1222.0
42.5°	1357.0	1330.7	1258.3	1169.2	1113.3	1086.9	1100.2	1119.9	1126.4
45°	1208.8	1179.2	1119.9	1044.1	998.0	984.9	1001.3	1014.5	1021.1
47.5°	1073.8	1047.5	998.0	928.9	895.9	889.4	905.8	912.4	918.9
50°	955.2	928.9	879.4	816.9	790.5	790.5	803.7	810.3	807.0
52.5°	839.9	816.9	770.8	718.0	701.6	701.6	711.4	714.7	721.4
55°	744.4	721.4	681.9	632.4	619.2	612.7	619.2	619.2	625.8
57.5°	655.5	635.6	599.5	553.3	536.9	530.3	527.0	523.7	530.3
60°	576.4	560.0	520.5	480.9	467.7	451.3	438.1	424.9	428.1
62.5°	503.9	487.5	451.3	411.7	398.6	375.5	359.1	342.5	349.2
65°	434.8	418.3	385.3	352.5	332.7	306.3	280.0	270.1	276.7
67.5°	372.2	359.1	326.1	293.1	276.7	247.0	220.6	220.6	223.9
70°	309.7	296.4	270.1	240.5	220.6	194.4	184.4	187.8	187.8
72.5°	253.6	243.7	217.4	191.1	171.3	154.8	154.8	158.1	161.4
75°	200.9	194.4	168.0	145.0	131.7	121.9	128.4	131.7	135.0
77.5°	154.8	145.0	125.2	108.7	98.8	102.1	108.7	112.0	115.3
80°	108.7	105.5	88.9	79.1	75.8	79.1	85.6	88.9	88.9
82.5°	69.2	65.9	56.0	52.7	52.7	56.0	62.6	62.6	62.6
85°	36.2	33.0	29.7	29.7	33.0	36.2	39.5	39.5	39.5
87.5°	13.1	9.9	13.1	13.1	16.4	16.4	16.4	16.4	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)