

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582718

Luminaire Tested: **HCC6S50D010MW-HM64560827-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MW-HM64560827-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4469.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582718
CATALOG NUMBER: HCC6S50D010MW-HM64560827-61WWW

Luminous Intensity Polar Plot





TEST NUMBER: P582718

CATALOG NUMBER: HCC6S50D010MW-HM64560827-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76				
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66				
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58				
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51				
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42				
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38				
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34				
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	131519	131519	131519
5°	137348	131130	125093
10°	141096	128872	117550
15°	144592	126079	110137
20°	145233	120370	101153
25°	142188	112694	92776
30°	134901	103630	85032
35°	122523	93137	76279
40°	106750	82955	68629
45°	92374	72597	60332
50°	80688	62505	52868
55°	71290	54937	45360
60°	64085	48143	39295
65°	57386	41885	38110
70°	51243	35727	35727
75°	44459	30098	33529
80°	35674	25508	30559
85°	24342	22329	26355



TEST NUMBER: P582718
 CATALOG NUMBER: HCC6S50D010MW-HM64560827-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.5	5.0
10°-20°	626.8	14.0
20°-30°	873.5	19.5
30°-40°	900.0	20.1
40°-50°	745.9	16.7
50°-60°	536.0	12.0
60°-70°	341.4	7.6
70°-80°	175.3	3.9
80°-90°	44.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1725.8	38.6
0°-40°	2625.8	58.8
0°-60°	3907.7	87.4
0°-90°	4469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4469.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2399	2399	2399	2399	2399	
5°	2496	2457	2383	2305	2273	239
15°	2548	2451	2222	2018	1941	718
25°	2351	2189	1863	1624	1534	1077
35°	1831	1682	1392	1208	1140	1137
45°	1192	1108	936	817	778	922
55°	746	684	575	510	475	672
65°	442	394	323	281	294	443
75°	210	181	142	149	158	224
85°	39	36	36	39	42	50
90°	0	0	0	0	0	



TEST NUMBER: P582718

CATALOG NUMBER: HCC6S50D010MW-HM64560827-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2399.1	2399.1	2399.1	2399.1	2399.1	2399.1	2399.1	2399.1	2399.1
2.5°	2444.3	2434.6	2421.8	2408.8	2389.4	2366.8	2347.5	2341.0	2331.3
5°	2495.9	2483.1	2457.2	2424.9	2382.9	2341.0	2305.4	2282.9	2273.2
7.5°	2528.3	2512.1	2476.6	2421.8	2360.3	2299.1	2247.3	2215.1	2202.1
10°	2534.7	2518.6	2470.2	2395.9	2315.1	2231.1	2166.7	2127.9	2111.7
12.5°	2544.3	2521.8	2460.5	2373.2	2269.9	2173.0	2092.4	2044.0	2027.8
15°	2547.7	2521.8	2450.8	2344.2	2221.5	2105.3	2018.1	1960.0	1940.6
17.5°	2534.7	2505.6	2421.8	2292.6	2153.7	2031.0	1927.6	1866.3	1840.5
20°	2489.5	2457.2	2360.3	2215.1	2063.3	1934.1	1827.6	1763.0	1733.9
22.5°	2431.4	2389.4	2279.7	2124.6	1966.4	1830.8	1724.3	1659.7	1630.6
25°	2350.7	2311.9	2189.2	2024.6	1863.1	1721.1	1624.1	1556.3	1533.8
27.5°	2257.0	2211.8	2085.9	1921.3	1756.5	1614.4	1520.8	1459.5	1430.4
30°	2131.1	2089.1	1963.2	1798.5	1637.1	1504.7	1407.9	1356.1	1343.3
32.5°	1982.5	1947.0	1824.3	1669.3	1514.4	1391.7	1310.9	1256.1	1243.1
35°	1830.8	1788.9	1682.2	1537.0	1391.7	1281.9	1207.6	1159.2	1139.8
37.5°	1666.2	1627.4	1537.0	1407.9	1278.7	1175.3	1110.7	1068.8	1049.4
40°	1491.7	1462.7	1378.7	1275.5	1159.2	1068.8	1013.9	978.3	959.0
42.5°	1330.3	1301.2	1243.1	1146.3	1049.4	968.7	920.2	888.0	871.8
45°	1191.5	1165.6	1107.5	1023.6	936.4	868.6	816.9	794.3	778.2
47.5°	1052.6	1039.8	988.0	910.6	829.9	771.7	736.2	710.4	697.5
50°	946.1	929.9	881.5	800.7	732.9	687.8	655.5	632.9	619.9
52.5°	836.3	820.2	775.0	707.2	652.3	610.2	578.0	558.6	545.7
55°	745.9	732.9	684.5	623.2	574.8	539.2	510.2	487.5	474.6
57.5°	662.0	649.0	603.8	545.7	503.7	471.5	445.6	426.2	410.0
60°	584.5	574.8	529.6	474.6	439.1	406.9	384.3	368.1	358.4
62.5°	516.7	497.2	458.5	410.0	377.8	351.9	329.4	319.7	326.1
65°	442.4	432.7	394.0	351.9	322.9	297.0	281.0	287.3	293.8
67.5°	381.0	368.1	335.8	297.0	271.3	251.9	242.2	255.1	258.3
70°	319.7	306.7	277.7	245.4	222.9	209.9	209.9	219.5	222.9
72.5°	261.6	251.9	226.0	200.2	184.0	174.3	180.8	187.3	190.5
75°	209.9	200.2	180.8	158.3	142.1	142.1	148.6	154.9	158.3
77.5°	161.4	154.9	135.6	119.5	113.0	113.0	119.5	122.7	125.9
80°	113.0	106.5	96.8	87.2	80.8	87.2	93.7	93.7	96.8
82.5°	74.3	71.0	64.6	58.1	58.1	61.3	64.6	67.8	67.8
85°	38.7	38.7	35.5	32.2	35.5	38.7	38.7	41.9	41.9
87.5°	12.9	12.9	12.9	12.9	16.2	16.2	16.2	16.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)