

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582609

Luminaire Tested: **HCC6S45D010MB-HM64560835-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010MB-HM64560835-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4362.1 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582609
CATALOG NUMBER: HCC6S45D010MB-HM64560835-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P582609

CATALOG NUMBER: HCC6S45D010MB-HM64560835-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89	89	89	89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78	78	78	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69	69	69	69
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61	61	61	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54	54	54	54
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44	44	44	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40	40	40	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37	37	37	37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34	34	34	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	134189	134189	134189
5°	136787	133947	130915
10°	141436	132240	126679
15°	145761	129938	122708
20°	148022	124523	116292
25°	145357	115991	108284
30°	138167	105700	99376
35°	124189	94469	89623
40°	107172	82784	80071
45°	90746	71271	69395
50°	77814	60194	59606
55°	67458	50674	48706
60°	58888	41137	34723
65°	51808	31715	19198
70°	44687	20965	9377
75°	37914	10209	3643
80°	29328	4325	2178
85°	17360	2139	2139



TEST NUMBER: P582609

CATALOG NUMBER: HCC6S45D010MB-HM64560835-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.0	5.3
10°-20°	653.2	15.0
20°-30°	919.9	21.1
30°-40°	939.9	21.5
40°-50°	757.8	17.4
50°-60°	508.3	11.7
60°-70°	257.2	5.9
70°-80°	82.2	1.9
80°-90°	12.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1804.1	41.4
0°-40°	2744.0	62.9
0°-60°	4010.0	91.9
0°-90°	4362.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4362.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2448	2448	2448	2448	2448	
5°	2486	2468	2434	2396	2379	239
15°	2568	2465	2290	2186	2162	725
25°	2403	2214	1918	1801	1790	1100
35°	1856	1687	1412	1332	1339	1155
45°	1170	1078	919	888	895	910
55°	706	627	530	506	510	635
65°	399	331	244	162	148	399
75°	179	127	48	17	17	192
85°	28	14	3	3	3	37
90°	0	0	0	0	0	



TEST NUMBER: P582609

CATALOG NUMBER: HCC6S45D010MB-HM64560835-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2447.8	2447.8	2447.8	2447.8	2447.8	2447.8	2447.8	2447.8	2447.8
2.5°	2458.1	2454.7	2451.3	2444.4	2434.1	2423.8	2416.8	2409.9	2406.5
5°	2485.7	2478.8	2468.5	2454.7	2434.1	2409.9	2396.2	2382.5	2379.0
7.5°	2523.6	2509.8	2482.3	2451.3	2416.8	2382.5	2358.3	2344.6	2334.3
10°	2540.8	2516.7	2478.8	2427.2	2375.6	2334.3	2303.2	2282.5	2275.7
12.5°	2554.6	2527.0	2472.0	2403.1	2334.3	2279.1	2244.8	2227.5	2220.6
15°	2568.3	2540.8	2465.1	2375.6	2289.5	2224.0	2186.2	2169.0	2162.1
17.5°	2568.3	2530.5	2440.9	2327.3	2224.0	2144.8	2106.9	2089.8	2086.3
20°	2537.3	2496.0	2385.9	2251.6	2134.5	2045.0	2010.6	2000.3	1993.4
22.5°	2478.8	2430.6	2306.7	2155.2	2027.8	1941.8	1903.9	1897.0	1890.1
25°	2403.1	2354.9	2213.7	2051.9	1917.6	1831.5	1800.6	1793.8	1790.2
27.5°	2306.7	2255.1	2106.9	1941.8	1797.2	1714.6	1687.0	1687.0	1683.5
30°	2182.7	2124.2	1979.7	1814.4	1669.8	1594.0	1573.3	1573.3	1569.9
32.5°	2031.3	1972.8	1841.8	1683.5	1545.8	1466.6	1449.5	1456.3	1452.9
35°	1855.7	1807.5	1687.0	1532.1	1411.6	1339.2	1332.4	1339.2	1339.2
37.5°	1680.1	1635.3	1532.1	1397.7	1284.2	1218.7	1218.7	1229.1	1225.7
40°	1497.6	1463.2	1366.8	1249.7	1156.8	1112.0	1105.1	1115.5	1118.9
42.5°	1325.5	1297.9	1215.3	1118.9	1036.2	991.5	1001.9	1008.8	1012.2
45°	1170.5	1143.0	1077.6	977.8	919.3	888.2	888.2	898.5	895.1
47.5°	1032.8	1012.2	946.7	850.4	798.7	785.0	791.9	798.7	798.7
50°	912.4	881.4	819.3	743.7	705.8	688.6	695.5	698.9	698.9
52.5°	798.7	778.1	716.1	647.3	612.8	602.5	602.5	606.0	606.0
55°	705.8	681.6	626.6	557.8	530.2	516.5	506.1	502.6	509.6
57.5°	616.3	595.6	543.9	478.6	447.6	433.8	413.1	406.2	413.1
60°	537.1	519.9	468.3	406.2	375.2	347.7	323.6	309.9	316.7
62.5°	468.3	447.6	395.9	344.3	309.9	278.8	241.1	220.3	230.6
65°	399.4	382.2	330.6	278.8	244.5	206.6	161.8	148.0	148.0
67.5°	337.4	320.2	272.0	227.2	185.9	141.1	99.8	96.4	99.8
70°	278.8	261.7	220.3	175.6	130.8	86.1	58.5	58.5	58.5
72.5°	230.6	210.0	172.2	127.4	82.6	44.8	31.0	34.5	34.5
75°	179.0	161.8	127.4	86.1	48.2	20.6	17.2	17.2	17.2
77.5°	134.3	120.5	89.5	55.1	24.0	6.9	6.9	6.9	6.9
80°	92.9	79.2	58.5	34.5	13.7	6.9	6.9	6.9	6.9
82.5°	55.1	48.2	34.5	17.2	6.9	3.4	3.4	3.4	3.4
85°	27.6	24.0	13.7	6.9	3.4	3.4	3.4	3.4	3.4
87.5°	6.9	6.9	3.4	3.4	0.0	3.4	3.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)