

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582711

Luminaire Tested: **HCC6W50D010MW-HM64560827-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MW-HM64560827-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4827.4 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582711
CATALOG NUMBER: HCC6W50D010MW-HM64560827-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582711

CATALOG NUMBER: HCC6W50D010MW-HM64560827-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67																			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59																			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53																			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47																			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	135055	135055	135055
5°	136457	135219	134327
10°	138396	134800	133364
15°	141652	133957	132674
20°	142970	129978	130345
25°	139835	123431	125777
30°	132444	114663	118544
35°	119926	104802	108690
40°	104446	94735	98198
45°	88614	83861	86862
50°	78479	73243	75179
55°	69121	62650	62344
60°	61947	52748	48505
65°	55285	42300	34764
70°	48646	30534	21734
75°	41027	18470	12306
80°	31601	8177	5114
85°	18304	2013	2013



TEST NUMBER: P582711
 CATALOG NUMBER: HCC6W50D010MW-HM64560827-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.8	4.8
10°-20°	672.1	13.9
20°-30°	971.6	20.1
30°-40°	1022.3	21.2
40°-50°	859.4	17.8
50°-60°	603.2	12.5
60°-70°	331.8	6.9
70°-80°	117.8	2.4
80°-90°	15.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1877.5	38.9
0°-40°	2899.8	60.1
0°-60°	4362.4	90.4
0°-90°	4827.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4827.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2464	2464	2464	2464	2464	
5°	2480	2473	2457	2448	2441	237
15°	2496	2454	2360	2331	2338	704
25°	2312	2196	2041	2044	2079	1058
35°	1792	1689	1566	1598	1624	1111
45°	1143	1111	1082	1108	1120	897
55°	723	684	656	656	652	651
65°	426	381	326	268	268	424
75°	194	155	87	58	58	208
85°	29	16	3	3	3	40
90°	0	0	0	0	0	



TEST NUMBER: P582711

CATALOG NUMBER: HCC6W50D010MW-HM64560827-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2463.6	2463.6	2463.6	2463.6	2463.6	2463.6	2463.6	2463.6	2463.6
2.5°	2463.6	2463.6	2460.4	2460.4	2453.9	2453.9	2450.7	2450.7	2450.7
5°	2479.7	2479.7	2473.3	2463.6	2457.2	2447.5	2447.5	2444.2	2441.0
7.5°	2489.4	2486.2	2476.6	2463.6	2447.5	2431.3	2424.8	2428.1	2424.8
10°	2486.2	2479.7	2466.9	2441.0	2421.6	2399.1	2395.8	2392.6	2395.8
12.5°	2492.6	2482.9	2457.2	2424.8	2392.6	2366.7	2363.5	2363.5	2366.7
15°	2495.9	2486.2	2453.9	2405.5	2360.3	2334.5	2331.2	2334.5	2337.7
17.5°	2486.2	2473.3	2424.8	2360.3	2308.6	2282.8	2282.8	2289.3	2295.7
20°	2450.7	2431.3	2363.5	2286.1	2228.0	2208.6	2215.0	2228.0	2234.3
22.5°	2386.1	2363.5	2286.1	2198.9	2137.5	2121.3	2137.5	2153.7	2160.0
25°	2311.8	2286.1	2195.6	2105.3	2040.6	2021.3	2043.8	2069.7	2079.4
27.5°	2211.8	2182.7	2098.8	1995.4	1930.8	1921.1	1947.0	1976.0	1982.5
30°	2092.3	2060.0	1966.4	1869.5	1811.4	1808.1	1837.2	1863.0	1872.7
32.5°	1947.0	1917.9	1837.2	1740.3	1688.7	1688.7	1717.8	1740.3	1750.0
35°	1792.0	1759.7	1688.7	1607.9	1566.0	1569.2	1598.2	1614.4	1624.1
37.5°	1607.9	1598.2	1543.4	1475.5	1446.5	1453.0	1475.5	1488.5	1498.2
40°	1459.5	1433.6	1398.1	1343.2	1323.8	1330.3	1352.8	1365.8	1372.2
42.5°	1298.0	1281.9	1252.8	1214.1	1201.1	1210.8	1230.2	1239.9	1236.6
45°	1143.0	1139.8	1110.7	1088.2	1081.7	1094.6	1107.5	1117.2	1120.4
47.5°	1030.0	1017.1	991.2	975.2	968.7	981.5	994.5	1000.9	1000.9
50°	920.2	907.4	881.5	865.3	858.8	871.8	881.5	887.9	881.5
52.5°	810.4	797.5	775.0	755.6	752.3	758.8	762.0	765.3	771.7
55°	723.2	710.4	684.5	662.0	655.5	658.6	655.5	655.5	652.3
57.5°	639.3	626.4	600.5	574.8	565.0	561.8	552.1	548.9	545.6
60°	565.0	548.9	523.1	494.0	481.1	468.1	452.1	442.4	442.4
62.5°	494.0	477.8	448.8	423.0	403.5	381.0	355.1	342.3	342.3
65°	426.2	413.4	381.0	351.9	326.1	297.0	268.0	261.6	268.0
67.5°	361.6	348.7	316.4	287.3	255.1	219.5	193.7	193.7	200.2
70°	303.5	290.6	261.6	226.0	190.5	154.9	135.6	135.6	135.6
72.5°	248.6	235.7	203.4	171.1	135.6	100.1	90.5	93.7	90.5
75°	193.7	184.0	154.9	119.5	87.2	61.3	58.1	54.9	58.1
77.5°	145.3	135.6	109.8	77.5	48.4	35.5	32.2	32.2	32.2
80°	100.1	90.5	71.0	45.2	25.9	16.2	16.2	16.2	16.2
82.5°	61.3	51.6	38.7	22.6	9.7	9.7	9.7	9.7	9.7
85°	29.1	22.6	16.2	6.5	3.2	3.2	3.2	3.2	3.2
87.5°	6.5	6.5	3.2	3.2	0.0	3.2	3.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)