

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582736

Luminaire Tested: **HCC6S50D010MW-HM64560830-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MW-HM64560830-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4826.2 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582736
CATALOG NUMBER: HCC6S50D010MW-HM64560830-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582736

CATALOG NUMBER: HCC6S50D010MW-HM64560830-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66																			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42																			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38																			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34																			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	142034	142034	142034
5°	148332	141613	135087
10°	152374	139176	126946
15°	156147	136159	118939
20°	156843	129990	109239
25°	153553	121701	100191
30°	145681	111916	91824
35°	132314	100579	82382
40°	115287	89589	74110
45°	99755	78403	65154
50°	87136	67503	57098
55°	76996	59324	48992
60°	69194	52002	42431
65°	61965	45232	41159
70°	55330	38564	38564
75°	47996	32491	36198
80°	38515	27529	33022
85°	26292	24153	28556



TEST NUMBER: P582736
 CATALOG NUMBER: HCC6S50D010MW-HM64560830-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.5	5.0
10°-20°	676.9	14.0
20°-30°	943.3	19.5
30°-40°	971.9	20.1
40°-50°	805.5	16.7
50°-60°	578.9	12.0
60°-70°	368.7	7.6
70°-80°	189.3	3.9
80°-90°	48.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1863.7	38.6
0°-40°	2835.6	58.8
0°-60°	4220.0	87.4
0°-90°	4826.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4826.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2591	2591	2591	2591	2591	
5°	2696	2654	2573	2490	2455	258
15°	2751	2647	2399	2179	2096	775
25°	2539	2364	2012	1754	1656	1163
35°	1977	1817	1503	1304	1231	1228
45°	1287	1196	1011	882	840	996
55°	806	739	621	551	513	726
65°	478	425	349	303	317	478
75°	227	195	153	160	171	242
85°	42	38	38	42	45	54
90°	0	0	0	0	0	



TEST NUMBER: P582736

CATALOG NUMBER: HCC6S50D010MW-HM64560830-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2590.9	2590.9	2590.9	2590.9	2590.9	2590.9	2590.9	2590.9	2590.9
2.5°	2639.7	2629.3	2615.2	2601.3	2580.4	2556.0	2535.0	2528.0	2517.7
5°	2695.5	2681.5	2653.6	2618.7	2573.4	2528.0	2489.8	2465.3	2454.8
7.5°	2730.4	2712.9	2674.5	2615.2	2549.0	2482.8	2427.0	2392.1	2378.2
10°	2737.3	2719.8	2667.5	2587.3	2500.2	2409.5	2339.8	2298.0	2280.5
12.5°	2747.7	2723.4	2657.1	2563.0	2451.4	2346.8	2259.6	2207.3	2189.8
15°	2751.3	2723.4	2646.6	2531.6	2399.1	2273.5	2179.4	2116.6	2095.7
17.5°	2737.3	2705.9	2615.2	2475.7	2325.9	2193.4	2081.7	2015.5	1987.6
20°	2688.5	2653.6	2549.0	2392.1	2228.2	2088.7	1973.7	1903.9	1872.5
22.5°	2625.7	2580.4	2461.8	2294.4	2123.6	1977.1	1862.1	1792.3	1761.0
25°	2538.6	2496.8	2364.2	2186.4	2012.0	1858.5	1754.0	1680.8	1656.4
27.5°	2437.5	2388.6	2252.6	2074.8	1896.9	1743.5	1642.4	1576.2	1544.7
30°	2301.4	2256.1	2120.1	1942.3	1768.0	1624.9	1520.3	1464.6	1450.6
32.5°	2141.0	2102.7	1970.1	1802.8	1635.4	1502.9	1415.8	1356.5	1342.6
35°	1977.1	1931.8	1816.7	1659.8	1502.9	1384.4	1304.2	1251.9	1231.0
37.5°	1799.3	1757.4	1659.8	1520.3	1380.8	1269.2	1199.5	1154.2	1133.3
40°	1611.0	1579.6	1489.0	1377.4	1251.9	1154.2	1094.9	1056.5	1035.6
42.5°	1436.7	1405.3	1342.6	1237.9	1133.3	1046.1	993.8	959.0	941.5
45°	1286.7	1258.8	1196.0	1105.4	1011.3	938.0	882.2	857.8	840.4
47.5°	1136.7	1122.8	1067.0	983.3	896.1	833.4	795.0	767.2	753.2
50°	1021.7	1004.2	952.0	864.7	791.5	742.7	707.9	683.4	669.5
52.5°	903.1	885.8	836.9	763.6	704.3	659.0	624.2	603.3	589.3
55°	805.6	791.5	739.3	673.1	620.7	582.4	550.9	526.5	512.6
57.5°	714.9	700.9	652.0	589.3	544.0	509.1	481.3	460.2	442.9
60°	631.1	620.7	571.8	512.6	474.3	439.3	415.0	397.5	387.0
62.5°	557.9	537.0	495.2	442.9	408.0	380.0	355.7	345.2	352.2
65°	477.7	467.2	425.4	380.0	348.7	320.8	303.4	310.4	317.3
67.5°	411.5	397.5	362.7	320.8	292.9	272.0	261.5	275.5	279.0
70°	345.2	331.3	299.9	265.0	240.6	226.6	226.6	237.1	240.6
72.5°	282.5	272.0	244.1	216.2	198.8	188.3	195.2	202.3	205.7
75°	226.6	216.2	195.2	170.9	153.4	153.4	160.4	167.3	170.9
77.5°	174.3	167.3	146.4	129.0	122.0	122.0	129.0	132.5	136.1
80°	122.0	115.0	104.6	94.1	87.2	94.1	101.1	101.1	104.6
82.5°	80.2	76.8	69.8	62.7	62.7	66.3	69.8	73.2	73.2
85°	41.8	41.8	38.4	34.8	38.4	41.8	41.8	45.4	45.4
87.5°	13.9	13.9	13.9	13.9	17.5	17.5	17.5	17.5	17.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)