

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582728

Luminaire Tested: **HCC6W50D010MB-HM64560830-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560830-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5195.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582728
CATALOG NUMBER: HCC6W50D010MB-HM64560830-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582728

CATALOG NUMBER: HCC6W50D010MB-HM64560830-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	141085	141085	141085
5°	141817	142587	142587
10°	145789	143262	142677
15°	150415	144087	144087
20°	152176	140788	144038
25°	149138	133738	140065
30°	141060	124279	131565
35°	127662	113655	119257
40°	111051	102821	106807
45°	94894	91653	94894
50°	83281	80304	83571
55°	72657	67658	70325
60°	64238	56213	55445
65°	57010	44337	37994
70°	50313	31303	22921
75°	42849	17728	11078
80°	31917	5525	3315
85°	17549	2201	2201



TEST NUMBER: P582728
 CATALOG NUMBER: HCC6W50D010MB-HM64560830-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.9	4.8
10°-20°	722.3	13.9
20°-30°	1054.9	20.3
30°-40°	1106.3	21.3
40°-50°	932.1	17.9
50°-60°	653.0	12.6
60°-70°	350.1	6.7
70°-80°	117.4	2.3
80°-90°	12.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2024.1	39.0
0°-40°	3130.4	60.2
0°-60°	4715.5	90.8
0°-90°	5195.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5195.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2574	2574	2574	2574	2574	
5°	2577	2588	2591	2591	2591	248
15°	2650	2615	2539	2525	2539	748
25°	2466	2361	2211	2249	2316	1129
35°	1908	1810	1698	1747	1782	1184
45°	1224	1203	1182	1214	1224	954
55°	760	736	708	722	736	684
65°	440	401	342	282	293	439
75°	202	157	84	52	52	214
85°	28	14	4	4	4	38
90°	0	0	0	0	0	



TEST NUMBER: P582728

CATALOG NUMBER: HCC6W50D010MB-HM64560830-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2573.6	2573.6	2573.6	2573.6	2573.6	2573.6	2573.6	2573.6	2573.6
2.5°	2556.2	2556.2	2563.1	2570.1	2577.1	2577.1	2580.6	2584.0	2580.6
5°	2577.1	2577.1	2587.6	2591.1	2591.1	2587.6	2591.1	2591.1	2591.1
7.5°	2608.5	2601.5	2605.0	2598.1	2591.1	2587.6	2584.0	2584.0	2584.0
10°	2619.0	2612.0	2605.0	2591.1	2573.6	2563.1	2559.7	2563.1	2563.1
12.5°	2632.9	2626.0	2608.5	2580.6	2559.7	2542.2	2538.8	2545.8	2545.8
15°	2650.3	2643.3	2615.4	2570.1	2538.8	2521.3	2524.7	2531.8	2538.8
17.5°	2650.3	2636.3	2591.1	2531.8	2493.4	2476.0	2489.9	2507.4	2517.8
20°	2608.5	2594.5	2531.8	2458.5	2413.3	2402.7	2427.2	2458.5	2469.0
22.5°	2552.7	2524.7	2451.5	2364.4	2315.6	2315.6	2350.4	2388.8	2402.7
25°	2465.6	2444.6	2360.9	2259.7	2211.0	2207.4	2249.3	2301.7	2315.6
27.5°	2367.9	2339.9	2249.3	2144.7	2092.4	2095.9	2141.2	2193.5	2207.4
30°	2228.4	2193.5	2113.3	2012.2	1963.3	1977.3	2022.6	2061.0	2078.4
32.5°	2071.5	2040.1	1966.8	1872.7	1830.8	1844.7	1883.1	1918.1	1932.0
35°	1907.6	1872.7	1809.9	1726.3	1698.3	1712.2	1747.2	1775.0	1782.0
37.5°	1722.7	1698.3	1652.9	1586.7	1565.8	1583.2	1611.1	1628.6	1635.6
40°	1551.8	1530.9	1492.5	1443.8	1436.8	1450.7	1478.6	1489.1	1492.5
42.5°	1384.5	1367.0	1342.6	1307.7	1307.7	1321.7	1346.1	1353.1	1356.6
45°	1224.0	1213.6	1203.1	1175.2	1182.2	1199.7	1213.6	1224.0	1224.0
47.5°	1084.5	1088.1	1074.1	1053.2	1060.2	1077.5	1088.1	1098.4	1098.4
50°	976.5	965.9	952.0	931.1	941.6	955.5	969.5	976.5	979.9
52.5°	850.9	847.4	837.0	812.5	819.5	826.5	840.4	850.9	854.3
55°	760.2	749.8	735.8	707.9	707.9	714.9	721.8	728.8	735.8
57.5°	673.1	662.5	641.6	610.2	606.8	606.8	603.3	610.2	620.7
60°	585.9	582.4	550.9	523.1	512.7	502.2	488.2	491.7	505.7
62.5°	509.1	502.2	474.3	439.5	418.4	401.1	383.6	380.2	394.1
65°	439.5	432.5	401.1	366.1	341.8	310.4	282.5	282.5	292.9
67.5°	376.6	362.7	334.8	296.4	265.0	226.6	198.8	205.7	209.3
70°	313.9	303.4	272.0	233.6	195.3	157.0	139.5	143.0	143.0
72.5°	258.0	244.1	212.7	174.3	136.1	101.1	94.1	90.7	90.7
75°	202.3	188.4	157.0	118.6	83.7	59.3	52.3	52.3	52.3
77.5°	146.4	136.1	108.1	73.2	45.4	27.9	24.4	20.9	20.9
80°	101.1	90.7	66.3	38.4	17.5	10.5	10.5	10.5	10.5
82.5°	59.3	48.8	31.4	17.5	7.0	3.5	3.5	3.5	3.5
85°	27.9	20.9	13.9	7.0	3.5	3.5	3.5	3.5	3.5
87.5°	3.5	3.5	3.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)