

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582639

Luminaire Tested: **HCC6S45D010MW-HM64560927-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010MW-HM64560927-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3792.9 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582639
CATALOG NUMBER: HCC6S45D010MW-HM64560927-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582639

CATALOG NUMBER: HCC6S45D010MW-HM64560927-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67				
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59				
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47				
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42				
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38				
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	106115	106115	106115
5°	107220	106240	105541
10°	108738	105915	104785
15°	111295	105250	104240
20°	112331	102121	102413
25°	109869	96985	98824
30°	104067	90090	93141
35°	94228	82342	85401
40°	82061	74432	77159
45°	69620	65883	68247
50°	61661	57550	59060
55°	54316	49212	48983
60°	48680	41455	38111
65°	43442	33233	27318
70°	38228	23994	17070
75°	32258	14509	9658
80°	24814	6409	4009
85°	14404	1635	1635



TEST NUMBER: P582639

CATALOG NUMBER: HCC6S45D010MW-HM64560927-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.7	4.8
10°-20°	528.1	13.9
20°-30°	763.3	20.1
30°-40°	803.2	21.2
40°-50°	675.2	17.8
50°-60°	473.9	12.5
60°-70°	260.7	6.9
70°-80°	92.6	2.4
80°-90°	12.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1475.2	38.9
0°-40°	2278.4	60.1
0°-60°	3427.5	90.4
0°-90°	3792.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3792.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1936	1936	1936	1936	1936	
5°	1948	1943	1931	1923	1918	186
15°	1961	1928	1854	1832	1837	553
25°	1816	1725	1603	1606	1634	831
35°	1408	1327	1230	1256	1276	873
45°	898	873	850	870	880	705
55°	568	538	515	515	512	511
65°	335	299	256	211	211	333
75°	152	122	68	46	46	163
85°	23	13	3	3	3	31
90°	0	0	0	0	0	



TEST NUMBER: P582639

CATALOG NUMBER: HCC6S45D010MW-HM64560927-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1935.7	1935.7	1935.7	1935.7	1935.7	1935.7	1935.7	1935.7	1935.7
2.5°	1935.7	1935.7	1933.1	1933.1	1928.1	1928.1	1925.5	1925.5	1925.5
5°	1948.4	1948.4	1943.3	1935.7	1930.6	1923.0	1923.0	1920.4	1917.9
7.5°	1956.0	1953.4	1945.8	1935.7	1923.0	1910.3	1905.2	1907.8	1905.2
10°	1953.4	1948.4	1938.1	1917.9	1902.7	1884.9	1882.4	1879.8	1882.4
12.5°	1958.6	1950.9	1930.6	1905.2	1879.8	1859.6	1857.0	1857.0	1859.6
15°	1961.0	1953.4	1928.1	1890.1	1854.5	1834.2	1831.6	1834.2	1836.7
17.5°	1953.4	1943.3	1905.2	1854.5	1813.9	1793.6	1793.6	1798.7	1803.7
20°	1925.5	1910.3	1857.0	1796.1	1750.5	1735.2	1740.4	1750.5	1755.5
22.5°	1874.8	1857.0	1796.1	1727.6	1679.4	1666.7	1679.4	1692.2	1697.2
25°	1816.4	1796.1	1725.1	1654.0	1603.4	1588.1	1605.8	1626.1	1633.8
27.5°	1737.8	1714.9	1649.0	1567.8	1517.0	1509.4	1529.7	1552.6	1557.6
30°	1644.0	1618.5	1545.0	1468.8	1423.2	1420.6	1443.5	1463.8	1471.4
32.5°	1529.7	1507.0	1443.5	1367.4	1326.8	1326.8	1349.7	1367.4	1375.0
35°	1408.0	1382.6	1326.8	1263.4	1230.4	1232.9	1255.8	1268.5	1276.1
37.5°	1263.4	1255.8	1212.6	1159.4	1136.5	1141.6	1159.4	1169.5	1177.1
40°	1146.7	1126.4	1098.5	1055.3	1040.1	1045.3	1063.0	1073.1	1078.2
42.5°	1019.8	1007.1	984.4	953.9	943.7	951.3	966.6	974.2	971.6
45°	898.0	895.6	872.7	855.0	849.8	860.0	870.1	877.8	880.3
47.5°	809.3	799.2	778.9	766.2	761.0	771.2	781.3	786.5	786.5
50°	723.0	712.8	692.5	679.9	674.8	684.9	692.5	697.7	692.5
52.5°	636.8	626.6	608.9	593.7	591.1	596.1	598.7	601.3	606.3
55°	568.3	558.1	537.8	520.1	514.9	517.5	514.9	514.9	512.5
57.5°	502.3	492.2	471.9	451.6	444.0	441.4	433.8	431.3	428.7
60°	444.0	431.3	411.0	388.1	378.1	367.9	355.2	347.6	347.6
62.5°	388.1	375.5	352.6	332.3	317.1	299.3	279.1	269.0	269.0
65°	334.9	324.7	299.3	276.5	256.2	233.4	210.6	205.5	210.6
67.5°	284.1	274.0	248.7	225.8	200.5	172.5	152.3	152.3	157.3
70°	238.5	228.3	205.5	177.6	149.7	121.8	106.5	106.5	106.5
72.5°	195.3	185.2	159.9	134.4	106.5	78.6	71.1	73.5	71.1
75°	152.3	144.6	121.8	93.8	68.5	48.2	45.6	43.2	45.6
77.5°	114.1	106.5	86.2	60.9	38.0	27.9	25.3	25.3	25.3
80°	78.6	71.1	55.8	35.5	20.3	12.7	12.7	12.7	12.7
82.5°	48.2	40.6	30.5	17.7	7.6	7.6	7.6	7.6	7.6
85°	22.9	17.7	12.7	5.0	2.6	2.6	2.6	2.6	2.6
87.5°	5.0	5.0	2.6	2.6	0.0	2.6	2.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)