

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582753

Luminaire Tested: **HCC6S50D010MB-HM64560835-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MB-HM64560835-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4616.5 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582753
CATALOG NUMBER: HCC6S50D010MB-HM64560835-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P582753

CATALOG NUMBER: HCC6S50D010MB-HM64560835-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89	89	89	89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78	78	78	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69	69	69	69
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61	61	61	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54	54	54	54
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44	44	44	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40	40	40	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37	37	37	37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34	34	34	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	142012	142012	142012
5°	144766	141756	138548
10°	149680	139944	134066
15°	154263	137509	129865
20°	156650	131786	123071
25°	153831	122753	114605
30°	146225	111859	105168
35°	131430	99970	94850
40°	113420	87607	84744
45°	96041	75419	73442
50°	82351	63708	63085
55°	71395	53628	51535
60°	62320	43549	36751
65°	54831	33544	20326
70°	47300	22183	9922
75°	40117	10802	3855
80°	31065	4578	2305
85°	18367	2327	2327



TEST NUMBER: P582753
 CATALOG NUMBER: HCC6S50D010MB-HM64560835-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.5	5.3
10°-20°	691.3	15.0
20°-30°	973.5	21.1
30°-40°	994.7	21.5
40°-50°	802.0	17.4
50°-60°	537.9	11.7
60°-70°	272.2	5.9
70°-80°	87.0	1.9
80°-90°	13.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1909.3	41.4
0°-40°	2903.9	62.9
0°-60°	4243.8	91.9
0°-90°	4616.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4616.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2590	2590	2590	2590	2590	
5°	2631	2612	2576	2536	2518	253
15°	2718	2609	2423	2314	2288	767
25°	2543	2343	2029	1906	1895	1164
35°	1964	1785	1494	1410	1417	1222
45°	1239	1140	973	940	947	963
55°	747	663	561	536	539	672
65°	423	350	259	171	157	422
75°	189	135	51	18	18	203
85°	29	14	4	4	4	39
90°	0	0	0	0	0	



TEST NUMBER: P582753

CATALOG NUMBER: HCC6S50D010MB-HM64560835-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2590.5	2590.5	2590.5	2590.5	2590.5	2590.5	2590.5	2590.5	2590.5
2.5°	2601.5	2597.8	2594.2	2586.9	2576.0	2565.0	2557.8	2550.5	2546.8
5°	2630.7	2623.4	2612.4	2597.8	2576.0	2550.5	2536.0	2521.3	2517.7
7.5°	2670.7	2656.2	2627.0	2594.2	2557.8	2521.3	2495.8	2481.3	2470.3
10°	2688.9	2663.4	2623.4	2568.7	2514.0	2470.3	2437.6	2415.6	2408.4
12.5°	2703.5	2674.4	2616.0	2543.2	2470.3	2412.1	2375.6	2357.4	2350.1
15°	2718.1	2688.9	2608.8	2514.0	2422.9	2353.7	2313.7	2295.4	2288.2
17.5°	2718.1	2678.0	2583.3	2463.1	2353.7	2269.9	2229.8	2211.7	2208.0
20°	2685.2	2641.5	2525.0	2382.9	2259.0	2164.3	2127.8	2116.9	2109.6
22.5°	2623.4	2572.3	2441.1	2280.9	2146.0	2054.9	2014.9	2007.6	2000.3
25°	2543.2	2492.1	2342.7	2171.5	2029.4	1938.4	1905.5	1898.3	1894.7
27.5°	2441.1	2386.6	2229.8	2054.9	1901.9	1814.5	1785.3	1785.3	1781.7
30°	2310.0	2248.0	2095.1	1920.2	1767.1	1686.9	1665.1	1665.1	1661.4
32.5°	2149.7	2087.8	1949.2	1781.7	1635.9	1552.2	1533.9	1541.2	1537.5
35°	1963.9	1912.9	1785.3	1621.4	1493.8	1417.3	1410.0	1417.3	1417.3
37.5°	1778.0	1730.6	1621.4	1479.3	1359.1	1289.8	1289.8	1300.8	1297.1
40°	1584.9	1548.5	1446.5	1322.6	1224.2	1176.9	1169.5	1180.5	1184.2
42.5°	1402.8	1373.6	1286.2	1184.2	1096.7	1049.3	1060.3	1067.5	1071.2
45°	1238.8	1209.7	1140.4	1034.8	972.8	940.1	940.1	950.9	947.3
47.5°	1093.0	1071.2	1002.0	899.9	845.4	830.7	838.0	845.4	845.4
50°	965.6	932.8	867.2	787.0	747.0	728.7	736.0	739.7	739.7
52.5°	845.4	823.4	757.8	685.0	648.6	637.6	637.6	641.3	641.3
55°	747.0	721.5	663.1	590.3	561.1	546.6	535.6	531.9	539.2
57.5°	652.1	630.3	575.7	506.4	473.7	459.1	437.2	429.9	437.2
60°	568.4	550.2	495.5	429.9	397.2	368.0	342.5	328.0	335.2
62.5°	495.5	473.7	419.0	364.3	328.0	295.1	255.1	233.1	244.1
65°	422.7	404.5	349.8	295.1	258.6	218.6	171.2	156.7	156.7
67.5°	357.0	338.8	287.8	240.5	196.8	149.4	105.7	102.0	105.7
70°	295.1	276.9	233.1	185.8	138.4	91.1	61.9	61.9	61.9
72.5°	244.1	222.3	182.2	134.9	87.4	47.4	32.8	36.5	36.5
75°	189.4	171.2	134.9	91.1	51.0	21.8	18.2	18.2	18.2
77.5°	142.1	127.5	94.7	58.3	25.5	7.3	7.3	7.3	7.3
80°	98.4	83.9	61.9	36.5	14.5	7.3	7.3	7.3	7.3
82.5°	58.3	51.0	36.5	18.2	7.3	3.7	3.7	3.7	3.7
85°	29.2	25.5	14.5	7.3	3.7	3.7	3.7	3.7	3.7
87.5°	7.3	7.3	3.7	3.7	0.0	3.7	3.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)