

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582752

Luminaire Tested: **HCC6S50D010MW-HM64560835-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MW-HM64560835-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5731.4 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582752
CATALOG NUMBER: HCC6S50D010MW-HM64560835-61WDWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582752

CATALOG NUMBER: HCC6S50D010MW-HM64560835-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91																												
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																												
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																												
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69																												
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63																												
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58																												
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																												
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50																												
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46																												
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213760
5°	215584
10°	223348
15°	242606
20°	252360
25°	241375
30°	208304
35°	149988
40°	84501
45°	43795
50°	26106
55°	18809
60°	15975
65°	18433
70°	23353
75°	24697
80°	24151
85°	22958



TEST NUMBER: P582752
 CATALOG NUMBER: HCC6S50D010MW-HM64560835-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.0	6.6
10°-20°	1205.7	21.0
20°-30°	1802.1	31.4
30°-40°	1377.5	24.0
40°-50°	481.2	8.4
50°-60°	183.4	3.2
60°-70°	143.8	2.5
70°-80°	121.7	2.1
80°-90°	39.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3384.7	59.1
0°-40°	4762.3	83.1
0°-60°	5426.8	94.7
0°-90°	5731.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5731.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3899	
5°	3918	377
15°	4275	1206
25°	3990	1802
35°	2241	1378
45°	565	481
55°	197	183
65°	142	144
75°	117	122
85°	36	39
90°	0	



TEST NUMBER: P582752
CATALOG NUMBER: HCC6S50D010MW-HM64560835-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3899.3
2.5°	3888.4
5°	3917.6
7.5°	3957.6
10°	4012.3
12.5°	4136.2
15°	4274.7
17.5°	4358.6
20°	4325.8
22.5°	4194.6
25°	3990.5
27.5°	3698.9
30°	3290.7
32.5°	2802.4
35°	2241.2
37.5°	1661.8
40°	1180.8
42.5°	827.3
45°	564.9
47.5°	397.2
50°	306.1
52.5°	240.6
55°	196.8
57.5°	160.4
60°	145.7
62.5°	142.1
65°	142.1
67.5°	149.4
70°	145.7
72.5°	134.9
75°	116.6
77.5°	98.4
80°	76.5
82.5°	54.7
85°	36.5
87.5°	14.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)