

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582783

Luminaire Tested: **HCC6S50D010MB-HM64560927-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MB-HM64560927-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4014.1 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582783
CATALOG NUMBER: HCC6S50D010MB-HM64560927-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P582783

CATALOG NUMBER: HCC6S50D010MB-HM64560927-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	112305	112305	112305
5°	113465	112431	111699
10°	115078	112089	110892
15°	117787	111385	110318
20°	118882	108072	108387
25°	116275	102641	104583
30°	110125	95344	98566
35°	99722	87147	90380
40°	86848	78776	81660
45°	73690	69728	72232
50°	65260	60911	62505
55°	57479	52089	51831
60°	51509	43856	40337
65°	45971	35179	28914
70°	40456	25389	18080
75°	34122	15356	10230
80°	26298	6787	4262
85°	15222	1698	1698



TEST NUMBER: P582783
 CATALOG NUMBER: HCC6S50D010MB-HM64560927-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.4	4.8
10°-20°	558.9	13.9
20°-30°	807.9	20.1
30°-40°	850.0	21.2
40°-50°	714.6	17.8
50°-60°	501.5	12.5
60°-70°	275.9	6.9
70°-80°	98.0	2.4
80°-90°	12.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1561.2	38.9
0°-40°	2411.2	60.1
0°-60°	3627.4	90.4
0°-90°	4014.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4014.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2049	2049	2049	2049	2049	
5°	2062	2057	2043	2035	2030	197
15°	2075	2040	1963	1938	1944	586
25°	1922	1826	1697	1700	1729	879
35°	1490	1404	1302	1329	1350	924
45°	950	924	899	921	932	746
55°	601	569	545	545	542	541
65°	354	317	271	223	223	353
75°	161	129	72	48	48	173
85°	24	14	3	3	3	33
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582783

CATALOG NUMBER: HCC6S50D010MB-HM64560927-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6
2.5°	2048.6	2048.6	2045.8	2045.8	2040.5	2040.5	2037.8	2037.8	2037.8
5°	2061.9	2061.9	2056.6	2048.6	2043.1	2035.1	2035.1	2032.4	2029.8
7.5°	2070.1	2067.3	2059.3	2048.6	2035.1	2021.6	2016.3	2019.0	2016.3
10°	2067.3	2061.9	2051.2	2029.8	2013.6	1994.8	1992.1	1989.5	1992.1
12.5°	2072.7	2064.6	2043.1	2016.3	1989.5	1968.0	1965.3	1965.3	1968.0
15°	2075.4	2067.3	2040.5	2000.3	1962.6	1941.1	1938.5	1941.1	1943.8
17.5°	2067.3	2056.6	2016.3	1962.6	1919.7	1898.2	1898.2	1903.5	1909.0
20°	2037.8	2021.6	1965.3	1900.8	1852.5	1836.5	1841.8	1852.5	1857.9
22.5°	1984.1	1965.3	1900.8	1828.4	1777.4	1763.9	1777.4	1790.8	1796.2
25°	1922.3	1900.8	1825.7	1750.5	1696.9	1680.7	1699.5	1721.0	1729.0
27.5°	1839.2	1815.0	1745.2	1659.2	1605.6	1597.4	1618.9	1643.1	1648.4
30°	1739.7	1712.9	1635.1	1554.6	1506.2	1503.5	1527.6	1549.1	1557.1
32.5°	1618.9	1594.8	1527.6	1447.1	1404.2	1404.2	1428.3	1447.1	1455.2
35°	1490.1	1463.3	1404.2	1337.0	1302.2	1304.9	1329.0	1342.4	1350.5
37.5°	1337.0	1329.0	1283.4	1226.9	1202.8	1208.2	1226.9	1237.7	1245.7
40°	1213.6	1192.1	1162.6	1116.9	1100.8	1106.1	1124.9	1135.6	1141.1
42.5°	1079.3	1065.9	1041.8	1009.5	998.8	1006.8	1023.0	1031.0	1028.3
45°	950.5	947.8	923.5	904.8	899.4	910.2	920.9	929.0	931.7
47.5°	856.5	845.7	824.2	810.9	805.4	816.2	826.9	832.3	832.3
50°	765.2	754.4	732.9	719.6	714.2	724.9	732.9	738.4	732.9
52.5°	673.9	663.1	644.4	628.3	625.6	630.9	633.6	636.3	641.6
55°	601.4	590.6	569.2	550.3	545.0	547.7	545.0	545.0	542.3
57.5°	531.6	520.8	499.3	478.0	469.8	467.2	459.1	456.5	453.7
60°	469.8	456.5	435.0	410.8	400.0	389.3	375.9	367.9	367.9
62.5°	410.8	397.4	373.2	351.7	335.6	316.9	295.4	284.6	284.6
65°	354.4	343.7	316.9	292.7	271.2	246.9	222.9	217.4	222.9
67.5°	300.7	289.9	263.1	238.9	212.1	182.6	161.1	161.1	166.4
70°	252.4	241.6	217.4	187.9	158.4	128.8	112.8	112.8	112.8
72.5°	206.7	196.0	169.1	142.3	112.8	83.3	75.2	77.8	75.2
75°	161.1	153.1	128.8	99.3	72.5	51.0	48.3	45.6	48.3
77.5°	120.8	112.8	91.3	64.5	40.3	29.5	26.8	26.8	26.8
80°	83.3	75.2	59.0	37.6	21.5	13.5	13.5	13.5	13.5
82.5°	51.0	43.0	32.2	18.8	8.0	8.0	8.0	8.0	8.0
85°	24.2	18.8	13.5	5.3	2.7	2.7	2.7	2.7	2.7
87.5°	5.3	5.3	2.7	2.7	0.0	2.7	2.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)