

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582674

Luminaire Tested: **HCC6S45D010SL-HM64560935-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560935-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4569.2 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582674
CATALOG NUMBER: HCC6S45D010SL-HM64560935-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582674

CATALOG NUMBER: HCC6S45D010SL-HM64560935-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	124074	124074	124074
5°	124719	125390	125390
10°	128210	125989	125471
15°	132282	126709	126709
20°	133822	123806	126664
25°	131149	117612	123170
30°	124044	109289	115701
35°	112263	99950	104875
40°	97662	90427	93933
45°	83458	80598	83458
50°	73226	70616	73499
55°	63902	59496	61847
60°	56487	49426	48757
65°	50122	38980	33415
70°	44238	27521	20148
75°	37660	15568	9743
80°	28065	4862	2873
85°	15410	1887	1887



TEST NUMBER: P582674
 CATALOG NUMBER: HCC6S45D010SL-HM64560935-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.1	4.8
10°-20°	635.2	13.9
20°-30°	927.7	20.3
30°-40°	972.9	21.3
40°-50°	819.7	17.9
50°-60°	574.3	12.6
60°-70°	307.9	6.7
70°-80°	103.2	2.3
80°-90°	11.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1780.0	39.0
0°-40°	2752.9	60.2
0°-60°	4146.9	90.8
0°-90°	4569.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4569.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2263	2263	2263	2263	2263	
5°	2266	2276	2279	2279	2279	218
15°	2331	2300	2233	2220	2233	657
25°	2168	2076	1944	1978	2036	993
35°	1678	1592	1494	1536	1567	1041
45°	1076	1058	1040	1067	1076	839
55°	669	647	622	635	647	602
65°	386	353	300	248	258	386
75°	178	138	74	46	46	189
85°	24	12	3	3	3	34
90°	0	0	0	0	0	



TEST NUMBER: P582674

CATALOG NUMBER: HCC6S45D010SL-HM64560935-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2263.3	2263.3	2263.3	2263.3	2263.3	2263.3	2263.3	2263.3	2263.3
2.5°	2247.9	2247.9	2254.0	2260.3	2266.4	2266.4	2269.4	2272.5	2269.4
5°	2266.4	2266.4	2275.5	2278.6	2278.6	2275.5	2278.6	2278.6	2278.6
7.5°	2293.9	2287.8	2290.9	2284.8	2278.6	2275.5	2272.5	2272.5	2272.5
10°	2303.2	2297.0	2290.9	2278.6	2263.3	2254.0	2251.0	2254.0	2254.0
12.5°	2315.4	2309.3	2293.9	2269.4	2251.0	2235.6	2232.6	2238.8	2238.8
15°	2330.8	2324.7	2300.0	2260.3	2232.6	2217.3	2220.4	2226.5	2232.6
17.5°	2330.8	2318.4	2278.6	2226.5	2192.7	2177.4	2189.6	2205.0	2214.2
20°	2293.9	2281.7	2226.5	2162.1	2122.2	2113.0	2134.5	2162.1	2171.2
22.5°	2244.9	2220.4	2156.0	2079.3	2036.3	2036.3	2066.9	2100.7	2113.0
25°	2168.2	2149.8	2076.2	1987.3	1944.4	1941.3	1978.0	2024.0	2036.3
27.5°	2082.3	2057.8	1978.0	1886.1	1840.1	1843.1	1883.0	1929.0	1941.3
30°	1959.6	1929.0	1858.5	1769.5	1726.5	1738.9	1778.7	1812.4	1827.8
32.5°	1821.7	1794.1	1729.7	1646.9	1610.1	1622.3	1656.0	1686.8	1699.0
35°	1677.5	1646.9	1591.6	1518.1	1493.5	1505.8	1536.4	1561.0	1567.1
37.5°	1514.9	1493.5	1453.7	1395.4	1377.0	1392.4	1416.9	1432.2	1438.3
40°	1364.7	1346.3	1312.6	1269.7	1263.6	1275.8	1300.3	1309.5	1312.6
42.5°	1217.5	1202.2	1180.7	1150.0	1150.0	1162.3	1183.8	1189.9	1192.9
45°	1076.5	1067.2	1058.0	1033.5	1039.6	1055.0	1067.2	1076.5	1076.5
47.5°	953.8	956.8	944.6	926.2	932.3	947.7	956.8	966.1	966.1
50°	858.6	849.5	837.2	818.9	828.0	840.3	852.5	858.6	861.8
52.5°	748.3	745.2	736.1	714.6	720.7	726.8	739.1	748.3	751.3
55°	668.6	659.3	647.1	622.5	622.5	628.7	634.8	640.9	647.1
57.5°	591.9	582.6	564.3	536.6	533.6	533.6	530.5	536.6	545.9
60°	515.2	512.1	484.6	460.1	450.8	441.6	429.3	432.4	444.7
62.5°	447.7	441.6	417.1	386.4	368.0	352.7	337.4	334.3	346.5
65°	386.4	380.3	352.7	322.0	300.5	273.0	248.4	248.4	257.6
67.5°	331.3	318.9	294.4	260.6	233.1	199.3	174.8	181.0	184.0
70°	276.0	266.9	239.2	205.5	171.7	138.1	122.7	125.7	125.7
72.5°	227.0	214.7	187.1	153.3	119.6	88.9	82.8	79.8	79.8
75°	177.8	165.6	138.1	104.3	73.5	52.1	46.0	46.0	46.0
77.5°	128.8	119.6	95.0	64.4	39.9	24.5	21.5	18.4	18.4
80°	88.9	79.8	58.3	33.8	15.4	9.1	9.1	9.1	9.1
82.5°	52.1	42.9	27.6	15.4	6.1	3.0	3.0	3.0	3.0
85°	24.5	18.4	12.3	6.1	3.0	3.0	3.0	3.0	3.0
87.5°	3.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)