

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582782

Luminaire Tested: **HCC6W50D010SL-HM64560927-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010SL-HM64560927-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.6 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582782
CATALOG NUMBER: HCC6W50D010SL-HM64560927-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582782

CATALOG NUMBER: HCC6W50D010SL-HM64560927-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	108632	108632	108632
5°	109195	109790	109790
10°	112256	110307	109862
15°	115812	110943	110943
20°	117167	108399	110907
25°	114823	102974	107849
30°	108612	95692	101307
35°	98297	87509	91825
40°	85503	79163	82240
45°	73062	70565	73062
50°	64117	61832	64348
55°	55941	52089	54144
60°	49459	43275	42694
65°	43896	34128	29264
70°	38724	24091	17647
75°	33000	13662	8536
80°	24561	4262	2526
85°	13523	1698	1698



TEST NUMBER: P582782
 CATALOG NUMBER: HCC6W50D010SL-HM64560927-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.1	4.8
10°-20°	556.1	13.9
20°-30°	812.3	20.3
30°-40°	851.9	21.3
40°-50°	717.7	17.9
50°-60°	502.8	12.6
60°-70°	269.6	6.7
70°-80°	90.4	2.3
80°-90°	9.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1558.5	39.0
0°-40°	2410.3	60.2
0°-60°	3630.8	90.8
0°-90°	4000.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1982	1982	1982	1982	1982	
5°	1984	1992	1995	1995	1995	191
15°	2041	2014	1955	1944	1955	576
25°	1898	1818	1702	1732	1783	870
35°	1469	1394	1308	1345	1372	912
45°	942	926	910	934	942	734
55°	585	566	545	556	566	527
65°	338	309	263	218	226	338
75°	156	121	64	40	40	165
85°	22	11	3	3	3	30
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582782

CATALOG NUMBER: HCC6W50D010SL-HM64560927-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1981.6	1981.6	1981.6	1981.6	1981.6	1981.6	1981.6	1981.6	1981.6
2.5°	1968.1	1968.1	1973.6	1978.9	1984.3	1984.3	1987.0	1989.6	1987.0
5°	1984.3	1984.3	1992.3	1995.1	1995.1	1992.3	1995.1	1995.1	1995.1
7.5°	2008.4	2003.1	2005.8	2000.4	1995.1	1992.3	1989.6	1989.6	1989.6
10°	2016.6	2011.1	2005.8	1995.1	1981.6	1973.6	1970.9	1973.6	1973.6
12.5°	2027.3	2021.9	2008.4	1987.0	1970.9	1957.5	1954.8	1960.1	1960.1
15°	2040.6	2035.3	2013.8	1978.9	1954.8	1941.3	1944.0	1949.4	1954.8
17.5°	2040.6	2029.9	1995.1	1949.4	1919.8	1906.5	1917.1	1930.6	1938.6
20°	2008.4	1997.8	1949.4	1893.0	1858.1	1850.0	1868.8	1893.0	1901.1
22.5°	1965.5	1944.0	1887.6	1820.5	1783.0	1783.0	1809.8	1839.3	1850.0
25°	1898.3	1882.3	1817.8	1740.0	1702.4	1699.7	1731.9	1772.2	1783.0
27.5°	1823.2	1801.7	1731.9	1651.4	1611.1	1613.7	1648.7	1688.9	1699.7
30°	1715.8	1688.9	1627.2	1549.4	1511.7	1522.4	1557.4	1586.9	1600.4
32.5°	1594.9	1570.8	1514.4	1441.9	1409.6	1420.4	1449.9	1476.8	1487.6
35°	1468.8	1441.9	1393.6	1329.1	1307.6	1318.4	1345.3	1366.8	1372.1
37.5°	1326.5	1307.6	1272.8	1221.7	1205.6	1219.0	1240.5	1254.0	1259.3
40°	1194.8	1178.8	1149.2	1111.7	1106.2	1117.0	1138.5	1146.5	1149.2
42.5°	1066.0	1052.5	1033.7	1006.9	1006.9	1017.7	1036.4	1041.9	1044.5
45°	942.4	934.4	926.4	904.9	910.2	923.7	934.4	942.4	942.4
47.5°	835.1	837.8	827.1	810.9	816.3	829.7	837.8	845.8	845.8
50°	751.8	743.8	733.0	716.9	725.0	735.8	746.5	751.8	754.5
52.5°	655.2	652.5	644.5	625.6	631.0	636.3	647.1	655.2	657.8
55°	585.3	577.3	566.5	545.0	545.0	550.5	555.8	561.2	566.5
57.5°	518.2	510.2	494.0	469.9	467.2	467.2	464.5	469.9	478.0
60°	451.1	448.4	424.2	402.7	394.7	386.7	375.9	378.6	389.4
62.5°	392.0	386.7	365.2	338.4	322.2	308.8	295.4	292.7	303.4
65°	338.4	332.9	308.8	281.9	263.1	238.9	217.5	217.5	225.6
67.5°	289.9	279.3	257.8	228.3	204.1	174.6	153.1	158.4	161.1
70°	241.6	233.6	209.4	179.9	150.3	120.8	107.4	110.1	110.1
72.5°	198.6	188.0	163.8	134.3	104.8	77.8	72.5	69.8	69.8
75°	155.8	145.0	120.8	91.3	64.5	45.7	40.3	40.3	40.3
77.5°	112.8	104.8	83.3	56.3	35.0	21.5	18.8	16.1	16.1
80°	77.8	69.8	51.0	29.5	13.5	8.0	8.0	8.0	8.0
82.5°	45.7	37.6	24.2	13.5	5.3	2.7	2.7	2.7	2.7
85°	21.5	16.1	10.7	5.3	2.7	2.7	2.7	2.7	2.7
87.5°	2.7	2.7	2.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)