

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582675

Luminaire Tested: **HCC6W45D010SL-HM64560935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582675
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010SL-HM64560935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4584.6 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582675
CATALOG NUMBER: HCC6W45D010SL-HM64560935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582675

CATALOG NUMBER: HCC6W45D010SL-HM64560935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	128263	128263	128263
5°	129595	128417	127570
10°	131433	128020	126657
15°	134530	127220	126000
20°	135783	123438	123794
25°	132806	117225	119444
30°	125785	108897	112581
35°	113896	99528	103222
40°	99186	89969	93260
45°	84156	79644	82489
50°	74531	69567	71401
55°	65651	59496	59209
60°	58833	50095	46060
65°	52509	40173	33013
70°	46194	28995	20645
75°	38973	17538	11692
80°	29991	7735	4862
85°	17360	1887	1887



TEST NUMBER: P582675

CATALOG NUMBER: HCC6W45D010SL-HM64560935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.1	4.8
10°-20°	638.3	13.9
20°-30°	922.7	20.1
30°-40°	970.9	21.2
40°-50°	816.2	17.8
50°-60°	572.8	12.5
60°-70°	315.1	6.9
70°-80°	111.9	2.4
80°-90°	14.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1783.1	38.9
0°-40°	2754.0	60.1
0°-60°	4143.0	90.4
0°-90°	4584.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4584.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2340	2340	2340	2340	2340	
5°	2355	2349	2334	2324	2318	225
15°	2370	2330	2242	2214	2220	669
25°	2196	2085	1938	1941	1975	1004
35°	1702	1604	1487	1518	1542	1055
45°	1086	1055	1027	1052	1064	852
55°	687	650	622	622	620	618
65°	405	362	310	254	254	403
75°	184	147	83	55	55	197
85°	28	15	3	3	3	38
90°	0	0	0	0	0	



TEST NUMBER: P582675

CATALOG NUMBER: HCC6W45D010SL-HM64560935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2339.7	2339.7	2339.7	2339.7	2339.7	2339.7	2339.7	2339.7	2339.7
2.5°	2339.7	2339.7	2336.6	2336.6	2330.5	2330.5	2327.5	2327.5	2327.5
5°	2355.0	2355.0	2348.9	2339.7	2333.6	2324.4	2324.4	2321.2	2318.2
7.5°	2364.2	2361.1	2352.0	2339.7	2324.4	2309.1	2303.0	2306.0	2303.0
10°	2361.1	2355.0	2342.7	2318.2	2299.8	2278.3	2275.3	2272.2	2275.3
12.5°	2367.3	2358.1	2333.6	2303.0	2272.2	2247.7	2244.7	2244.7	2247.7
15°	2370.4	2361.1	2330.5	2284.5	2241.6	2217.1	2213.9	2217.1	2220.1
17.5°	2361.1	2348.9	2303.0	2241.6	2192.5	2167.9	2167.9	2174.2	2180.3
20°	2327.5	2309.1	2244.7	2171.0	2115.9	2097.4	2103.5	2115.9	2122.0
22.5°	2266.1	2244.7	2171.0	2088.3	2030.0	2014.6	2030.0	2045.4	2051.5
25°	2195.6	2171.0	2085.1	1999.4	1938.0	1919.6	1941.1	1965.6	1974.7
27.5°	2100.5	2072.9	1993.2	1895.1	1833.8	1824.5	1849.1	1876.7	1882.8
30°	1987.1	1956.4	1867.4	1775.5	1720.3	1717.2	1744.8	1769.4	1778.5
32.5°	1849.1	1821.4	1744.8	1652.8	1603.7	1603.7	1631.3	1652.8	1662.0
35°	1701.9	1671.2	1603.7	1527.1	1487.2	1490.3	1517.9	1533.2	1542.4
37.5°	1527.1	1517.9	1465.8	1401.4	1373.8	1379.9	1401.4	1413.6	1422.8
40°	1386.0	1361.5	1327.7	1275.6	1257.2	1263.3	1284.8	1297.1	1303.2
42.5°	1232.7	1217.3	1189.8	1152.9	1140.7	1149.9	1168.3	1177.5	1174.4
45°	1085.5	1082.4	1054.9	1033.4	1027.3	1039.5	1051.8	1061.0	1064.0
47.5°	978.2	966.0	941.4	926.1	920.0	932.2	944.5	950.6	950.6
50°	873.9	861.7	837.2	821.8	815.7	827.9	837.2	843.3	837.2
52.5°	769.7	757.4	735.9	717.5	714.5	720.6	723.6	726.8	732.9
55°	686.9	674.6	650.1	628.6	622.5	625.6	622.5	622.5	619.5
57.5°	607.1	594.9	570.3	545.8	536.6	533.6	524.3	521.3	518.2
60°	536.6	521.3	496.8	469.2	456.9	444.7	429.3	420.1	420.1
62.5°	469.2	453.8	426.3	401.8	383.3	361.9	337.4	325.0	325.0
65°	404.8	392.5	361.9	334.2	309.7	282.1	254.5	248.3	254.5
67.5°	343.5	331.1	300.5	273.0	242.2	208.6	184.0	184.0	190.1
70°	288.2	276.0	248.3	214.7	180.9	147.2	128.8	128.8	128.8
72.5°	236.1	223.8	193.2	162.6	128.8	95.0	85.9	88.9	85.9
75°	184.0	174.8	147.2	113.4	82.8	58.3	55.2	52.1	55.2
77.5°	137.9	128.8	104.3	73.5	46.0	33.8	30.6	30.6	30.6
80°	95.0	85.9	67.4	42.9	24.5	15.4	15.4	15.4	15.4
82.5°	58.3	49.0	36.8	21.5	9.1	9.1	9.1	9.1	9.1
85°	27.6	21.5	15.4	6.1	3.0	3.0	3.0	3.0	3.0
87.5°	6.1	6.1	3.0	3.0	0.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)