

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582808

Luminaire Tested: **HCC6W50D010MB-HM64560930-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560930-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4439.5 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582808
CATALOG NUMBER: HCC6W50D010MB-HM64560930-61WWW

Luminous Intensity Polar Plot





TEST NUMBER: P582808

CATALOG NUMBER: HCC6W50D010MB-HM64560930-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	130653	130653	130653
5°	136446	130266	124268
10°	140167	128026	116776
15°	143633	125245	109405
20°	144277	119570	100488
25°	141250	111944	92159
30°	134014	102940	84469
35°	121713	92521	75777
40°	106049	82412	68178
45°	91761	72116	59936
50°	80151	62096	52527
55°	70822	54574	45074
60°	63657	47836	39043
65°	57010	41613	37864
70°	50906	35471	35471
75°	44141	29886	33296
80°	35453	25319	30402
85°	24216	22203	26229



TEST NUMBER: P582808
 CATALOG NUMBER: HCC6W50D010MB-HM64560930-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.0	5.0
10°-20°	622.6	14.0
20°-30°	867.7	19.5
30°-40°	894.1	20.1
40°-50°	741.0	16.7
50°-60°	532.5	12.0
60°-70°	339.1	7.6
70°-80°	174.2	3.9
80°-90°	44.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1714.4	38.6
0°-40°	2608.4	58.8
0°-60°	3881.9	87.4
0°-90°	4439.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4439.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2383	2383	2383	2383	2383	
5°	2480	2441	2367	2290	2258	238
15°	2531	2435	2207	2005	1928	713
25°	2335	2175	1851	1614	1524	1070
35°	1819	1671	1382	1200	1132	1130
45°	1184	1100	930	812	773	916
55°	741	680	571	507	472	667
65°	440	391	321	279	292	440
75°	208	180	141	148	157	222
85°	38	35	35	38	42	49
90°	0	0	0	0	0	



TEST NUMBER: P582808

CATALOG NUMBER: HCC6W50D010MB-HM64560930-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2383.3	2383.3	2383.3	2383.3	2383.3	2383.3	2383.3	2383.3	2383.3
2.5°	2428.1	2418.6	2405.7	2392.9	2373.7	2351.3	2332.0	2325.5	2315.9
5°	2479.5	2466.6	2441.0	2408.9	2367.2	2325.5	2290.2	2267.8	2258.2
7.5°	2511.6	2495.6	2460.3	2405.7	2344.8	2283.8	2232.6	2200.4	2187.6
10°	2518.0	2501.9	2453.9	2380.1	2299.9	2216.5	2152.4	2113.9	2097.8
12.5°	2527.6	2505.1	2444.2	2357.6	2255.0	2158.7	2078.6	2030.4	2014.4
15°	2530.8	2505.1	2434.6	2328.7	2206.8	2091.4	2004.7	1947.0	1927.7
17.5°	2518.0	2489.1	2405.7	2277.4	2139.5	2017.6	1915.0	1854.1	1828.3
20°	2473.1	2441.0	2344.8	2200.4	2049.6	1921.4	1815.6	1751.4	1722.5
22.5°	2415.4	2373.7	2264.6	2110.6	1953.5	1818.7	1712.9	1648.7	1619.9
25°	2335.2	2296.7	2174.8	2011.2	1850.7	1709.6	1613.5	1546.0	1523.6
27.5°	2242.1	2197.3	2072.2	1908.5	1744.9	1603.8	1510.9	1449.8	1421.0
30°	2117.1	2075.4	1950.2	1786.6	1626.2	1494.8	1398.5	1347.2	1334.4
32.5°	1969.4	1934.2	1812.4	1658.4	1504.4	1382.5	1302.3	1247.7	1235.0
35°	1818.7	1777.1	1671.2	1526.8	1382.5	1273.5	1199.7	1151.6	1132.3
37.5°	1655.2	1616.7	1526.8	1398.5	1270.2	1167.5	1103.4	1061.7	1042.5
40°	1481.9	1453.1	1369.6	1267.0	1151.6	1061.7	1007.2	972.0	952.7
42.5°	1321.5	1292.7	1235.0	1138.7	1042.5	962.3	914.2	882.1	866.0
45°	1183.6	1158.0	1100.2	1016.8	930.2	862.8	811.6	789.0	773.1
47.5°	1045.7	1032.9	981.5	904.5	824.3	766.6	731.4	705.6	692.9
50°	939.8	923.8	875.7	795.5	728.1	683.2	651.2	628.6	615.9
52.5°	830.8	814.8	769.8	702.5	647.9	606.2	574.2	555.0	542.1
55°	741.0	728.1	680.0	619.1	571.0	535.7	506.8	484.3	471.6
57.5°	657.6	644.7	599.8	542.1	500.4	468.3	442.6	423.4	407.3
60°	580.6	571.0	526.0	471.6	436.3	404.1	381.7	365.6	356.1
62.5°	513.3	494.0	455.5	407.3	375.3	349.6	327.1	317.6	323.9
65°	439.5	429.8	391.4	349.6	320.8	295.1	279.1	285.4	291.9
67.5°	378.5	365.6	333.6	295.1	269.4	250.3	240.6	253.4	256.6
70°	317.6	304.7	275.9	243.8	221.3	208.4	208.4	218.1	221.3
72.5°	259.8	250.3	224.5	198.9	182.8	173.3	179.6	186.0	189.2
75°	208.4	198.9	179.6	157.2	141.1	141.1	147.5	154.0	157.2
77.5°	160.4	154.0	134.8	118.7	112.3	112.3	118.7	121.9	125.1
80°	112.3	105.8	96.3	86.6	80.2	86.6	93.1	93.1	96.3
82.5°	73.8	70.6	64.1	57.8	57.8	60.9	64.1	67.3	67.3
85°	38.5	38.5	35.3	32.1	35.3	38.5	38.5	41.7	41.7
87.5°	12.9	12.9	12.9	12.9	16.1	16.1	16.1	16.1	16.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)