

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582844

Luminaire Tested: **HCC6S50D010BZ-HM64560940-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582844  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S50D010BZ-HM64560940-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4633.4 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582844  
CATALOG NUMBER: HCC6S50D010BZ-HM64560940-61WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582844

CATALOG NUMBER: HCC6S50D010BZ-HM64560940-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	136360	136360	136360
5°	142406	135962	129694
10°	146290	133620	121880
15°	149904	130716	114189
20°	150577	124792	104875
25°	147414	116837	96187
30°	139863	107441	88153
35°	127033	96557	79083
40°	110679	86004	71155
45°	95770	75271	62557
50°	83656	64817	54821
55°	73909	56954	47033
60°	66442	49919	40731
65°	59488	43429	39524
70°	53118	37025	37025
75°	46111	31199	34737
80°	37000	26424	31696
85°	25285	23147	27424



TEST NUMBER: P582844

CATALOG NUMBER: HCC6S50D010BZ-HM64560940-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	233.8	5.0
10°-20°	649.8	14.0
20°-30°	905.6	19.5
30°-40°	933.1	20.1
40°-50°	773.4	16.7
50°-60°	555.8	12.0
60°-70°	353.9	7.6
70°-80°	181.8	3.9
80°-90°	46.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1789.2	38.6
0°-40°	2722.4	58.8
0°-60°	4051.5	87.4
0°-90°	4633.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4633.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2487	2487	2487	2487	2487	
5°	2588	2548	2471	2390	2357	248
15°	2641	2541	2303	2092	2012	744
25°	2437	2270	1932	1684	1590	1117
35°	1898	1744	1443	1252	1182	1179
45°	1235	1148	971	847	807	956
55°	773	710	596	529	492	697
65°	459	408	335	291	305	459
75°	218	187	147	154	164	232
85°	40	37	37	40	44	51
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582844

CATALOG NUMBER: HCC6S50D010BZ-HM64560940-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4
2.5°	2534.2	2524.2	2510.8	2497.5	2477.3	2453.9	2433.8	2427.1	2417.0
5°	2587.8	2574.5	2547.7	2514.1	2470.7	2427.1	2390.2	2366.8	2356.8
7.5°	2621.2	2604.6	2567.7	2510.8	2447.2	2383.6	2330.0	2296.6	2283.1
10°	2628.0	2611.2	2561.0	2484.0	2400.4	2313.3	2246.4	2206.1	2189.5
12.5°	2638.0	2614.6	2551.0	2460.6	2353.5	2253.0	2169.4	2119.1	2102.4
15°	2641.3	2614.6	2540.9	2430.5	2303.2	2182.7	2092.4	2032.0	2012.0
17.5°	2628.0	2597.8	2510.8	2376.9	2232.9	2105.7	1998.6	1935.0	1908.3
20°	2581.1	2547.7	2447.2	2296.6	2139.1	2005.3	1894.8	1827.8	1797.7
22.5°	2520.8	2477.3	2363.5	2202.8	2038.8	1898.2	1787.7	1720.7	1690.6
25°	2437.1	2397.0	2269.8	2099.0	1931.6	1784.4	1683.9	1613.6	1590.2
27.5°	2340.0	2293.1	2162.6	1991.9	1821.2	1673.8	1576.8	1513.2	1483.1
30°	2209.5	2166.0	2035.5	1864.7	1697.3	1560.1	1459.6	1406.1	1392.6
32.5°	2055.5	2018.7	1891.5	1730.8	1570.1	1442.8	1359.2	1302.3	1288.8
35°	1898.2	1854.6	1744.2	1593.5	1442.8	1329.1	1252.1	1201.8	1181.7
37.5°	1727.4	1687.3	1593.5	1459.6	1325.7	1218.6	1151.6	1108.1	1088.1
40°	1546.6	1516.5	1429.5	1322.4	1201.8	1108.1	1051.2	1014.4	994.3
42.5°	1379.3	1349.2	1288.8	1188.4	1088.1	1004.3	954.1	920.6	903.9
45°	1235.3	1208.5	1148.3	1061.2	970.9	900.5	847.0	823.5	806.9
47.5°	1091.4	1078.0	1024.4	944.1	860.4	800.1	763.3	736.5	723.1
50°	980.9	964.2	914.0	830.2	760.0	713.1	679.5	656.2	642.8
52.5°	867.1	850.3	803.4	733.2	676.2	632.8	599.2	579.2	565.8
55°	773.3	760.0	709.7	646.1	595.9	559.1	529.0	505.5	492.1
57.5°	686.3	672.9	626.0	565.8	522.2	488.8	462.0	441.9	425.2
60°	606.0	595.9	549.0	492.1	455.3	421.9	398.4	381.7	371.5
62.5°	535.6	515.5	475.4	425.2	391.7	364.9	341.4	331.4	338.1
65°	458.6	448.5	408.4	364.9	334.8	308.0	291.2	298.0	304.7
67.5°	395.0	381.7	348.2	308.0	281.2	261.1	251.1	264.4	267.9
70°	331.4	318.0	287.9	254.4	231.0	217.7	217.7	227.7	231.0
72.5°	271.2	261.1	234.3	207.5	190.8	180.8	187.4	194.2	197.5
75°	217.7	207.5	187.4	164.0	147.3	147.3	154.0	160.7	164.0
77.5°	167.3	160.7	140.7	123.9	117.2	117.2	123.9	127.2	130.6
80°	117.2	110.4	100.4	90.3	83.7	90.3	97.1	97.1	100.4
82.5°	77.0	73.7	67.0	60.2	60.2	63.7	67.0	70.3	70.3
85°	40.2	40.2	36.8	33.4	36.8	40.2	40.2	43.6	43.6
87.5°	13.3	13.3	13.3	13.3	16.8	16.8	16.8	16.8	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)