

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593373

Luminaire Tested: **HCC6W50D010BZ-HM64560950-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010BZ-HM64560950-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4241.7 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593373
CATALOG NUMBER: HCC6W50D010BZ-HM64560950-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P593373

CATALOG NUMBER: HCC6W50D010BZ-HM64560950-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	130488	130488	130488
5°	133006	130244	127300
10°	137534	128583	123177
15°	141743	126351	119320
20°	143938	121087	113083
25°	141341	112791	105296
30°	134356	102775	96635
35°	120756	91859	87154
40°	104217	80501	77867
45°	88242	69302	67480
50°	75665	58531	57951
55°	65594	49269	47348
60°	57254	40008	33769
65°	50369	30833	18679
70°	43469	20388	9120
75°	36876	9934	3558
80°	28507	4199	2115
85°	16857	2076	2076



TEST NUMBER: P593373

CATALOG NUMBER: HCC6W50D010BZ-HM64560950-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.6	5.3
10°-20°	635.2	15.0
20°-30°	894.5	21.1
30°-40°	913.9	21.5
40°-50°	736.9	17.4
50°-60°	494.2	11.7
60°-70°	250.1	5.9
70°-80°	79.9	1.9
80°-90°	12.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.3	41.4
0°-40°	2668.2	62.9
0°-60°	3899.3	91.9
0°-90°	4241.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4241.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2380	2380	2380	2380	2380	
5°	2417	2400	2367	2330	2313	233
15°	2498	2397	2226	2126	2102	705
25°	2337	2153	1865	1751	1741	1070
35°	1804	1640	1373	1296	1302	1123
45°	1138	1048	894	864	870	885
55°	686	609	516	492	495	617
65°	388	321	238	157	144	388
75°	174	124	47	17	17	187
85°	27	13	3	3	3	36
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593373

CATALOG NUMBER: HCC6W50D010BZ-HM64560950-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2380.3	2380.3	2380.3	2380.3	2380.3	2380.3	2380.3	2380.3	2380.3
2.5°	2390.3	2386.9	2383.6	2376.9	2366.8	2356.8	2350.2	2343.5	2340.2
5°	2417.0	2410.4	2400.4	2386.9	2366.8	2343.5	2330.0	2316.6	2313.3
7.5°	2453.9	2440.5	2413.7	2383.6	2350.2	2316.6	2293.3	2279.8	2269.8
10°	2470.7	2447.3	2410.4	2360.2	2309.9	2269.8	2239.6	2219.6	2212.8
12.5°	2484.0	2457.3	2403.7	2336.7	2269.8	2216.3	2182.7	2166.0	2159.3
15°	2497.5	2470.7	2397.0	2309.9	2226.3	2162.6	2125.8	2109.1	2102.4
17.5°	2497.5	2460.6	2373.6	2263.2	2162.6	2085.6	2048.8	2032.1	2028.7
20°	2467.3	2427.2	2320.0	2189.5	2075.6	1988.6	1955.1	1945.1	1938.4
22.5°	2410.4	2363.5	2243.0	2095.7	1971.8	1888.2	1851.3	1844.6	1837.9
25°	2336.7	2289.8	2152.6	1995.3	1864.7	1781.1	1750.8	1744.2	1740.8
27.5°	2243.0	2192.8	2048.8	1888.2	1747.5	1667.2	1640.4	1640.4	1637.1
30°	2122.5	2065.6	1924.9	1764.3	1623.6	1550.1	1530.0	1530.0	1526.6
32.5°	1975.2	1918.3	1791.1	1637.1	1503.2	1426.2	1409.4	1416.1	1412.7
35°	1804.4	1757.6	1640.4	1489.7	1372.6	1302.3	1295.6	1302.3	1302.3
37.5°	1633.7	1590.2	1489.7	1359.2	1248.7	1185.1	1185.1	1195.2	1191.9
40°	1456.3	1422.8	1329.1	1215.2	1124.9	1081.3	1074.6	1084.6	1088.1
42.5°	1288.9	1262.1	1181.7	1088.1	1007.6	964.2	974.2	980.9	984.2
45°	1138.2	1111.4	1047.9	950.8	893.9	863.8	863.8	873.8	870.4
47.5°	1004.3	984.2	920.6	826.9	776.6	763.3	770.0	776.6	776.6
50°	887.2	857.1	796.8	723.1	686.3	669.5	676.2	679.5	679.5
52.5°	776.6	756.5	696.3	629.4	595.9	585.9	585.9	589.2	589.2
55°	686.3	662.9	609.3	542.3	515.5	502.2	492.1	488.8	495.4
57.5°	599.2	579.2	529.0	465.3	435.2	421.9	401.8	395.0	401.8
60°	522.2	505.5	455.3	395.0	364.9	338.1	314.7	301.3	308.0
62.5°	455.3	435.2	385.0	334.8	301.3	271.2	234.3	214.2	224.3
65°	388.3	371.7	321.4	271.2	237.7	200.9	157.3	144.0	144.0
67.5°	328.1	311.3	264.4	221.0	180.8	137.2	97.1	93.8	97.1
70°	271.2	254.4	214.2	170.8	127.2	83.7	56.9	56.9	56.9
72.5°	224.3	204.2	167.3	123.9	80.3	43.6	30.1	33.4	33.4
75°	174.1	157.3	123.9	83.7	46.9	20.1	16.8	16.8	16.8
77.5°	130.6	117.2	87.0	53.6	23.4	6.7	6.7	6.7	6.7
80°	90.3	77.0	56.9	33.4	13.3	6.7	6.7	6.7	6.7
82.5°	53.6	46.9	33.4	16.8	6.7	3.3	3.3	3.3	3.3
85°	26.8	23.4	13.3	6.7	3.3	3.3	3.3	3.3	3.3
87.5°	6.7	6.7	3.3	3.3	0.0	3.3	3.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)