

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593375

Luminaire Tested: **HCC6W50D010MB-HM64560950-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560950-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4797.5 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593375
CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593375

CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	134293	134293	134293
5°	137200	134256	131856
10°	141397	133014	128544
15°	145869	131244	125358
20°	148185	126314	120270
25°	145750	118827	113359
30°	138762	110156	105928
35°	126545	99441	97868
40°	110650	89332	88852
45°	95219	78613	80435
50°	82769	68501	69934
55°	72284	60127	60777
60°	64216	52101	47705
65°	57308	43844	36463
70°	50425	35952	30566
75°	43251	28340	29060
80°	34853	24309	28507
85°	23147	21008	25285



TEST NUMBER: P593375
 CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.9	4.8
10°-20°	660.3	13.8
20°-30°	942.6	19.6
30°-40°	987.3	20.6
40°-50°	831.3	17.3
50°-60°	591.7	12.3
60°-70°	346.3	7.2
70°-80°	163.9	3.4
80°-90°	42.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1834.8	38.2
0°-40°	2822.2	58.8
0°-60°	4245.1	88.5
0°-90°	4797.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4797.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2450	2450	2450	2450	2450	
5°	2493	2473	2440	2406	2396	240
15°	2570	2477	2312	2219	2209	725
25°	2410	2239	1964	1871	1874	1103
35°	1891	1734	1486	1436	1462	1174
45°	1228	1138	1014	1017	1038	954
55°	756	693	629	629	636	682
65°	442	392	338	284	281	441
75°	204	171	134	130	137	219
85°	37	30	33	40	40	48
90°	0	0	0	0	0	



TEST NUMBER: P593375

CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2449.7	2449.7	2449.7	2449.7	2449.7	2449.7	2449.7	2449.7	2449.7
2.5°	2453.1	2453.1	2449.7	2446.3	2439.7	2429.7	2422.9	2416.2	2416.2
5°	2493.2	2486.6	2473.1	2456.4	2439.7	2419.6	2406.2	2396.1	2396.1
7.5°	2526.7	2513.3	2486.6	2456.4	2426.2	2399.6	2376.1	2362.7	2359.4
10°	2540.1	2523.3	2483.2	2436.3	2389.5	2352.7	2325.9	2309.2	2309.2
12.5°	2553.4	2533.4	2479.9	2412.9	2352.7	2302.5	2275.7	2262.3	2259.0
15°	2570.2	2543.4	2476.6	2392.8	2312.5	2255.6	2218.9	2208.8	2208.8
17.5°	2570.2	2536.8	2453.1	2349.4	2249.0	2185.3	2151.9	2141.9	2145.2
20°	2540.1	2503.2	2402.9	2275.7	2165.2	2098.3	2064.9	2058.1	2061.6
22.5°	2483.2	2439.7	2325.9	2188.7	2068.2	1997.9	1967.8	1967.8	1964.5
25°	2409.6	2362.7	2238.9	2095.0	1964.5	1894.2	1870.7	1874.1	1874.1
27.5°	2312.5	2265.6	2141.9	1987.9	1857.4	1787.1	1770.3	1777.1	1780.4
30°	2192.1	2141.9	2011.4	1860.7	1740.2	1669.9	1659.9	1669.9	1673.4
32.5°	2044.8	2007.9	1880.9	1726.9	1613.1	1552.8	1549.5	1559.5	1572.9
35°	1890.9	1850.6	1733.6	1593.1	1485.9	1435.7	1435.7	1452.4	1462.4
37.5°	1723.6	1683.4	1576.3	1459.1	1368.8	1321.9	1328.6	1345.4	1348.7
40°	1546.2	1516.0	1425.7	1325.3	1248.3	1211.5	1221.5	1238.3	1241.6
42.5°	1378.8	1352.0	1278.4	1188.1	1131.2	1104.4	1117.8	1137.9	1144.5
45°	1228.2	1198.1	1137.9	1060.9	1014.0	1000.7	1017.4	1030.8	1037.5
47.5°	1091.0	1064.2	1014.0	943.7	910.3	903.6	920.4	927.0	933.7
50°	970.5	943.7	893.5	830.0	803.2	803.2	816.5	823.3	820.0
52.5°	853.4	830.0	783.1	729.6	712.9	712.9	722.9	726.2	732.9
55°	756.3	732.9	692.8	642.6	629.1	622.5	629.1	629.1	635.9
57.5°	666.0	645.9	609.0	562.3	545.5	538.8	535.5	532.2	538.8
60°	585.7	568.9	528.7	488.6	475.2	458.5	445.1	431.7	435.1
62.5°	512.1	495.3	458.5	418.3	405.0	381.5	364.8	348.0	354.8
65°	441.8	425.0	391.5	358.1	338.0	311.2	284.5	274.5	281.1
67.5°	378.2	364.8	331.3	297.8	281.1	251.0	224.3	224.3	227.6
70°	314.6	301.2	274.5	244.3	224.3	197.5	187.4	190.7	190.7
72.5°	257.7	247.7	220.8	194.2	174.1	157.3	157.3	160.6	164.0
75°	204.2	197.5	170.7	147.3	133.8	123.8	130.5	133.8	137.2
77.5°	157.3	147.3	127.2	110.4	100.4	103.7	110.4	113.7	117.2
80°	110.4	107.1	90.3	80.3	77.0	80.3	87.0	90.3	90.3
82.5°	70.3	67.0	56.9	53.5	53.5	56.9	63.5	63.5	63.5
85°	36.8	33.4	30.1	30.1	33.4	36.8	40.2	40.2	40.2
87.5°	13.3	10.0	13.3	13.3	16.8	16.8	16.8	16.8	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)