

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582750

Luminaire Tested: **HCC6W50D010MB-HM64560835-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560835-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5388.9 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582750
CATALOG NUMBER: HCC6W50D010MB-HM64560835-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582750
 CATALOG NUMBER: HCC6W50D010MB-HM64560835-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	98	97	96	95	94	92	92	84	84	84															
	1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	84	84	84	81	78	77	77	70	70	70															
	2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	81	78	77	70	70	64	64	64	59	59															
	3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	70	70	64	64	59	59	54	54	54	46	46															
	4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	64	64	59	59	54	54	46	46	46	46															
	5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	59	59	54	54	46	46	46	46	46	46															
	6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	54	54	46	46	46	46	46	46	46	46															
	7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	46	46	46	46	46	46	46	46	46	46															
	8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	46	46	46	46	46	46	46	46	46	46															
	9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46	46	46	46	46	46	46	46	46															
	10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	46	46	46	46	46	46	46	46	46	46															

AVERAGE LUMINANCE (cd/sqm):

	0°	211047
	5°	212458
	10°	214915
	15°	219326
	20°	220554
	25°	213684
	30°	193846
	35°	157617
	40°	104625
	45°	58223
	50°	32647
	55°	18121
	60°	9999
	65°	7562
	70°	5257
	75°	3855
	80°	2305
	85°	2327



TEST NUMBER: P582750
 CATALOG NUMBER: HCC6W50D010MB-HM64560835-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.5	6.8
10°-20°	1089.6	20.2
20°-30°	1606.0	29.8
30°-40°	1436.5	26.7
40°-50°	623.2	11.6
50°-60°	183.1	3.4
60°-70°	58.4	1.1
70°-80°	20.6	0.4
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3064.1	56.9
0°-40°	4500.6	83.5
0°-60°	5306.9	98.5
0°-90°	5388.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5388.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3850	
5°	3861	369
15°	3864	1090
25°	3533	1606
35°	2355	1436
45°	751	623
55°	190	183
65°	58	58
75°	18	21
85°	4	3
90°	0	



TEST NUMBER: P582750
CATALOG NUMBER: HCC6W50D010MB-HM64560835-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3849.8
2.5°	3839.0
5°	3860.8
7.5°	3868.1
10°	3860.8
12.5°	3860.8
15°	3864.5
17.5°	3842.5
20°	3780.6
22.5°	3674.8
25°	3532.7
27.5°	3332.2
30°	3062.3
32.5°	2741.6
35°	2355.2
37.5°	1913.9
40°	1462.0
42.5°	1068.2
45°	751.0
47.5°	535.9
50°	382.8
52.5°	273.4
55°	189.6
57.5°	127.5
60°	91.2
62.5°	72.9
65°	58.3
67.5°	43.7
70°	32.8
72.5°	25.5
75°	18.2
77.5°	14.5
80°	7.3
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)