

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593357

Luminaire Tested: **HCC6S50D010MW-HM64560850-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MW-HM64560850-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5437.3 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593357
CATALOG NUMBER: HCC6S50D010MW-HM64560850-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P593357

CATALOG NUMBER: HCC6S50D010MW-HM64560850-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87	87	87	87
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52	52	52	52
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46	46	46	46
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42	42	42	42
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38	38	38	38
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34	34	34	34
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31	31	31	31

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	152208	152208	152208
5°	155503	152162	149449
10°	160256	150754	145689
15°	165330	148752	142078
20°	167950	143168	136308
25°	165185	134675	128475
30°	157271	124855	120044
35°	143416	112705	110925
40°	125406	101247	100703
45°	107918	89095	91157
50°	93814	77635	79255
55°	81928	68155	68872
60°	72768	59063	54064
65°	64936	49694	41327
70°	57141	40744	34653
75°	49013	32153	32936
80°	39525	27560	32327
85°	26229	23839	28619



TEST NUMBER: P593357
 CATALOG NUMBER: HCC6S50D010MW-HM64560850-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.9	4.8
10°-20°	748.4	13.8
20°-30°	1068.3	19.6
30°-40°	1119.0	20.6
40°-50°	942.2	17.3
50°-60°	670.6	12.3
60°-70°	392.5	7.2
70°-80°	185.7	3.4
80°-90°	47.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2079.5	38.2
0°-40°	3198.6	58.8
0°-60°	4811.3	88.5
0°-90°	5437.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5437.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2776	2776	2776	2776	2776	
5°	2826	2803	2765	2727	2716	272
15°	2913	2807	2621	2515	2503	822
25°	2731	2538	2226	2120	2124	1250
35°	2143	1965	1684	1627	1658	1331
45°	1392	1290	1149	1153	1176	1081
55°	857	785	713	713	721	773
65°	501	444	383	322	319	499
75°	231	193	152	148	156	248
85°	42	34	38	46	46	54
90°	0	0	0	0	0	



TEST NUMBER: P593357

CATALOG NUMBER: HCC6S50D010MW-HM64560850-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2776.5	2776.5	2776.5	2776.5	2776.5	2776.5	2776.5	2776.5	2776.5
2.5°	2780.3	2780.3	2776.5	2772.6	2765.1	2753.7	2746.2	2738.5	2738.5
5°	2825.8	2818.2	2803.0	2784.1	2765.1	2742.3	2727.2	2715.8	2715.8
7.5°	2863.7	2848.6	2818.2	2784.1	2750.0	2719.6	2693.0	2677.9	2674.0
10°	2878.9	2859.9	2814.4	2761.3	2708.2	2666.5	2636.1	2617.2	2617.2
12.5°	2894.0	2871.2	2810.7	2734.7	2666.5	2609.5	2579.2	2564.1	2560.3
15°	2913.1	2882.7	2806.8	2712.0	2621.0	2556.5	2514.7	2503.4	2503.4
17.5°	2913.1	2875.1	2780.3	2662.7	2549.0	2476.8	2438.9	2427.5	2431.3
20°	2878.9	2837.1	2723.4	2579.2	2454.1	2378.2	2340.3	2332.7	2336.5
22.5°	2814.4	2765.1	2636.1	2480.6	2344.0	2264.4	2230.3	2230.3	2226.5
25°	2730.9	2677.9	2537.5	2374.4	2226.5	2146.8	2120.2	2124.0	2124.0
27.5°	2621.0	2567.8	2427.5	2253.0	2105.1	2025.4	2006.5	2014.1	2017.9
30°	2484.5	2427.5	2279.6	2108.9	1972.4	1892.7	1881.3	1892.7	1896.4
32.5°	2317.5	2275.8	2131.7	1957.2	1828.2	1759.9	1756.1	1767.5	1782.7
35°	2143.0	2097.6	1964.8	1805.5	1684.1	1627.2	1627.2	1646.2	1657.5
37.5°	1953.4	1907.9	1786.5	1653.8	1551.4	1498.2	1505.8	1524.8	1528.6
40°	1752.4	1718.2	1615.8	1502.0	1414.8	1373.0	1384.5	1403.4	1407.2
42.5°	1562.7	1532.3	1449.0	1346.5	1282.1	1251.7	1266.9	1289.7	1297.2
45°	1392.0	1357.9	1289.7	1202.4	1149.2	1134.1	1153.1	1168.2	1175.8
47.5°	1236.5	1206.2	1149.2	1069.6	1031.7	1024.2	1043.1	1050.6	1058.3
50°	1100.0	1069.6	1012.7	940.7	910.3	910.3	925.5	933.1	929.3
52.5°	967.2	940.7	887.5	826.8	807.9	807.9	819.3	823.0	830.7
55°	857.2	830.7	785.1	728.2	713.1	705.5	713.1	713.1	720.6
57.5°	754.8	732.1	690.3	637.3	618.3	610.7	606.9	603.1	610.7
60°	663.7	644.8	599.2	553.8	538.7	519.6	504.5	489.3	493.1
62.5°	580.3	561.3	519.6	474.2	458.9	432.4	413.5	394.5	402.0
65°	500.6	481.7	443.8	405.9	383.1	352.8	322.4	311.1	318.6
67.5°	428.6	413.5	375.6	337.5	318.6	284.5	254.2	254.2	257.9
70°	356.5	341.4	311.1	276.9	254.2	223.8	212.5	216.2	216.2
72.5°	292.1	280.7	250.4	220.0	197.2	178.2	178.2	182.1	185.9
75°	231.4	223.8	193.4	166.9	151.8	140.3	148.0	151.8	155.5
77.5°	178.2	166.9	144.1	125.2	113.8	117.6	125.2	129.0	132.7
80°	125.2	121.4	102.4	91.1	87.3	91.1	98.6	102.4	102.4
82.5°	79.6	75.8	64.5	60.7	60.7	64.5	72.0	72.0	72.0
85°	41.7	37.9	34.1	34.1	37.9	41.7	45.5	45.5	45.5
87.5°	15.1	11.3	15.1	15.1	19.0	19.0	19.0	19.0	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)