

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582791

Luminaire Tested: **HCC6W50D010MW-HM64560927-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MW-HM64560927-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3847.6 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582791
CATALOG NUMBER: HCC6W50D010MW-HM64560927-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582791

CATALOG NUMBER: HCC6W50D010MW-HM64560927-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	107705	107705	107705
5°	110037	107676	105750
10°	113402	106678	103088
15°	116987	105256	100540
20°	118847	101305	96457
25°	116892	95304	90919
30°	111283	88349	84950
35°	101489	79752	78501
40°	88738	71641	71262
45°	76372	63045	64503
50°	66386	54932	56083
55°	57976	48228	48744
60°	51498	41784	38254
65°	45958	35153	29251
70°	40440	28835	24507
75°	34673	22748	23320
80°	27971	19510	22888
85°	18555	16857	20254



TEST NUMBER: P582791

CATALOG NUMBER: HCC6W50D010MW-HM64560927-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.0	4.8
10°-20°	529.6	13.8
20°-30°	756.0	19.6
30°-40°	791.9	20.6
40°-50°	666.7	17.3
50°-60°	474.5	12.3
60°-70°	277.7	7.2
70°-80°	131.4	3.4
80°-90°	33.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.5	38.2
0°-40°	2263.4	58.8
0°-60°	3404.6	88.5
0°-90°	3847.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3847.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1965	1965	1965	1965	1965	
5°	2000	1984	1957	1930	1922	192
15°	2061	1986	1855	1780	1772	582
25°	1932	1796	1576	1500	1503	885
35°	1516	1390	1192	1152	1173	942
45°	985	913	813	816	832	765
55°	607	556	505	505	510	547
65°	354	314	271	228	226	353
75°	164	137	107	105	110	176
85°	30	24	27	32	32	38
90°	0	0	0	0	0	



TEST NUMBER: P582791

CATALOG NUMBER: HCC6W50D010MW-HM64560927-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1964.7	1964.7	1964.7	1964.7	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1967.4	1967.4	1964.7	1962.0	1956.7	1948.6	1943.2	1937.9	1937.9
5°	1999.6	1994.2	1983.5	1970.0	1956.7	1940.5	1929.8	1921.7	1921.7
7.5°	2026.5	2015.7	1994.2	1970.0	1945.9	1924.4	1905.7	1894.9	1892.2
10°	2037.2	2023.8	1991.5	1954.0	1916.4	1886.9	1865.4	1851.9	1851.9
12.5°	2047.9	2031.8	1988.8	1935.2	1886.9	1846.6	1825.1	1814.4	1811.7
15°	2061.3	2039.8	1986.2	1919.1	1854.6	1809.1	1779.5	1771.5	1771.5
17.5°	2061.3	2034.5	1967.4	1884.2	1803.6	1752.6	1725.8	1717.8	1720.5
20°	2037.2	2007.7	1927.2	1825.1	1736.5	1682.9	1656.0	1650.7	1653.4
22.5°	1991.5	1956.7	1865.4	1755.3	1658.7	1602.4	1578.2	1578.2	1575.6
25°	1932.5	1894.9	1795.6	1680.2	1575.6	1519.1	1500.3	1503.1	1503.1
27.5°	1854.6	1817.1	1717.8	1594.4	1489.6	1433.3	1419.8	1425.2	1427.9
30°	1758.0	1717.8	1613.1	1492.3	1395.7	1339.4	1331.2	1339.4	1342.0
32.5°	1639.9	1610.4	1508.4	1385.0	1293.7	1245.4	1242.6	1250.8	1261.5
35°	1516.5	1484.3	1390.3	1277.6	1191.7	1151.5	1151.5	1164.8	1173.0
37.5°	1382.2	1350.0	1264.1	1170.3	1097.7	1060.2	1065.5	1079.0	1081.7
40°	1240.0	1215.8	1143.4	1062.9	1001.1	971.6	979.6	993.1	995.8
42.5°	1105.8	1084.4	1025.3	952.8	907.2	885.8	896.5	912.6	918.0
45°	985.1	960.9	912.6	850.8	813.2	802.5	816.0	826.7	832.0
47.5°	875.0	853.5	813.2	756.9	730.1	724.7	738.1	743.4	748.9
50°	778.4	756.9	716.6	665.6	644.1	644.1	654.9	660.3	657.6
52.5°	684.4	665.6	628.1	585.1	571.7	571.7	579.8	582.5	587.8
55°	606.6	587.8	555.5	515.4	504.6	499.2	504.6	504.6	510.0
57.5°	534.2	518.0	488.5	450.9	437.4	432.1	429.4	426.8	432.1
60°	469.7	456.3	424.1	391.9	381.1	367.8	357.0	346.3	348.9
62.5°	410.6	397.3	367.8	335.5	324.8	306.0	292.5	279.2	284.5
65°	354.3	340.8	314.0	287.2	271.0	249.7	228.2	220.1	225.5
67.5°	303.3	292.5	265.7	238.9	225.5	201.2	179.9	179.9	182.5
70°	252.3	241.5	220.1	195.9	179.9	158.4	150.3	152.9	152.9
72.5°	206.7	198.6	177.2	155.7	139.6	126.1	126.1	128.8	131.6
75°	163.7	158.4	136.9	118.1	107.4	99.3	104.6	107.4	110.1
77.5°	126.1	118.1	102.0	88.6	80.5	83.3	88.6	91.3	93.9
80°	88.6	85.9	72.5	64.4	61.8	64.4	69.8	72.5	72.5
82.5°	56.3	53.7	45.6	43.0	43.0	45.6	51.0	51.0	51.0
85°	29.5	26.8	24.2	24.2	26.8	29.5	32.2	32.2	32.2
87.5°	10.7	8.0	10.7	10.7	13.5	13.5	13.5	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)