

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582950

Luminaire Tested: **HCC6S05D010SL-HM60525930-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582950  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S05D010SL-HM60525930-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 643.7 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582950  
CATALOG NUMBER: HCC6S05D010SL-HM60525930-61WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P582950

CATALOG NUMBER: HCC6S05D010SL-HM60525930-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91	91	91	91	91	91	91	91	91	91	91	91																
	2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82	82	82	82	82	82	82	82	82	82	82	82																
	3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75	75	75	75	75	75	75	75	75	75	75	75																
	4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69	69	69	69	69	69	69	69	69	69	69	69																
	5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63	63	63	63	63	63	63	63	63	63	63	63																
	6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58	58	58	58	58	58	58	58	58	58	58	58																
	7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54	54	54	54	54	54	54	54	54																
	8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50	50	50	50	50	50	50	50	50	50	50	50																
	9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46	46	46	46	46	46	46	46	46	46	46	46																
	10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43	43	43	43	43	43	43	43	43	43	43	43																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	24011
	5°	24213
	10°	25083
	15°	27248
	20°	28347
	25°	27110
	30°	23396
	35°	16851
	40°	9496
	45°	4915
	50°	2934
	55°	2112
	60°	1798
	65°	2062
	70°	2629
	75°	2775
	80°	2715
	85°	2579



TEST NUMBER: P582950  
 CATALOG NUMBER: HCC6S05D010SL-HM60525930-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.3	6.6
10°-20°	135.4	21.0
20°-30°	202.4	31.4
30°-40°	154.7	24.0
40°-50°	54.0	8.4
50°-60°	20.6	3.2
60°-70°	16.1	2.5
70°-80°	13.7	2.1
80°-90°	4.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.1	59.1
0°-40°	534.9	83.1
0°-60°	609.5	94.7
0°-90°	643.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	643.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	438	
5°	440	42
15°	480	135
25°	448	202
35°	252	155
45°	63	54
55°	22	21
65°	16	16
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P582950  
CATALOG NUMBER: HCC6S05D010SL-HM60525930-61WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	438.0
2.5°	436.7
5°	440.0
7.5°	444.5
10°	450.6
12.5°	464.5
15°	480.1
17.5°	489.5
20°	485.9
22.5°	471.1
25°	448.2
27.5°	415.4
30°	369.6
32.5°	314.7
35°	251.8
37.5°	186.7
40°	132.7
42.5°	92.9
45°	63.4
47.5°	44.6
50°	34.4
52.5°	27.0
55°	22.1
57.5°	18.0
60°	16.4
62.5°	15.9
65°	15.9
67.5°	16.8
70°	16.4
72.5°	15.1
75°	13.1
77.5°	11.1
80°	8.6
82.5°	6.1
85°	4.1
87.5°	1.6
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)