

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582809

Luminaire Tested: **HCC6S50D010MW-HM64560930-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MW-HM64560930-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4596.7 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582809
CATALOG NUMBER: HCC6S50D010MW-HM64560930-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582809

CATALOG NUMBER: HCC6S50D010MW-HM64560930-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	128674	128674	128674
5°	131460	128637	126342
10°	135480	127447	123161
15°	139762	125756	120114
20°	141984	121035	115230
25°	139647	113855	108617
30°	132951	105554	101490
35°	121245	95278	93779
40°	106013	85589	85131
45°	91242	75326	77062
50°	79307	65627	67000
55°	69264	57613	58234
60°	61519	49919	45709
65°	54909	42002	34945
70°	48309	34429	29300
75°	41430	27175	27832
80°	33401	23267	27339
85°	22203	20191	24216



TEST NUMBER: P582809
 CATALOG NUMBER: HCC6S50D010MW-HM64560930-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.2	4.8
10°-20°	632.7	13.8
20°-30°	903.1	19.6
30°-40°	946.0	20.6
40°-50°	796.5	17.3
50°-60°	566.9	12.3
60°-70°	331.8	7.2
70°-80°	157.0	3.4
80°-90°	40.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1758.0	38.2
0°-40°	2704.1	58.8
0°-60°	4067.4	88.5
0°-90°	4596.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4596.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2347	2347	2347	2347	2347	
5°	2389	2370	2338	2306	2296	230
15°	2463	2373	2216	2126	2116	695
25°	2309	2145	1882	1792	1796	1057
35°	1812	1661	1424	1376	1401	1125
45°	1177	1090	972	975	994	914
55°	725	664	603	603	609	653
65°	423	375	324	273	269	422
75°	196	164	128	125	131	210
85°	35	29	32	38	38	46
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582809

CATALOG NUMBER: HCC6S50D010MW-HM64560930-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2347.2	2347.2	2347.2	2347.2	2347.2	2347.2	2347.2	2347.2	2347.2
2.5°	2350.4	2350.4	2347.2	2344.0	2337.6	2328.0	2321.6	2315.1	2315.1
5°	2388.9	2382.4	2369.7	2353.6	2337.6	2318.3	2305.5	2295.9	2295.9
7.5°	2420.9	2408.2	2382.4	2353.6	2324.8	2299.1	2276.6	2263.9	2260.7
10°	2433.8	2417.7	2379.2	2334.4	2289.5	2254.2	2228.5	2212.5	2212.5
12.5°	2446.6	2427.4	2376.1	2311.9	2254.2	2206.1	2180.5	2167.6	2164.4
15°	2462.6	2437.0	2372.9	2292.7	2215.8	2161.2	2125.9	2116.4	2116.4
17.5°	2462.6	2430.6	2350.4	2251.0	2154.9	2093.9	2061.8	2052.2	2055.4
20°	2433.8	2398.5	2302.4	2180.5	2074.7	2010.5	1978.4	1972.0	1975.2
22.5°	2379.2	2337.6	2228.5	2097.1	1981.6	1914.3	1885.5	1885.5	1882.3
25°	2308.7	2263.9	2145.2	2007.3	1882.3	1815.0	1792.5	1795.7	1795.7
27.5°	2215.8	2170.8	2052.2	1904.7	1779.6	1712.3	1696.3	1702.6	1705.8
30°	2100.3	2052.2	1927.2	1782.8	1667.5	1600.0	1590.5	1600.0	1603.3
32.5°	1959.2	1924.0	1802.1	1654.6	1545.6	1487.8	1484.6	1494.2	1507.1
35°	1811.7	1773.3	1661.0	1526.3	1423.7	1375.6	1375.6	1391.7	1401.3
37.5°	1651.4	1612.9	1510.3	1398.1	1311.5	1266.6	1273.0	1289.1	1292.3
40°	1481.4	1452.6	1365.9	1269.8	1196.0	1160.8	1170.4	1186.4	1189.6
42.5°	1321.1	1295.4	1224.9	1138.4	1083.8	1058.2	1071.0	1090.2	1096.7
45°	1176.9	1147.9	1090.2	1016.5	971.6	958.7	974.8	987.7	994.0
47.5°	1045.3	1019.7	971.6	904.3	872.2	865.8	881.9	888.2	894.6
50°	929.9	904.3	856.1	795.3	769.5	769.5	782.4	788.8	785.6
52.5°	817.7	795.3	750.3	699.0	683.0	683.0	692.7	695.8	702.2
55°	724.7	702.2	663.7	615.7	602.8	596.4	602.8	602.8	609.3
57.5°	638.1	618.8	583.7	538.7	522.7	516.2	513.0	509.8	516.2
60°	561.1	545.1	506.6	468.1	455.3	439.3	426.5	413.7	416.9
62.5°	490.6	474.5	439.3	400.8	388.0	365.5	349.5	333.5	339.9
65°	423.3	407.2	375.2	343.1	323.8	298.2	272.6	262.9	269.4
67.5°	362.3	349.5	317.5	285.3	269.4	240.5	214.8	214.8	218.0
70°	301.4	288.6	262.9	234.1	214.8	189.2	179.5	182.8	182.8
72.5°	246.9	237.3	211.6	186.0	166.8	150.7	150.7	153.9	157.1
75°	195.6	189.2	163.6	141.1	128.3	118.7	125.1	128.3	131.4
77.5°	150.7	141.1	121.9	105.8	96.3	99.4	105.8	109.0	112.2
80°	105.8	102.6	86.6	77.0	73.7	77.0	83.4	86.6	86.6
82.5°	67.3	64.1	54.6	51.3	51.3	54.6	60.9	60.9	60.9
85°	35.3	32.1	28.8	28.8	32.1	35.3	38.5	38.5	38.5
87.5°	12.9	9.6	12.9	12.9	16.1	16.1	16.1	16.1	16.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)