

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582962

Luminaire Tested: **HCC6S05D010MB-HM60525935-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010MB-HM60525935-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 641.9 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582962
CATALOG NUMBER: HCC6S05D010MB-HM60525935-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582962

CATALOG NUMBER: HCC6S05D010MB-HM60525935-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17433	17433	17433
5°	17521	17615	17615
10°	18008	17702	17624
15°	18587	17804	17804
20°	18802	17391	17793
25°	18424	16519	17305
30°	17427	15357	16249
35°	15774	14040	14730
40°	13726	12702	13196
45°	11722	11327	11722
50°	10294	9919	10319
55°	8975	8363	8688
60°	7938	6940	6853
65°	7031	5487	4696
70°	6219	3879	2821
75°	5295	2203	1356
80°	3946	663	379
85°	2201	314	314



TEST NUMBER: P582962
 CATALOG NUMBER: HCC6S05D010MB-HM60525935-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	4.8
10°-20°	89.2	13.9
20°-30°	130.3	20.3
30°-40°	136.7	21.3
40°-50°	115.2	17.9
50°-60°	80.7	12.6
60°-70°	43.3	6.7
70°-80°	14.5	2.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.1	39.0
0°-40°	386.7	60.2
0°-60°	582.6	90.8
0°-90°	641.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	318	318	318	318	318	
5°	318	320	320	320	320	31
15°	328	323	314	312	314	92
25°	305	292	273	278	286	140
35°	236	224	210	216	220	146
45°	151	149	146	150	151	118
55°	94	91	88	89	91	85
65°	54	50	42	35	36	54
75°	25	19	10	6	6	27
85°	4	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582962

CATALOG NUMBER: HCC6S05D010MB-HM60525935-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	318.0	318.0	318.0	318.0	318.0	318.0	318.0	318.0	318.0
2.5°	315.8	315.8	316.6	317.5	318.4	318.4	318.8	319.2	318.8
5°	318.4	318.4	319.7	320.1	320.1	319.7	320.1	320.1	320.1
7.5°	322.3	321.4	321.8	320.9	320.1	319.7	319.2	319.2	319.2
10°	323.5	322.7	321.8	320.1	318.0	316.6	316.3	316.6	316.6
12.5°	325.3	324.4	322.3	318.8	316.3	314.0	313.7	314.5	314.5
15°	327.5	326.6	323.2	317.5	313.7	311.5	311.9	312.8	313.7
17.5°	327.5	325.7	320.1	312.8	308.0	305.9	307.6	309.7	311.1
20°	322.3	320.6	312.8	303.7	298.1	296.9	299.9	303.7	305.0
22.5°	315.4	311.9	302.8	292.1	286.1	286.1	290.4	295.2	296.9
25°	304.6	302.0	291.7	279.2	273.1	272.7	277.9	284.3	286.1
27.5°	292.6	289.1	277.9	265.0	258.5	258.9	264.5	271.0	272.7
30°	275.3	271.0	261.1	248.6	242.6	244.3	249.8	254.6	256.7
32.5°	255.9	252.0	243.0	231.3	226.2	227.9	232.7	237.0	238.7
35°	235.7	231.3	223.6	213.2	209.8	211.5	215.8	219.3	220.1
37.5°	212.8	209.8	204.2	196.1	193.5	195.6	199.0	201.3	202.0
40°	191.8	189.2	184.4	178.3	177.5	179.2	182.7	184.0	184.4
42.5°	171.1	168.9	165.9	161.6	161.6	163.3	166.3	167.1	167.6
45°	151.2	150.0	148.6	145.2	146.1	148.3	150.0	151.2	151.2
47.5°	134.0	134.5	132.7	130.1	131.0	133.1	134.5	135.7	135.7
50°	120.7	119.3	117.6	115.0	116.3	118.1	119.8	120.7	121.0
52.5°	105.1	104.6	103.4	100.3	101.2	102.2	103.8	105.1	105.5
55°	93.9	92.7	90.9	87.5	87.5	88.4	89.2	90.1	90.9
57.5°	83.2	81.8	79.3	75.4	74.9	74.9	74.6	75.4	76.7
60°	72.4	72.0	68.0	64.6	63.3	62.0	60.3	60.8	62.5
62.5°	62.9	62.0	58.6	54.2	51.8	49.5	47.3	47.0	48.7
65°	54.2	53.4	49.5	45.2	42.3	38.3	34.9	34.9	36.2
67.5°	46.6	44.9	41.4	36.6	32.8	28.0	24.5	25.4	25.9
70°	38.8	37.5	33.6	28.8	24.2	19.4	17.3	17.6	17.6
72.5°	31.9	30.2	26.3	21.6	16.8	12.5	11.6	11.2	11.2
75°	25.0	23.3	19.4	14.7	10.4	7.3	6.4	6.4	6.4
77.5°	18.1	16.8	13.3	9.0	5.6	3.5	3.1	2.6	2.6
80°	12.5	11.2	8.1	4.7	2.1	1.2	1.2	1.2	1.2
82.5°	7.3	6.0	3.8	2.1	0.9	0.5	0.5	0.5	0.5
85°	3.5	2.6	1.7	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)