

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582971

Luminaire Tested: **HCC6W05D010MB-HM60525935-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W05D010MB-HM60525935-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 617.3 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582971
CATALOG NUMBER: HCC6W05D010MB-HM60525935-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582971

CATALOG NUMBER: HCC6W05D010MB-HM60525935-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	34	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17285	17285	17285
5°	17653	17274	16971
10°	18197	17117	16544
15°	18774	16890	16129
20°	19071	16259	15477
25°	18757	15291	14584
30°	17851	14179	13635
35°	16282	12796	12588
40°	14241	11500	11436
45°	12257	10117	10350
50°	10652	8818	8998
55°	9300	7732	7818
60°	8267	6699	6129
65°	7368	5643	4696
70°	6491	4616	3927
75°	5549	3643	3728
80°	4483	3125	3662
85°	2956	2705	3271



TEST NUMBER: P582971
 CATALOG NUMBER: HCC6W05D010MB-HM60525935-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.8	4.8
10°-20°	85.0	13.8
20°-30°	121.3	19.6
30°-40°	127.1	20.6
40°-50°	107.0	17.3
50°-60°	76.1	12.3
60°-70°	44.5	7.2
70°-80°	21.1	3.4
80°-90°	5.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.1	38.2
0°-40°	363.2	58.8
0°-60°	546.3	88.5
0°-90°	617.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	315	315	315	315	315	
5°	321	318	314	310	308	31
15°	331	319	298	286	284	93
25°	310	288	253	241	241	142
35°	243	223	191	185	188	151
45°	158	146	130	131	134	123
55°	97	89	81	81	82	88
65°	57	50	44	37	36	57
75°	26	22	17	17	18	28
85°	5	4	4	5	5	6
90°	0	0	0	0	0	



TEST NUMBER: P582971

CATALOG NUMBER: HCC6W05D010MB-HM60525935-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3
2.5°	315.7	315.7	315.3	314.8	313.9	312.7	311.8	311.0	311.0
5°	320.8	320.0	318.2	316.1	313.9	311.3	309.6	308.4	308.4
7.5°	325.1	323.4	320.0	316.1	312.2	308.8	305.8	304.1	303.6
10°	326.9	324.8	319.6	313.6	307.5	302.7	299.3	297.2	297.2
12.5°	328.6	326.0	319.1	310.5	302.7	296.3	292.9	291.1	290.7
15°	330.8	327.2	318.7	307.9	297.6	290.3	285.6	284.2	284.2
17.5°	330.8	326.5	315.7	302.3	289.4	281.3	277.0	275.6	276.1
20°	326.9	322.2	309.2	292.9	278.7	270.1	265.7	264.9	265.3
22.5°	319.6	313.9	299.3	281.6	266.1	257.1	253.2	253.2	252.8
25°	310.1	304.1	288.2	269.6	252.8	243.7	240.7	241.1	241.1
27.5°	297.6	291.5	275.6	255.8	239.0	230.0	227.8	228.7	229.2
30°	282.0	275.6	258.8	239.4	224.0	214.9	213.6	214.9	215.4
32.5°	263.2	258.4	242.0	222.3	207.6	199.8	199.4	200.7	202.4
35°	243.3	238.2	223.1	205.0	191.2	184.8	184.8	186.9	188.1
37.5°	221.8	216.6	202.8	187.8	176.2	170.1	171.0	173.1	173.6
40°	199.0	195.0	183.5	170.5	160.7	155.9	157.2	159.3	159.8
42.5°	177.4	174.0	164.5	152.9	145.5	142.2	143.8	146.4	147.2
45°	158.1	154.1	146.4	136.5	130.5	128.8	131.0	132.7	133.5
47.5°	140.3	137.0	130.5	121.5	117.2	116.3	118.4	119.3	120.1
50°	124.9	121.5	115.0	106.8	103.4	103.4	105.1	106.0	105.5
52.5°	109.8	106.8	100.8	93.9	91.8	91.8	93.0	93.5	94.4
55°	97.3	94.4	89.2	82.7	80.9	80.1	80.9	80.9	81.8
57.5°	85.7	83.2	78.4	72.3	70.2	69.4	68.9	68.5	69.4
60°	75.4	73.2	68.0	62.8	61.1	59.0	57.3	55.6	55.9
62.5°	65.9	63.7	59.0	53.8	52.1	49.0	46.9	44.7	45.7
65°	56.8	54.7	50.4	46.1	43.5	40.0	36.6	35.4	36.2
67.5°	48.7	46.9	42.6	38.3	36.2	32.3	28.8	28.8	29.3
70°	40.5	38.8	35.4	31.4	28.8	25.4	24.1	24.5	24.5
72.5°	33.1	31.9	28.5	25.0	22.4	20.2	20.2	20.7	21.1
75°	26.2	25.4	21.9	19.0	17.2	15.9	16.8	17.2	17.6
77.5°	20.2	19.0	16.4	14.2	12.9	13.3	14.2	14.7	15.0
80°	14.2	13.8	11.6	10.3	9.9	10.3	11.2	11.6	11.6
82.5°	9.0	8.6	7.3	6.9	6.9	7.3	8.1	8.1	8.1
85°	4.7	4.3	3.8	3.8	4.3	4.7	5.2	5.2	5.2
87.5°	1.7	1.2	1.7	1.7	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)