

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582811

Luminaire Tested: **HCC6S50D010MW-HM64560935-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MW-HM64560935-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5118.0 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582811
CATALOG NUMBER: HCC6S50D010MW-HM64560935-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582811
 CATALOG NUMBER: HCC6S50D010MW-HM64560935-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61																			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57																			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54																			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243045
5°	246830
10°	260884
15°	290478
20°	301242
25°	247157
30°	173191
35°	118159
40°	61551
45°	21638
50°	9688
55°	3106
60°	1776
65°	1258
70°	1042
75°	678
80°	0
85°	0



TEST NUMBER: P582811
 CATALOG NUMBER: HCC6S50D010MW-HM64560935-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.5	8.5
10°-20°	1439.4	28.1
20°-30°	1832.8	35.8
30°-40°	1092.3	21.3
40°-50°	264.9	5.2
50°-60°	40.7	0.8
60°-70°	10.0	0.2
70°-80°	3.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3706.7	72.4
0°-40°	4799.1	93.8
0°-60°	5104.6	99.7
0°-90°	5118.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5118.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4434	
5°	4485	434
15°	5118	1439
25°	4086	1833
35°	1766	1092
45°	279	265
55°	32	41
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582811
CATALOG NUMBER: HCC6S50D010MW-HM64560935-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4433.5
2.5°	4433.5
5°	4485.4
7.5°	4566.6
10°	4686.6
12.5°	4874.8
15°	5118.2
17.5°	5270.8
20°	5163.7
22.5°	4751.5
25°	4086.1
27.5°	3352.6
30°	2736.0
32.5°	2236.2
35°	1765.6
37.5°	1301.5
40°	860.1
42.5°	464.1
45°	279.1
47.5°	175.3
50°	113.6
52.5°	68.1
55°	32.5
57.5°	19.5
60°	16.2
62.5°	13.0
65°	9.7
67.5°	6.5
70°	6.5
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)